



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Revision Date 02.02.2012

Version 3.3

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Catalogue No.	820920
Product name	n-Octadecane for synthesis
REACH Registration Number	A registration number is not available for this substance as the substance or its use are exempted from registration according to Article 2 REACH Regulation (EC) No 1907/2006, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis For additional information on uses please refer to the Merck Chemicals portal (www.merck-chemicals.com).
-----------------	---

1.3 Details of the supplier of the safety data sheet

Company	Merck KGaA * 64271 Darmstadt * Germany * Phone:+49 6151 72-0
Responsible Department	EQ-RS * e-mail: prodsafe@merckgroup.com

1.4 Emergency telephone number	Please contact the regional company representation in your country.
--------------------------------	---

SECTION 2. Hazards identification

2.1 Classification of the substance or mixture

This substance is not classified as dangerous according to European Union legislation.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)
Not a dangerous substance according to GHS.

Labelling (67/548/EEC or 1999/45/EC)

The product does not need to be labelled in accordance with EC directives or respective national laws.

2.3 Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	$\text{CH}_3(\text{CH}_2)_{16}\text{CH}_3$	$\text{C}_{18}\text{H}_{38}$ (Hill)
CAS-No.	593-45-3	
EC-No.	209-790-3	
Molar mass	254,49 g/mol	

For the full text of the H-Statements mentioned in this Section, see Section 16.

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

Catalogue No.	820920
Product name	n-Octadecane for synthesis

Remarks	No dangerous ingredients according to Regulation (EC) No. 1907/2006
---------	---

SECTION 4. First aid measures

4.1 Description of first aid measures

After inhalation: fresh air.

After skin contact: wash off with plenty of water. Remove contaminated clothing.

After eye contact: rinse out with plenty of water.

After swallowing: caution if victim vomits. Risk of aspiration! Keep airways free. Pulmonary failure possible after aspiration of vomit. Consult a physician.

4.2 Most important symptoms and effects, both acute and delayed

We have no description of any toxic symptoms.

4.3 Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

5.2 Special hazards arising from the substance or mixture

Combustible material, Vapours are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapours possible in the event of fire.

5.3 Advice for firefighters

Special protective equipment for firefighters

In the event of fire, wear self-contained breathing apparatus.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid inhalation of vapours/aerosols or dusts. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

6.2 Environmental precautions

Do not empty into drains.

6.3 Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7.2 and 10.5).

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

Catalogue No. 820920
Product name n-Octadecane for synthesis

Depending on the state of matter, take up with suitable equipment or with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

6.4 Reference to other sections

Indications about waste treatment see section 13.

SECTION 7. Handling and storage

7.1 Precautions for safe handling

Observe label precautions.

7.2 Conditions for safe storage, including any incompatibilities

Tightly closed.

Store at +15°C to +25°C.

7.3 Specific end uses

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

SECTION 8. Exposure controls/personal protection

8.1 Control parameters

8.2 Exposure controls

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

See section 7.1.

Individual protection measures

Protective clothing needs to be selected specifically for the workplace, depending on concentrations and quantities of the hazardous substances handled. The chemical resistance of the protective equipment should be enquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

full contact:

Glove material:	Nitrile rubber
Glove thickness:	0,11 mm
Break through time:	> 480 min

splash contact:

Glove material:	Nitrile rubber
Glove thickness:	0,11 mm
Break through time:	> 480 min

The protective gloves to be used must comply with the specifications of EC Directive 89/686/EEC and the related standard EN374, for example KCL 741 Dermatril® L (full contact), KCL 741 Dermatril® L (splash contact).

The breakthrough times stated above were determined by KCL in laboratory tests acc. to EN374 with samples of the recommended glove types.

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

Catalogue No. 820920
Product name n-Octadecane for synthesis

This recommendation applies only to the product stated in the safety data sheet(>,<)> supplied by us and for the designated use. When dissolving in or mixing with other substances and under conditions deviating from those stated in EN374 please contact the supplier of CE-approved gloves (e.g. KCL GmbH, D-36124 Eichenzell, Internet: www.kcl.de).

Respiratory protection

required when dusts/vapours/aerosols are generated.

Environmental exposure controls

Do not empty into drains.

SECTION 9. Physical and chemical properties

9.1 Information on basic physical and chemical properties

Form	solid
Colour	off-white
Odour	characteristic
Odour Threshold	No information available.
pH	No information available.
Melting point	26 - 29 °C
Boiling point/boiling range	317 °C
Flash point	154 °C Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapour pressure	< 0,1 hPa at 20 °C
Relative vapour density	8,78
Relative density	0,78 g/cm ³ at 20 °C
Water solubility	< 0,0001 g/l at 25 °C (Lit.), (experimental)
Partition coefficient: n-octanol/water	log Pow: 9,18 (calculated) Potential bioaccumulation

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

Catalogue No.	820920
Product name	n-Octadecane for synthesis

Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	No information available.
Oxidizing properties	No information available.

9.2 Other data

Ignition temperature	235 °C
----------------------	--------

SECTION 10. Stability and reactivity

10.1 Reactivity

Forms explosive mixtures with air on intense heating.
The following applies in general to flammable organic substances and preparations: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

10.3 Possibility of hazardous reactions

Violent reactions possible with:
Strong oxidizing agents

10.4 Conditions to avoid

Strong heating.
A range from approx. 15 Kelvin below the flash point is to be rated as critical.

10.5 Incompatible materials

no information available

10.6 Hazardous decomposition products

no information available

SECTION 11. Toxicological information

11.1 Information on toxicological effects

Acute oral toxicity

Symptoms: Risk of aspiration upon vomiting., Aspiration may cause pulmonary oedema and pneumonitis.

Acute inhalation toxicity

Symptoms: Pneumonia

Skin irritation

Repeated or prolonged exposure may cause skin irritation and dermatitis, due to degreasing properties of the product.

Specific target organ toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

Catalogue No. 820920
Product name n-Octadecane for synthesis

Specific target organ toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Based on available data the classification criteria are not met.

11.2 Further information

Quantitative data on the toxicity of this product are not available.

Further toxicological data:

After absorption of large quantities:

narcosis

Damage to:

Liver

Other information

It generally applies for aliphatic hydrocarbons with 6 - 18 carbon atoms that they may cause pneumonia, in some cases also pulmonary oedema, upon direct inhalation, i.e. in conditions that can occur only in very special circumstances (nebulizations, spraying, inhalation of aerosols and similar). After absorption of very large quantities: narcosis.

Further data:

However, when the product is handled appropriately, hazardous effects are unlikely to occur.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

12.1 Toxicity

No information available.

12.2 Persistence and degradability

No information available.

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 9,18

(calculated)

Potential bioaccumulation

12.4 Mobility in soil

No information available.

12.5 Results of PBT and vPvB assessment

PBT/vPvB assessment not available as chemical safety assessment not required/not conducted.

12.6 Other adverse effects

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

Waste treatment methods

See www.retrologistik.com for processes regarding the return of chemicals and containers, or contact us there if you have further questions.

SECTION 14. Transport information

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

Catalogue No.	820920
Product name	n-Octadecane for synthesis

Major Accident Hazard	96/82/EC
Legislation	Directive 96/82/EC does not apply

National legislation

Storage class	10
---------------	----

15.2 Chemical Safety Assessment

For this product a chemical safety assessment was not carried out.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Regional representation

This information is given on the authorised Safety Data Sheet for your country.

The information contained herein is based on the present state of our knowledge. It characterises the product with regard to the appropriate safety precautions. It does not represent a guarantee of any properties of the product.