

Datasheet

C2orf3 MaxPab mouse polyclonal antibody (B01)

mistakenly thought to identify a transcription factor gene.
[provided by RefSeq]

Catalog Number: H00006936-B01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human C2orf3 protein.

Immunogen: C2orf3 (AAH00853, 1 a.a. ~ 215 a.a)
full-length human protein.

Sequence:

MAHRPKRTFRQRAADSSDSGAEESPAEPGAPRELP
VPGSAEEEPSPGGGRAQVAGLPHRIRGPRGRGRVWA
SSRRATKAAPRADEGSESRTLVDSTDEEDKIHHSSES
KDDQGLSSDSSSSLGEKELSSTVKIPDAAFIQAARRKR
ELARAQDDYISLDVQHTSSISGMKRESEDDPESEPDD
HEKRIPFTLRPQTLRQRMAEESSMDLPIYED

Host: Mouse

Reactivity: Human

Applications: Det Ab, IF, WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: No additive

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 6936

Gene Symbol: C2orf3

Gene Alias: DNABF, GCF, TCF9

Gene Summary: The first mRNA transcript isolated for this gene was part of an artificial chimera derived from two distinct gene transcripts and a primer used in the cloning process (see Genbank accession M29204). A positively charged amino terminus present only in the chimera was determined to bind GC-rich DNA, thus