



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 02/04/2013

Version 1.0

SECTION 1. Identification

Product identifier

Product number	841811
Product name	Copper(I) cyanide for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Acute toxicity, Category 2, Inhalation, H330
Acute toxicity, Category 1, Dermal, H310
Acute toxicity, Category 2, Oral, H300
Acute aquatic toxicity, Category 1, H400
Chronic aquatic toxicity, Category 1, H410

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

Hazard Statements

H300 + H310 + H330 Fatal if swallowed, in contact with skin or if inhaled.

H410 Very toxic to aquatic life with long lasting effects.

Precautionary Statements

P273 Avoid release to the environment.

P280 Wear protective gloves/ protective clothing.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	CuCN	CCuN (Hill)
CAS-No.	544-92-3	
Molar mass	89.56 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Copper cyanide (>= 90 % - <= 100 %)

544-92-3

SECTION 4. First aid measures

Description of first-aid measures

General advice

General information: Rapid action is called for. First aider needs to protect himself. Immediately call in physician (mentioning hydrocyanic acid poisoning).

Inhalation

After inhalation: fresh air. Call a physician immediately. If breathing stops: immediately apply artificial respiration, if necessary also oxygen.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Call a physician immediately.

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

Ingestion

If swallowed: give water to drink (two glasses at most). Seek medical advice immediately. In exceptional cases only, if medical care is not available within one hour, induce vomiting (only in persons who are wide awake and fully conscious), administer activated charcoal (20 - 40 g in a 10% slurry) and consult a doctor as quickly as possible.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, Cough, Shortness of breath, Unconsciousness, Headache, Convulsions, Vertigo, Impairment of vision, death

The following applies to cyanogen compounds/ nitriles in general: utmost caution! Release of hydrocyanic acid is possible - blockade of cellular respiration. Cardiovascular disorders, dyspnoea, unconsciousness.

Indication of any immediate medical attention and special treatment needed

Keep antidotes ready
dimethylaminophenol
Cobalt-EDTA
sodium thiosulfate

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.
Ambient fire may liberate hazardous vapors.
Fire may cause evolution of:
Hydrogen cyanide (hydrocyanic acid)

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.
Suppress (knock down) gases/vapors/mists with a water spray jet.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Avoid generation and inhalation of dusts in all circumstances. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up carefully. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Work under hood. Do not inhale substance/mixture.

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry. Keep in a well-ventilated place. Keep locked up or in an area accessible only to qualified or authorized persons.

Advice on common storage

Not together with acids.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

841811

Version 1.0

Product name

Copper(I) cyanide for synthesis

SECTION 9. Physical and chemical properties

Physical state	solid
Color	white
Odor	odorless
Odor Threshold	not applicable
pH	No information available.
Melting point	473 °C
Boiling point	No information available.
Flash point	not applicable
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	2.92 g/cm ³
Water solubility	at 68 °F (20 °C) practically insoluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.
Ignition temperature	not applicable
Bulk density	ca. 750 kg/m ³

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

magnesium, Strong oxidizing agents, nitrates, Bases

A risk of explosion and/or of toxic gas formation exists with the following substances:

Acids, Possible formation of:

Hydrogen cyanide (hydrocyanic acid)

Conditions to avoid

Strong heating.

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Acute oral toxicity

LD50 rat: 1,265 mg/kg (RTECS) (Regulation (EC) No 1272/2008, Annex VI)

absorption

Acute inhalation toxicity

Symptoms: mucosal irritations, Cough, Shortness of breath

absorption

Acute dermal toxicity

absorption

Skin irritation

Severe irritations

Eye irritation

Severe irritations

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

After absorption:

Headache, Dizziness, Impairment of vision, Shortness of breath, Unconsciousness, Convulsions, death

Other information

The following applies to cyanogen compounds/ nitriles in general: utmost caution! Release of hydrocyanic acid is possible - blockade of cellular respiration. Cardiovascular disorders, dyspnoea, unconsciousness.

Further data:

This substance should be handled with particular care.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Discharge into the environment must be avoided.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 1587
Proper shipping name	COPPER CYANIDE
Class	6.1
Packing group	II
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 1587
Proper shipping name	COPPER CYANIDE
Class	6.1
Packing group	II
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 1587
Proper shipping name	COPPER CYANIDE
Class	6.1
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-A

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Harmful if swallowed.

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

SARA 313

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

The following components are subject to reporting levels established by SARA Title III, Section 313:

Ingredients

Copper cyanide 544-92-3

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

Massachusetts Right To Know

Ingredients

Copper cyanide

Pennsylvania Right To Know

Ingredients

Copper cyanide

New Jersey Right To Know

Ingredients

Copper cyanide

Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H300	Fatal if swallowed.
H310	Fatal in contact with skin.
H330	Fatal if inhaled.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

MATERIAL SAFETY DATA SHEET
according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 841811
Product name Copper(I) cyanide for synthesis

Version 1.0

Date of issue:02/04/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.