MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013 Version 1.0

SECTION 1. Identification

Product identifier

Product number 811684

Product name Crown ether/18-Crown-6 for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses Chemical for synthesis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)

e-mail: mm_sds@merckgroup.com

Emergency telephone 800-424-9300 CHEMTREC (USA)
+1-703-527-3887 CHEMTREC (International)
24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Acute toxicity, Category 4, Oral, H302

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Warning

Hazard Statements
H302 Harmful if swallowed.

Precautionary Statements
P262 Do not get in eyes, on skin, or on clothing.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	$C_{12}H_{24}O_6$ (Hill)
CAS-No.	17455-13-9
Molar mass	264.32 g/mol

Hazardous ingredients

Chemical Name (Concentration)
CAS-No.
1,4,7,10,13,16-hexaoxacyclooctadecane (>= 90 % - <= 100 %)
17455-13-9

SECTION 4. First aid measures

Description of first-aid measures

Inhalation
After inhalation: fresh air.

Skin contact
After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact
After eye contact: rinse out with plenty of water.

Ingestion
After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Dermatitis, Nausea, Vomiting, CNS disorders

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media
Water, Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media
For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.
Vapors are heavier than air and may spread along floors.
Forms explosive mixtures with air on intense heating.
Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters
In the event of fire, wear self-contained breathing apparatus.

Further information
Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Avoid inhalation of dusts.
Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.
Observe possible material restrictions (see sections 7 and 10).
Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Application of skin- protective barrier cream recommended.
Wash hands after working with substance.

Eye/face protection
Safety glasses

Hand protection
Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:
protective clothing

Respiratory protection
required when dusts are generated.
Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	solid
Color	colorless
Odor	No strong odor known.
Odor Threshold	No information available.
pH	No information available.
Melting point	36 - 39 °C
Boiling point	No information available.
Flash point	228 °F (109 °C)
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	No information available.
Water solubility	soluble

Partition coefficient: n-octanol/water	log Pow: -0.68 (experimental) Bioaccumulation is not expected (log Pow <1). (Lit.)
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.
The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

Strong acids, Strong oxidizing agents

Conditions to avoid

Strong heating.
A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

no information available

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact, Ingestion

Acute oral toxicity
absorption
Symptoms: Nausea, Vomiting

LD50 rat: 525 mg/kg (RTECS)

Acute dermal toxicity
LD50 rabbit: 3,888 mg/kg
(External MSDS)

Skin irritation
Possible damages: Dermatitis

Eye irritation
rabbit
Result: slight irritation
(RTECS)

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information
After absorption:
CNS disorders
In high doses:
Possible damages:
Damage to:
Kidney
Other dangerous properties can not be excluded.
Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability
No information available.

Bioaccumulative potential
Partition coefficient: n-octanol/water
log Pow: -0.68
(experimental)
Bioaccumulation is not expected (log Pow <1). (Lit.)

Mobility in soil
No information available.

Other adverse effects
Additional ecological information
Discharge into the environment must be avoided.

SECTION 13. Disposal considerations
The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information
Land transport (DOT)
Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)
Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)
Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information
United States of America
OSHA Hazards
Harmful if swallowed.

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards
Acute Health Hazard

SARA 313
SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

1,4,7,10,13,16-hexaoxacyclooctadecane

New Jersey Right To Know

Ingredients

1,4,7,10,13,16-hexaoxacyclooctadecane

Notification status

TSCA:	On TSCA Inventory
DSL:	All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H302	Harmful if swallowed.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:03/11/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.