





Pureimage™

The most advanced line of clean paper and documentation available for the most demanding applications.



Critical print

Purus International, Inc.

82860 Avenue 45 • Indio, CA 92201 **760-775-4500** • Fax: 760-775-5575

E-mail: info@purusint.com • www.purusint.com



for critical cleanroom environments





Pure image[™] Cleanroom Paper

For writing, printing and photocopying in cleanroom environments.

Characteristics:

- Dual Binding Technology
- Suitable for use in Class 10 to Class 1000 (ISO class 4 to Class 6) cleanroom.
- Pure image Premier Paper produced in Class 10 (ISO 4) cleanroom.
- Excellent printability and heat toner adhesion.
- Double sided web cleaned prior to sheeting.
- High opacity and durability.

Specifications:	22lb/80 gsm	28 lb/105 gsm
Basis Weight (g/m2)	78 – 83	102 – 107
Caliper (micron) Tear Strength MD/CD	94 – 104 74/75	110 – 120 80/81
Brightness (%)	88 – 92	88 – 92

			V WK Catalog Number		
Size	Weight (*)	Color (**)	Poly Substrate	Latex Substrate	Packaging(***)
8.5" x 11"	22lb	Blue	87003-436	87004-191	250/10/2500, cs
8.5" x 11"	22lb	White	87003-434	87004-188	250/10/2500, cs
8.5" x 11"	22lb	Yellow	82028-072	87004-192	250/10/2500, cs
8.5" x 11"	22lb	Green	87004-164	87004-194	250/10/2500, cs

^{(*) 28}lb and 11"x17" are also availble in select sizes and colors

^(***) Packaging is formatted in Sheets per Ream / Reams per Case / Sheets per Case.



Critical print Cleanroom Notebook

For writing in cleanroom environments.

Characteristics:

- Cleanroom processed and packaged
- Amide and Silicone free
- Dual Binding Technology without any organic fillers
- Completely recyclable
- Custom printing available

Specifications:	22lb/80 gsm
Basis Weight (g/m2)	78 – 83
Caliper (micron)	94 – 104
Tear Strength MD/CD	74/75
Brightness (%)	88 – 92



^(**) Pink, Cream, Orange and Purple are also available in 8.5"x11" paper.