

SAFETY DATA SHEET

1. Identification

Product identifier: SODIUM HYDROXIDE SOLUTION

Other means of identification

Product No.: 5002, 4690, 400D, 3729, H385, 5674, 5672, 5671, 5668, 5661, 0895, 0338, 0312, 5000, 30400

Recommended use and restriction on use

Recommended use: Not available.

Restrictions on use: Not known.

Manufacturer/Importer/Supplier/Distributor information

Manufacturer

Company Name: Avantor Performance Materials, Inc.
Address: 3477 Corporate Parkway, Suite 200
Center Valley, PA 18034

Telephone: Customer Service: 855-282-6867

Fax:
Contact Person: Environmental Health & Safety
e-mail: info@avantormaterials.com

Emergency telephone number:

24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

2. Hazard(s) identification

Hazard classification

Physical hazards

Corrosive to metals Category 1

Health hazards

Skin corrosion/irritation Category 1

Serious eye damage/eye irritation Category 1

Specific target organ toxicity - single exposure Category 3

Environmental hazards

Acute hazards to the aquatic environment Category 3

Label elements

Hazard symbol:



Signal word:

Danger

Hazard statement:	May be corrosive to metals. Causes severe skin burns and eye damage. May cause respiratory irritation. Harmful to aquatic life.
Precautionary statement	
Prevention:	Keep only in original container. Do not breathe dust/mist/vapors. Use only outdoors or in a well-ventilated area. Wear protective gloves/protective clothing/eye protection/face protection. Wash thoroughly after handling. Avoid release to the environment.
Response:	Absorb spillage to prevent material damage. IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Remove/take off immediately all contaminated clothing. Rinse skin with water/shower. Wash contaminated clothing before reuse. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor/physician. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Specific treatment (see this label). Collect spillage.
Storage:	Store in corrosive resistant container with a resistant inner liner. Store in a well-ventilated place. Keep container tightly closed. Store locked up.
Disposal:	Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Other hazards which do not result in GHS classification: None.

3. Composition/information on ingredients

Mixtures

Chemical identity	Common name and synonyms	CAS number	Content in percent (%)*
SODIUM HYDROXIDE		1310-73-2	20 - 40%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

General information:	Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.
Ingestion:	Call a physician or poison control center immediately. Do NOT induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Inhalation:	Move to fresh air. If breathing stops, provide artificial respiration. If breathing is difficult, give oxygen. Call a physician or poison control center immediately.
Skin contact:	Immediately flush with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Call a physician or poison control center immediately. Wash contaminated clothing before reuse. Destroy or thoroughly clean contaminated shoes.

Eye contact: Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Call a physician or poison control center immediately. In case of irritation from airborne exposure, move to fresh air. Get medical attention immediately.

Most important symptoms/effects, acute and delayed

Symptoms: Causes severe skin and eye burns. Causes digestive tract burns. Mist or vapor extremely irritating to eyes and respiratory tract.

Indication of immediate medical attention and special treatment needed

Treatment: Symptoms may be delayed.

5. Fire-fighting measures

General fire hazards: The product is non-combustible. Product is highly caustic. Wear protective gear if spilled during fire fighting.

Suitable (and unsuitable) extinguishing media

Suitable extinguishing media: The product is non-combustible. Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media: None known.

Specific hazards arising from the chemical: Product is highly caustic. Wear appropriate protective gear if spilled during fire fighting. Contact with metals may evolve flammable hydrogen gas.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: Put on protective equipment before entering danger area. See Section 8 of the MSDS for Personal Protective Equipment. Keep unauthorized personnel away. Keep upwind. Ventilate closed spaces before entering them. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.

Methods and material for containment and cleaning up: Neutralize spill area and washings with dilute acetic acid. Absorb spill with vermiculite or other inert material, then place in a container for chemical waste. Collect in a non-combustible container for prompt disposal. Dike far ahead of larger spill for later recovery and disposal.

Notification Procedures: Inform authorities if large amounts are involved.

Environmental precautions: Do not contaminate water sources or sewer. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling: Use personal protective equipment as required. Avoid breathing mists or vapors. Avoid contact with eyes, skin, and clothing. Do not taste or swallow. Wash hands thoroughly after handling. Do not eat, drink or smoke when using the product. See Section 8 of the MSDS for Personal Protective Equipment.

Conditions for safe storage, including any incompatibilities: Do not store in metal containers. Keep container tightly closed. Store in a well-ventilated place. Store in a dry place.

8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Chemical identity	Type	Exposure Limit values	Source
SODIUM HYDROXIDE	Ceiling	2 mg/m3	US. ACGIH Threshold Limit Values (2011)
	Ceil_Time	2 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2010)
	PEL	2 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	Ceiling	2 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)

Appropriate engineering controls No data available.

Individual protection measures, such as personal protective equipment

General information: Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. An eye wash and safety shower must be available in the immediate work area.

Eye/face protection: Wear safety glasses with side shields (or goggles) and a face shield.

Skin protection

Hand protection: Chemical resistant gloves

Other: Wear suitable protective clothing and gloves.

Respiratory protection: In case of inadequate ventilation use suitable respirator.

Hygiene measures: Provide eyewash station and safety shower. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Avoid contact with skin. Do not get in eyes. Wash contaminated clothing before reuse.

9. Physical and chemical properties

Appearance

Physical state: Liquid
Form: Liquid
Color: Colorless
Odor: Odorless

Odor threshold:	No data available.
pH:	14
Melting point/freezing point:	1 °C
Initial boiling point and boiling range:	115 °C
Flash Point:	Not applicable (water-based)
Evaporation rate:	As water
Flammability (solid, gas):	No data available.
Upper/lower limit on flammability or explosive limits	
Flammability limit - upper (%):	
Flammability limit - lower (%):	
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	As water
Vapor density:	As water
Relative density:	1.26 (20 °C)
Solubility(ies)	
Solubility in water:	Miscible with water.
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	No data available.
Auto-ignition temperature:	No data available.
Decomposition temperature:	No data available.
Viscosity:	No data available.

10. Stability and reactivity

Reactivity:	Reacts violently with strong acids.
Chemical stability:	Material is stable under normal conditions.
Possibility of hazardous reactions:	Hazardous polymerization does not occur.
Conditions to avoid:	Avoid contact with oxidizing agents. Reacts violently with strong acids.
Incompatible materials:	Oxidizing agents. Acids. Maleic Anhydride Halogens. Nitromethane. Contact with metals may evolve flammable hydrogen gas.
Hazardous decomposition products:	Sodium oxides

11. Toxicological information

Information on likely routes of exposure

Ingestion:	May cause burns of the gastrointestinal tract if swallowed.
Inhalation:	May cause damage to mucous membranes in nose, throat, lungs and bronchial system.
Skin contact:	Causes severe skin burns.
Eye contact:	Causes serious eye damage.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral Product:	No data available.
----------------------	--------------------

**Dermal
Product:**

No data available.

**Inhalation
Product:**

No data available.

**Repeated dose toxicity
Product:**

No data available.

**Skin corrosion/irritation
Product:**

Causes severe skin burns.

**Serious eye damage/eye irritation
Product:**

Causes serious eye damage.

**Respiratory or skin sensitization
Product:**

Not a skin sensitizer.

**Carcinogenicity
Product:**

This substance has no evidence of carcinogenic properties.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:

No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:

No carcinogenic components identified

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):

No carcinogenic components identified

Germ cell mutagenicity**In vitro****Product:**

No mutagenic components identified

In vivo**Product:**

No mutagenic components identified

Reproductive toxicity**Product:**

No components toxic to reproduction

Specific target organ toxicity - single exposure**Product:**

Respiratory tract irritation.

Specific target organ toxicity - repeated exposure**Product:**

None known.

Aspiration hazard**Product:**

Not classified

Other effects:

None known.

12. Ecological information**Ecotoxicity:****Acute hazards to the aquatic environment:**

Fish

Product: No data available.

Specified substance(s):

SODIUM HYDROXIDE LC 50 (Western mosquitofish (*Gambusia affinis*), 96 h): 125 mg/l Mortality

Aquatic invertebrates

Product: No data available.

Chronic hazards to the aquatic environment:
Fish

Product: No data available.

Aquatic invertebrates

Product: No data available.

Toxicity to Aquatic Plants

Product: No data available.

Persistence and degradability
Biodegradation

Product: Expected to be readily biodegradable.

BOD/COD ratio

Product: No data available.

Bioaccumulative potential
Bioconcentration factor (BCF)

Product: No data available on bioaccumulation.

Partition coefficient n-octanol / water (log Kow)

Product: No data available.

Mobility in soil:

The product is water soluble and may spread in water systems.

Other adverse effects:

Harmful to aquatic organisms. The product may affect the acidity (pH-factor) in water with risk of harmful effects to aquatic organisms.

13. Disposal considerations
Disposal instructions:

Discharge, treatment, or disposal may be subject to national, state, or local laws. Since emptied containers retain product residue, follow label warnings even after container is emptied.

Contaminated packaging:

Since emptied containers retain product residue, follow label warnings even after container is emptied.

14. Transport information
DOT

UN number:	UN 1824
UN proper shipping name:	Sodium hydroxide solution
Transport hazard class(es)	
Class(es):	8
Label(s):	8
Packing group:	II
Marine Pollutant:	No

IMDG

UN number:	UN 1824
UN proper shipping name:	SODIUM HYDROXIDE SOLUTION
Transport hazard class(es)	
Class(es):	8
Label(s):	8
EmS No.:	F-A, S-B
Packing group:	II
Marine Pollutant:	No

IATA

UN number:	UN 1824
Proper Shipping Name:	Sodium hydroxide solution
Transport hazard class(es):	
Class(es):	8
Label(s):	8
Marine Pollutant:	No
Packing group:	II

15. Regulatory information
US federal regulations
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

SODIUM HYDROXIDE Reportable quantity: 1000 lbs.

Superfund amendments and reauthorization act of 1986 (SARA)
Hazard categories

<input checked="" type="checkbox"/> Acute (Immediate)	<input type="checkbox"/> Chronic (Delayed)	<input type="checkbox"/> Fire	<input type="checkbox"/> Reactive	<input type="checkbox"/> Pressure Generating
---	--	-------------------------------	-----------------------------------	--

SARA 302 Extremely hazardous substance

None present or none present in regulated quantities.

SARA 304 Emergency release notification

Chemical identity	RQ
SODIUM HYDROXIDE	1000 lbs.

SARA 311/312 Hazardous chemical

Chemical identity	Threshold Planning Quantity
SODIUM HYDROXIDE	500 lbs

SARA 313 (TRI reporting)

None present or none present in regulated quantities.

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

SODIUM HYDROXIDE Reportable quantity: 1000 lbs.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

None present or none present in regulated quantities.

US state regulations
US. California Proposition 65

No ingredient regulated by CA Prop 65 present.

US. New Jersey Worker and Community Right-to-Know Act

SODIUM HYDROXIDE Listed

US. Massachusetts RTK - Substance List

SODIUM HYDROXIDE Listed

US. Pennsylvania RTK - Hazardous Substances

SODIUM HYDROXIDE Listed

US. Rhode Island RTK

SODIUM HYDROXIDE Listed

Inventory Status:

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	On or in compliance with the inventory
Japan (ENCS) List:	On or in compliance with the inventory
China Inv. Existing Chemical Substances:	Not in compliance with the inventory.
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Japan ISHL Listing:	Not in compliance with the inventory.
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.

16. Other information, including date of preparation or last revision

NFPA Hazard ID



Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe

Issue date: 08-15-2014
Revision date: No data available.
Version #: 1.1
Further information: No data available.

Disclaimer:

THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED "AS IS," AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION<(>,<)> WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.