

# SAFETY DATA SHEET

## 1. Identification

**Product identifier:** HYDROXYLAMINE SULFATE

**Other means of identification**

**Product No.:** N646

**Recommended use and restriction on use**

**Recommended use:** Not available.

**Restrictions on use:** Not known.

**Details of the supplier of the safety data sheet**

### Manufacturer

Company Name: Avantor Performance Materials, Inc.  
Address: 3477 Corporate Parkway, Suite 200  
Center Valley, PA 18034

Telephone: Customer Service: 855-282-6867

Fax:  
Contact Person: Environmental Health & Safety  
E-mail: info@avantormaterials.com

**Emergency telephone number:**

24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

## 2. Hazard(s) identification

### Hazard Classification

#### Physical Hazards

Corrosive to metals Category 1

#### Health Hazards

Acute toxicity (Oral)	Category 4
Acute toxicity (Dermal)	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2A
Skin sensitizer	Category 1
Carcinogenicity	Category 2
Specific Target Organ Toxicity - Repeated Exposure	Category 2

### Label Elements

**Hazard Symbol:**



**Signal Word:** Danger

**Hazard Statement:** Suspected of causing cancer.  
Harmful if swallowed.  
Harmful in contact with skin.  
Causes skin irritation.  
Causes serious eye irritation.  
Causes damage to organs through prolonged or repeated exposure.

**Precautionary Statement**

**Prevention:** Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves/protective clothing/eye protection/face protection. Keep only in original container. Wash hands thoroughly after handling.

**Response:** IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell. Rinse mouth. IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

**Other hazards which do not result in GHS classification:** None.

### 3. Composition/information on ingredients

**Substances**

Chemical Identity	Common name and synonyms	CAS number	Content in percent (%)*
HYDROXYLAMINE SULFATE (2:1) (SALT)		10039-54-0	100%

\* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

### 4. First-aid measures

**General information:** Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.

**Ingestion:** Rinse mouth thoroughly. Call a POISON CENTER or doctor/physician if you feel unwell.

**Inhalation:** Move to fresh air. Get medical attention if symptoms persist.

**Skin Contact:** Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing. Wash contaminated clothing before reuse.

**Eye contact:** Flush thoroughly with water. If irritation occurs, get medical assistance.

**Most important symptoms/effects, acute and delayed**

**Symptoms:** Irritating to eyes, respiratory system and skin.

**Indication of immediate medical attention and special treatment needed**

**Treatment:** Treat symptomatically. Symptoms may be delayed.

### 5. Fire-fighting measures

**General Fire Hazards:** Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool. Cool containers exposed to flames with water until well after the fire is out.

#### Suitable (and unsuitable) extinguishing media

**Suitable extinguishing media:** Use fire-extinguishing media appropriate for surrounding materials.

**Unsuitable extinguishing media:** None known.

**Specific hazards arising from the chemical:** During fire, gases hazardous to health may be formed.

#### Special protective equipment and precautions for firefighters

**Special fire fighting procedures:** In case of fire and/or explosion do not breathe fumes.

**Special protective equipment for fire-fighters:** Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

### 6. Accidental release measures

**Personal precautions, protective equipment and emergency procedures:** Keep unauthorized personnel away. Use personal protective equipment. See Section 8 of the SDS for Personal Protective Equipment.

**Methods and material for containment and cleaning up:** Sweep up and place in a clearly labeled container for chemical waste. Clean surface thoroughly to remove residual contamination.

**Notification Procedures:** Prevent entry into waterways, sewer, basements or confined areas. Inform authorities if large amounts are involved. Avoid release to the environment.

**Environmental Precautions:** Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

### 7. Handling and storage

**Precautions for safe handling:** Use personal protective equipment as required. Avoid inhalation of dust. Wash thoroughly after handling. Avoid contact with eyes. Avoid contact with skin. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe dust/fume/gas/mist/vapors/spray. Wash hands thoroughly after handling. Wear protective gloves/protective clothing/eye protection/face protection. Wash contaminated clothing before reuse.

**Conditions for safe storage, including any incompatibilities:** Store locked up. Store in cool, dry place. Store in a well-ventilated place. Keep only in original container.

### 8. Exposure controls/personal protection

#### Control Parameters

##### Occupational Exposure Limits

None of the components have assigned exposure limits.

**Appropriate Engineering Controls** No data available.

**Individual protection measures, such as personal protective equipment**

**General information:** Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

**Eye/face protection:** Use tight fitting goggles if dust is generated.

**Skin Protection**

**Hand Protection:** Wear protective gloves.

**Other:** Wear suitable protective clothing.

**Respiratory Protection:** In case of inadequate ventilation use suitable respirator.

**Hygiene measures:** Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Provide eyewash station and safety shower.

## 9. Physical and chemical properties

### Appearance

**Physical state:** solid

**Form:** Crystalline Powder.

**Color:** White

**Odor:** No data available.

**Odor threshold:** No data available.

**pH:** No data available.

**Melting point/freezing point:** 170 °C

**Initial boiling point and boiling range:** No data available.

**Flash Point:** not applicable

**Evaporation rate:** No data available.

**Flammability (solid, gas):** No data available.

**Upper/lower limit on flammability or explosive limits**

**Flammability limit - upper (%):** No data available.

**Flammability limit - lower (%):** No data available.

**Explosive limit - upper (%):** No data available.

**Explosive limit - lower (%):** No data available.

**Vapor pressure:** No data available.

**Vapor density:** No data available.

**Relative density:** 1.9 (20 °C)

**Solubility(ies)**

**Solubility in water:** Freely Soluble

**Solubility (other):** No data available.

**Partition coefficient (n-octanol/water):** No data available.

**Auto-ignition temperature:** No data available.

**Decomposition temperature:** No data available.

**Viscosity:** No data available.

## Other information

**Molecular weight:** 164.14 g/mol ( $\text{H}_3\text{NO}_1/2\text{H}_2\text{O}_4\text{S}$ )

## 10. Stability and reactivity

<b>Reactivity:</b>	No dangerous reaction known under conditions of normal use.
<b>Chemical Stability:</b>	Material is stable under normal conditions.
<b>Possibility of Hazardous Reactions:</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid:</b>	Heat, sparks, flames. Contact with incompatible materials.
<b>Incompatible Materials:</b>	Strong oxidizing agents. Bases.
<b>Hazardous Decomposition Products:</b>	Nitrogen Oxides Oxides of Carbon.

## 11. Toxicological information

### Information on likely routes of exposure

<b>Ingestion:</b>	Harmful if swallowed.
<b>Inhalation:</b>	May be harmful if inhaled.
<b>Skin Contact:</b>	Harmful in contact with skin. Causes skin irritation.
<b>Eye contact:</b>	Causes serious eye irritation.

### Information on toxicological effects

#### Acute toxicity (list all possible routes of exposure)

<b>Oral Product:</b>	No data available.
<b>Dermal Product:</b>	No data available.
<b>Inhalation Product:</b>	No data available.
<b>Repeated dose toxicity Product:</b>	No data available.

<b>Skin Corrosion/Irritation Product:</b>	Causes skin irritation.
---	-------------------------

<b>Serious Eye Damage/Eye Irritation Product:</b>	Causes serious eye irritation.
---	--------------------------------

<b>Respiratory or Skin Sensitization Product:</b>	May cause an allergic skin reaction.
---	--------------------------------------

<b>Carcinogenicity Product:</b>	Suspected of causing cancer.
---------------------------------	------------------------------

**IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:**

No carcinogenic components identified

**US. National Toxicology Program (NTP) Report on Carcinogens:**

No carcinogenic components identified

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):**

No carcinogenic components identified

**Germ Cell Mutagenicity****In vitro****Product:** No mutagenic components identified**In vivo****Product:** No mutagenic components identified**Reproductive toxicity****Product:** No components toxic to reproduction**Specific Target Organ Toxicity - Single Exposure****Product:** No data available.**Specific Target Organ Toxicity - Repeated Exposure****Product:** Causes damage to organs through prolonged or repeated exposure.**Aspiration Hazard****Product:** Not classified**Other effects:**

None known.

**12. Ecological information****Ecotoxicity:****Acute hazards to the aquatic environment:****Fish****Product:** No data available.**Aquatic Invertebrates****Product:** No data available.**Chronic hazards to the aquatic environment:****Fish****Product:** No data available.**Aquatic Invertebrates****Product:** No data available.**Toxicity to Aquatic Plants****Product:** No data available.**Persistence and Degradability****Biodegradation****Product:** There are no data on the degradability of this product.**BOD/COD Ratio****Product:** No data available.

## Bioaccumulative Potential

### Bioconcentration Factor (BCF)

**Product:** No data available on bioaccumulation.

### Partition Coefficient n-octanol / water (log Kow)

**Product:** No data available.

**Mobility in Soil:** No data available.

**Other Adverse Effects:** No data on possible environmental effects have been found.

## 13. Disposal considerations

**Disposal instructions:** Discharge, treatment, or disposal may be subject to national, state, or local laws. Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

**Contaminated Packaging:** Since emptied containers retain product residue, follow label warnings even after container is emptied.

## 14. Transport information

### DOT

UN Number: UN 2865  
UN Proper Shipping Name: Hydroxylamine sulfate  
Transport Hazard Class(es)  
Class(es): 8  
Label(s): 8  
Packing Group: III  
Marine Pollutant: Not a Marine Pollutant  
Special precautions for user: –

### IMDG

UN Number: UN 2865  
UN Proper Shipping Name: HYDROXYLAMINE SULPHATE  
Transport Hazard Class(es)  
Class(es): 8  
Label(s): 8  
EmS No.: F-A, S-B  
Packing Group: III  
Marine Pollutant: Not a Marine Pollutant  
Special precautions for user: –

### IATA

UN Number: UN 2865  
Proper Shipping Name: Hydroxylamine sulphate  
Transport Hazard Class(es)  
Class(es): 8  
Label(s): 8  
Marine Pollutant: Not a Marine Pollutant  
Packing Group: III  
Special precautions for user: –

## 15. Regulatory information

### US Federal Regulations

### TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)**

None present or none present in regulated quantities.

**CERCLA Hazardous Substance List (40 CFR 302.4):**

None present or none present in regulated quantities.

**Superfund Amendments and Reauthorization Act of 1986 (SARA)****Hazard categories**

Acute (Immediate)

Chronic (Delayed)

**SARA 302 Extremely Hazardous Substance**

None present or none present in regulated quantities.

**SARA 304 Emergency Release Notification**

None present or none present in regulated quantities.

**SARA 311/312 Hazardous Chemical**

<u>Chemical Identity</u>	<u>Threshold Planning Quantity</u>
HYDROXYLAMINE	10000 lbs
SULFATE (2:1) (SALT)	

**SARA 313 (TRI Reporting)**

None present or none present in regulated quantities.

**Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)**

None present or none present in regulated quantities.

**Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):**

None present or none present in regulated quantities.

**US State Regulations****US. California Proposition 65**

No ingredient regulated by CA Prop 65 present.

**US. New Jersey Worker and Community Right-to-Know Act****Chemical Identity**

HYDROXYLAMINE SULFATE (2:1) (SALT)

**US. Massachusetts RTK - Substance List**

No ingredient regulated by MA Right-to-Know Law present.

**US. Pennsylvania RTK - Hazardous Substances**

No ingredient regulated by PA Right-to-Know Law present.

**US. Rhode Island RTK**

No ingredient regulated by RI Right-to-Know Law present.




**Inventory Status:**

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	On or in compliance with the inventory
Japan (ENCS) List:	On or in compliance with the inventory
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Japan ISHL Listing:	On or in compliance with the inventory
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.

**16. Other information, including date of preparation or last revision**

**NFPA Hazard ID**



Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe; RNP - Rating not possible

<b>Issue Date:</b>	03-25-2015
<b>Revision Date:</b>	No data available.
<b>Version #:</b>	1.0
<b>Further Information:</b>	No data available.

**Disclaimer:**

THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED "AS IS," AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION, WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.