



# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013

Version 1.0

## SECTION 1. Identification

### Product identifier

Product number	104094
Product name	Glycerol 85% for analysis EMSURE® Reag. Ph Eur

### Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis, Chemical production
-----------------	---

### Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation   290 Concord Road, Billerica, MA 01821, United States of America   SDS Phone Support: +1-978-715-1335   General Inquiries: +1-978-715-4321   Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)  e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

## SECTION 2. Hazards identification

### GHS-Labeling

Not a hazardous substance or mixture according to Regulation (EC) No 1272/2008.

### OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

### Other hazards

None known.

## SECTION 3. Composition/information on ingredients

Chemical nature	Aqueous solution
-----------------	------------------

### Hazardous ingredients

Chemical Name ( Concentration)	
CAS-No.	
glycerine ( >= 70 % - < 90 % )	
56-81-5	

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 104094  
Product name Glycerol 85% for analysis EMSURE® Reag. Ph Eur

---

Version 1.0

---

## SECTION 4. First aid measures

### Description of first-aid measures

#### *Inhalation*

After inhalation: fresh air.

#### *Skin contact*

After skin contact: wash off with plenty of water. Remove contaminated clothing.

#### *Eye contact*

After eye contact: rinse out with plenty of water.

#### *Ingestion*

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

### Most important symptoms and effects, both acute and delayed

irritant effects, Cyanosis, gastric pain, Drowsiness, Diarrhea, Vomiting, Headache

### Indication of any immediate medical attention and special treatment needed

No information available.

---

## SECTION 5. Fire-fighting measures

### Extinguishing media

#### *Suitable extinguishing media*

Water, Foam, Carbon dioxide (CO<sub>2</sub>), Dry powder

#### *Unsuitable extinguishing media*

For this substance/mixture no limitations of extinguishing agents are given.

### Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapors possible in the event of fire.

### Advice for firefighters

#### *Special protective equipment for fire-fighters*

In the event of fire, wear self-contained breathing apparatus.

#### *Further information*

Prevent fire extinguishing water from contaminating surface water or the ground water system.

---

## SECTION 6. Accidental release measures

### Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

Protective equipment see section 8.

---

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 104094  
Product name Glycerol 85% for analysis EMSURE® Reag. Ph Eur

Version 1.0

## Environmental precautions

Do not let product enter drains.

## Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® H\*, Merck Art. No. 101595). Dispose of properly. Clean up affected area.

## SECTION 7. Handling and storage

### Precautions for safe handling

Observe label precautions.

### Conditions for safe storage, including any incompatibilities

Tightly closed.

Store at +5°C to +30°C (+41°F to +86°F).

## SECTION 8. Exposure controls/personal protection

### Exposure limit(s)

#### Ingredients

Basis	Value	Threshold limits	Remarks
<i>glycerine 56-81-5</i>			
ACGIH	Time Weighted Average (TWA):	10 mg/m³	Form of exposure: Mist.
OSHA_TRANS	PEL:	15 mg/m³	Form of exposure: Total dust.
	PEL:	5 mg/m³	Form of exposure: Respirable fraction.
Z1A	Time Weighted Average (TWA):	10 mg/m³	Form of exposure: Total dust.
	Time Weighted Average (TWA):	5 mg/m³	Form of exposure: Respirable fraction.

### Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

### Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

### Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

### Eye/face protection

Safety glasses

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 104094  
Product name Glycerol 85% for analysis EMSURE® Reag. Ph Eur

Version 1.0

## *Hand protection*

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

## *Respiratory protection*

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

## SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	odorless
Odor Threshold	No information available.
pH	ca. 5 at 100 g/l 68 °F ( 20 °C)
Melting point	-10 °C
Boiling point/boiling range	> 266 °F ( > 130 °C) at 1,013 hPa
Flash point	ca. 356 °F ( 180 °C) Method: open cup  390 °F ( 199 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	not applicable
Upper explosion limit	not applicable
Vapor pressure	ca. 8 hPa at 68 °F ( 20 °C)
Relative vapor density	No information available.
Relative density	1.23 g/cm <sup>3</sup> at 68 °F ( 20 °C)

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	104094	Version 1.0
Product name	Glycerol 85% for analysis EMSURE® Reag. Ph Eur	

Water solubility	at 68 °F ( 20 °C) soluble
Partition coefficient: n-octanol/water	log Pow: -1.76 (experimental) (calculated on the pure substance) Bioaccumulation is not expected (log Pow <1).
Autoignition temperature	No information available.
Decomposition temperature	> 266 °F ( > 130 °C)
Viscosity, dynamic	ca. 150 mPa.s at 68 °F ( 20 °C)
Explosive properties	No information available.
Ignition temperature	ca. 804 °F ( 429 °C)

### SECTION 10. Stability and reactivity

#### Reactivity

Forms explosive mixtures with air on intense heating.

#### Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

#### Possibility of hazardous reactions

Risk of explosion with:

halogens, Strong oxidizing agents, peroxi compounds, hydrogen peroxide, perchlorates, Nitriles, Nitric acid

with

conc. sulfuric acid

Risk of ignition or formation of inflammable gases or vapors with:

potassium permanganate, halogen oxides, hydrides, chromium(VI) oxide

Exothermic reaction with:

Oxides of phosphorus

#### Conditions to avoid

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Strong heating.

#### Incompatible materials

no information available

#### Hazardous decomposition products

no information available

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

104094

Version 1.0

Product name

Glycerol 85% for analysis EMSURE® Reag. Ph Eur

---

### SECTION 11. Toxicological information

#### Information on toxicological effects

##### *Likely route of exposure*

Inhalation, Eye contact, Skin contact

##### *Target Organs*

Eyes

Skin

Respiratory system

Kidneys

##### *Acute oral toxicity*

Symptoms: Vomiting, Diarrhea

##### *Acute inhalation toxicity*

Symptoms: Irritation symptoms in the respiratory tract.

##### *Specific target organ systemic toxicity - single exposure*

The substance or mixture is not classified as specific target organ toxicant, single exposure.

##### *Specific target organ systemic toxicity - repeated exposure*

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

##### *Aspiration hazard*

Regarding the available data the classification criteria are not fulfilled.

#### Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

#### Further information

Further toxicological data:

After swallowing of large amounts:

gastric pain, Headache, Cyanosis

Further data:

Substances which occur in nature

Handle in accordance with good industrial hygiene and safety practice.

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

104094

Version 1.0

Product name

Glycerol 85% for analysis EMSURE® Reag. Ph Eur

## Ingredients

## SECTION 12. Ecological information

### Ecotoxicity

#### *Toxicity to fish*

LC50 *Carassius auratus* (goldfish): > 5,000 mg/l; 24 h (calculated on the pure substance) (Lit.)

#### *Toxicity to daphnia and other aquatic invertebrates*

EC50 *E.sulcatum*: 3,200 mg/l; 72 h (calculated on the pure substance) (Lit.)

EC50 *Daphnia magna* (Water flea): > 10,000 mg/l; 24 h (calculated on the pure substance) (IUCLID)

#### *Toxicity to algae*

IC50 *Scenedesmus quadricauda* (Green algae): > 10,000 mg/l; 7 d (calculated on the pure substance) (Lit.)

#### *Toxicity to bacteria*

EC50 *Pseudomonas putida*: > 10,000 mg/l; 16 h (calculated on the pure substance) (Lit.)

### Persistence and degradability

#### *Biodegradability*

63 %; 14 d

OECD Test Guideline 301C

(calculated on the pure substance)

Readily biodegradable.

#### *Theoretical oxygen demand (ThOD)*

1,217 mg/g

(calculated on the pure substance) (Lit.)

#### *Ratio BOD/ThBOD*

BOD5 71 %

(calculated on the pure substance)

#### *Ratio COD/ThBOD*

95 %

(calculated on the pure substance), (Lit.)

### Bioaccumulative potential

#### *Partition coefficient: n-octanol/water*

log Pow: -1.76

(experimental)

(calculated on the pure substance) Bioaccumulation is not expected (log Pow <1).

### Mobility in soil

No information available.

### Other adverse effects

#### *Additional ecological information*

No ecological problems are to be expected when the product is handled and used with due care and attention.

## Ingredients

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

104094

Version 1.0

Product name

Glycerol 85% for analysis EMSURE® Reag. Ph Eur

---

---

### SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

---

### SECTION 14. Transport information

#### Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

#### Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

#### Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

---

### SECTION 15. Regulatory information

#### United States of America

##### OSHA Hazards

Target organ effects

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

##### SARA 311/312 Hazards

Chronic Health Hazard

##### SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.



# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

104094

Version 1.0

Product name

Glycerol 85% for analysis EMSURE® Reag. Ph Eur

---

## **SARA 302**

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

## **Clean Water Act**

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

## **DEA List I**

Not listed

## **DEA List II**

Not listed

## **Massachusetts Right To Know**

*Ingredients*

glycerine

## **Pennsylvania Right To Know**

*Ingredients*

glycerine

water

## **New Jersey Right To Know**

*Ingredients*

glycerine

water

## **Notification status**

TSCA:

On TSCA Inventory

DSL:

All components of this product are on the Canadian DSL.

---

## **SECTION 16. Other information**

### **Training advice**

Provide adequate information, instruction and training for operators.

### **Key or legend to abbreviations and acronyms used in the safety data sheet**

Used abbreviations and acronyms can be looked up at [www.wikipedia.org](http://www.wikipedia.org).

Date of issue:03/11/2013

---

MATERIAL SAFETY DATA SHEET  
according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 104094

Version 1.0

Product name Glycerol 85% for analysis EMSURE® Reag. Ph Eur

---

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

*All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.*