

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

**SECTION 1. PRODUCT AND COMPANY IDENTIFICATION**

Product name : Iso-Octane (362)

MSDS Number : 000000011379

Product Use Description : Solvent

Manufacturer or supplier's details : Honeywell International Inc.  
101 Columbia Road  
Morristown, NJ 07962-1057

For more information call : 1-800-368-0050  
+1-231-726-3171  
(Monday-Friday, 9:00am-5:00pm)

In case of emergency call : **Medical: 1-800-498-5701 or +1-303-389-1414**  
: **Transportation (CHEMTREC): 1-800-424-9300 or +1-703-527-3887**  
:  
: (24 hours/day, 7 days/week)

**SECTION 2. HAZARDS IDENTIFICATION****Emergency Overview**

Form : liquid, clear

Color : colourless

Odor : slight hydrocarbon-like

**Classification of the substance or mixture**

Classification of the substance or mixture : Flammable liquids, Category 2  
Skin irritation, Category 2  
Specific target organ toxicity - single exposure, Category 3,  
Central nervous system  
Aspiration hazard, Category 1

## Iso-Octane (362)

000000011379

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

## GHS Label elements, including precautionary statements

Symbol(s)

:



Signal word

: Danger

Hazard statements

: Highly flammable liquid and vapour.  
May be fatal if swallowed and enters airways.  
Causes skin irritation.  
May cause drowsiness and dizziness.

Precautionary statements

: **Prevention:**  
Keep away from heat/sparks/open flames/hot surfaces. - No smoking.  
Keep container tightly closed.  
Ground/bond container and receiving equipment.  
Use explosion-proof electrical/ ventilating/ lighting/ equipment.  
Use only non-sparking tools.  
Take precautionary measures against static discharge.  
Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.  
Wash skin thoroughly after handling.  
Use only outdoors or in a well-ventilated area.  
Wear protective gloves/ eye protection/ face protection.

**Response:**

IF SWALLOWED: Immediately call a POISON CENTER or doctor/ physician.  
IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.  
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.  
Call a POISON CENTER or doctor/ physician if you feel unwell.  
Do NOT induce vomiting.  
If skin irritation occurs: Get medical advice/ attention.  
Take off contaminated clothing and wash before reuse.  
In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

**Storage:**

Store in a well-ventilated place. Keep container tightly closed.

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

Keep cool.  
Store locked up.

**Disposal:**

Dispose of contents/ container to an approved waste disposal plant.

**Carcinogenicity**

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP, IARC, or OSHA.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Formula : C<sub>8</sub>H<sub>18</sub>

Chemical nature : Substance

Chemical Name	CAS-No.	Concentration
2,2,4-Trimethylpentane	540-84-1	100.00 %

**SECTION 4. FIRST AID MEASURES**

Inhalation : Call a physician immediately. Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Use oxygen as required, provided a qualified operator is present.

Skin contact : Wash off immediately with plenty of water for at least 15 minutes. Take off contaminated clothing and shoes immediately. Wash contaminated clothing before re-use. Call a physician.

Eye contact : Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Call a physician.

Ingestion : Do NOT induce vomiting. If a person vomits when lying on his back, place him in the recovery position. Call a physician immediately. Never give anything by mouth to an unconscious

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

person.

**Notes to physician**

Treatment : Treat symptomatically.

**SECTION 5. FIREFIGHTING MEASURES**

Suitable extinguishing media : Foam  
Carbon dioxide (CO<sub>2</sub>)  
Dry chemical  
Cool closed containers exposed to fire with water spray.

Unsuitable extinguishing media : Do not use a solid water stream as it may scatter and spread fire.

Specific hazards during firefighting : Extremely flammable.  
Vapours may form explosive mixtures with air.  
Vapours are heavier than air and may spread along floors.  
Vapors may travel to areas away from work site before igniting/flashback to vapor source.  
In case of fire hazardous decomposition products may be produced such as:  
Carbon monoxide  
Carbon dioxide (CO<sub>2</sub>)

Special protective equipment for firefighters : Wear self-contained breathing apparatus and protective suit.

**SECTION 6. ACCIDENTAL RELEASE MEASURES**

Personal precautions : Wear personal protective equipment. Unprotected persons must be kept away.  
Immediately evacuate personnel to safe areas.  
Keep people away from and upwind of spill/leak.  
Ensure adequate ventilation.  
Remove all sources of ignition.  
Do not swallow.  
Do not breathe vapours or spray mist.  
Avoid contact with skin, eyes and clothing.

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

Environmental precautions : Prevent further leakage or spillage if safe to do so.  
Prevent product from entering drains.  
Discharge into the environment must be avoided.  
Do not flush into surface water or sanitary sewer system.  
Do not allow run-off from fire fighting to enter drains or water courses.

Methods for cleaning up : Ventilate the area.  
No sparking tools should be used.  
Use explosion-proof equipment.  
Contain spillage, soak up with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and transfer to a container for disposal according to local / national regulations (see section 13).

**SECTION 7. HANDLING AND STORAGE****Handling**

Handling : Wear personal protective equipment.  
Use only in well-ventilated areas.  
Keep container tightly closed.  
Do not smoke.  
Do not swallow.  
Do not breathe vapours or spray mist.  
Avoid contact with skin, eyes and clothing.

Advice on protection against fire and explosion : Keep away from fire, sparks and heated surfaces.  
Take precautionary measures against static discharges.  
Ensure all equipment is electrically grounded before beginning transfer operations.  
Use explosion-proof equipment.  
Keep product and empty container away from heat and sources of ignition.  
No sparking tools should be used.  
No smoking.

**Storage**

Requirements for storage areas and containers : Store in area designed for storage of flammable liquids.  
Protect from physical damage.  
Keep containers tightly closed in a dry, cool and well-ventilated

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

place.  
Containers which are opened must be carefully resealed and kept upright to prevent leakage.  
Keep away from heat and sources of ignition.  
Keep away from direct sunlight.  
Store away from incompatible substances.  
Container hazardous when empty.  
Do not pressurize, cut, weld, braze, solder, drill, grind or expose containers to heat or sources of ignition.

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

- |                          |   |  |
|--------------------------|---|--|
| Protective measures      | : | Ensure that eyewash stations and safety showers are close to the workstation location.   |
| Engineering measures     | : | Use with local exhaust ventilation.<br>Prevent vapour buildup by providing adequate ventilation during and after use.  |
| Eye protection           | : | Do not wear contact lenses.<br>Wear as appropriate:<br>Safety glasses with side-shields<br>If splashes are likely to occur, wear:<br>Goggles or face shield, giving complete protection to eyes  |
| Hand protection          | : | Solvent-resistant gloves<br>Gloves must be inspected prior to use.<br>Replace when worn.   |
| Skin and body protection | : | Wear as appropriate:<br>Solvent-resistant apron<br>Flame retardant antistatic protective clothing<br>If splashes are likely to occur, wear:<br>Protective suit   |
| Respiratory protection   | : | When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.<br>For rescue and maintenance work in storage tanks use self-contained breathing apparatus.<br>Use NIOSH approved respiratory protection. |
| Hygiene measures         | : | When using, do not eat, drink or smoke.<br>Wash hands and face before breaks and immediately after   |

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

handling the product.  
Keep working clothes separately.  
Remove and wash contaminated clothing before re-use.  
Do not swallow.  
Do not breathe vapours or spray mist.  
Avoid contact with skin, eyes and clothing.

**Exposure Guidelines**

Components	CAS-No.	Value	Control parameters	Update	Basis
2,2,4-Trimethylpentane	540-84-1	TWA : time weighted average	(300 ppm)	03 2012	ACGIH:US. ACGIH Threshold Limit Values
2,2,4-Trimethylpentane	540-84-1	TWA : time weighted average	(300 ppm)	2008	ACGIH:US. ACGIH Threshold Limit Values
2,2,4-Trimethylpentane	540-84-1	Ceil_Tim e : Ceiling Limit Value and Time Period (if specified) :	1,800 mg/m3 (385 ppm)	2005	NIOSH/GUIDE:US. NIOSH: Pocket Guide to Chemical Hazards
2,2,4-Trimethylpentane	540-84-1	REL : Recomm ended exposure limit (REL):	350 mg/m3 (75 ppm)	2005	NIOSH/GUIDE:US. NIOSH: Pocket Guide to Chemical Hazards
2,2,4-Trimethylpentane	540-84-1	PEL : Permissi ble exposure limit	2,350 mg/m3 (500 ppm)	02 2006	OSHA_TRANS:US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

2,2,4-Trimethylpentane	540-84-1	STEL : Short term exposure limit	1,800 mg/m3 (375 ppm)	1989	Z1A:US. OSHA Table Z-1-A (29 CFR 1910.1000)
------------------------	----------	--	--------------------------	------	---

2,2,4-Trimethylpentane	540-84-1	TWA : time weighted average	1,450 mg/m3 (300 ppm)	1989	Z1A:US. OSHA Table Z-1-A (29 CFR 1910.1000)
------------------------	----------	--------------------------------------	--------------------------	------	---

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

Physical state	: liquid, clear
Color	: colourless
Odor	: slight hydrocarbon-like
pH	: Note: not applicable
Melting point/freezing point	: -107.4 °C
Boiling point/boiling range	: 99.24 °C
Flash point	: 18 °F (-8 °C) Method: closed cup
Lower explosion limit	: 1 %(V)
Upper explosion limit	: 7 %(V)
Vapor pressure	: 54.66 hPa at 20 °C(68 °F)
Vapor density	: 3.9 Note: (Air = 1.0)



**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

Density : 0.69 g/cm<sup>3</sup> at 20 °C

Water solubility : 0.002 g/l at 25 °C

Ignition temperature : 411 °C

Molecular weight : 114.23 g/mol

**SECTION 10. STABILITY AND REACTIVITY**

Chemical stability : Stable under recommended storage conditions.

Possibility of hazardous reactions : Hazardous polymerisation does not occur.

Conditions to avoid : Heat, flames and sparks.  
Keep away from direct sunlight.

Incompatible materials to avoid : Strong oxidizing agents  
Strong acids  
Strong bases  
Reducing agents

Hazardous decomposition products : In case of fire hazardous decomposition products may be produced such as:  
Carbon monoxide  
Carbon dioxide (CO<sub>2</sub>)

**SECTION 11. TOXICOLOGICAL INFORMATION**

Acute oral toxicity : LD<sub>50</sub>: > 5,000 mg/kg

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

	Species: rat Note: No deaths
Acute inhalation toxicity	: LC50: 33.52 mg/l , vapour Exposure time: 4 h Species: rat Method: OECD Test Guideline 403
Acute dermal toxicity	: LD50: > 2,000 mg/kg Species: rabbit Method: OECD Test Guideline 402 Note: No deaths
Skin irritation	: Species: rabbit Result: Irritating to skin.
Eye irritation	: Species: rabbit Result: slight irritation

**SECTION 12. ECOLOGICAL INFORMATION****Further information on ecology**

Additional ecological information	: Bioaccumulation is unlikely. Not inherently biodegradable. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
-----------------------------------	---

**SECTION 13. DISPOSAL CONSIDERATIONS**

Disposal methods	: Observe all Federal, State, and Local Environmental regulations.
------------------	--

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

**SECTION 14. TRANSPORT INFORMATION**

**DOT**      UN/ID No.                               : UN 1262  
              Proper shipping name           : OCTANES  
              Class                                : 3  
              Packing group                   : II  
              Hazard Labels                   : 3

**IATA**      UN/ID No.                               : UN 1262  
              Description of the goods       : OCTANES  
              Class                                : 3  
              Packaging group                : II  
              Hazard Labels                   : 3  
              Packing instruction (cargo aircraft) : 364  
              Packing instruction (passenger aircraft) : 353  
              Packing instruction (passenger aircraft) : Y341

**IMDG**      UN/ID No.                               : UN 1262  
              Description of the goods       : OCTANES  
              Class                                : 3  
              Packaging group                : II  
              Hazard Labels                   : 3  
              EmS Number                     : F-E, S-E  
              Marine pollutant                : no

**SECTION 15. REGULATORY INFORMATION****Inventories**

US. Toxic Substances                       : On TSCA Inventory  
Control Act

Australia. Industrial                       : On the inventory, or in compliance with the inventory  
Chemical (Notification and  
Assessment) Act

Canada. Canadian                           : All components of this product are on the Canadian DSL.  
Environmental Protection

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

Act (CEPA). Domestic  
Substances List (DSL)

Japan. Kashin-Hou Law  
List : On the inventory, or in compliance with the inventory

Korea. Toxic Chemical  
Control Law (TCCL) List : On the inventory, or in compliance with the inventory

Philippines. The Toxic  
Substances and Hazardous  
and Nuclear Waste Control  
Act : On the inventory, or in compliance with the inventory

China. Inventory of Existing  
Chemical Substances : On the inventory, or in compliance with the inventory

New Zealand. Inventory of  
Chemicals (NZIoC), as  
published by ERMA New  
Zealand : On the inventory, or in compliance with the inventory

**National regulatory information**

US. EPA CERCLA  
Hazardous Substances (40  
CFR 302) : The following component(s) of this product is/are subject to  
release reporting under 40 CFR 302 when release exceeds the  
Reportable Quantity (RQ):

Reportable quantity: 1000 lbs  
: 2,2,4-Trimethylpentane 540-84-1

**SARA 302 Components** : SARA 302: No chemicals in this material are subject to the  
reporting requirements of SARA Title III, Section 302.

**SARA 313 Components** : SARA 313: This material does not contain any chemical  
components with known CAS numbers that exceed the  
threshold (De Minimis) reporting levels established by SARA  
Title III, Section 313.

**SARA 311/312 Hazards** : Fire Hazard  
Acute Health Hazard

**CERCLA Reportable  
Quantity** : 1000 lbs

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

**California Prop. 65** : This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

**Massachusetts RTK** : 2,2,4-Trimethylpentane 540-84-1

**New Jersey RTK** : 2,2,4-Trimethylpentane 540-84-1

**Pennsylvania RTK** : 2,2,4-Trimethylpentane 540-84-1

**WHMIS Classification** : B2: Flammable liquid  
D2B: Toxic Material Causing Other Toxic Effects  
This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

**SECTION 16. OTHER INFORMATION**

	<b>HMIS III</b>	<b>NFPA</b>
Health hazard	: 1	1
Flammability	: 3	3
Physical Hazard	: 0	
Instability	:	0

Hazard rating and rating systems (e.g. HMIS® III, NFPA): This information is intended solely for the use of individuals trained in the particular system.

**Further information**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other

**Iso-Octane (362)****000000011379**

Version 1.6

Revision Date 04/24/2014

Print Date 12/04/2014

materials or in any process, unless specified in the text. Final determination of suitability of any material is the sole responsibility of the user. This information should not constitute a guarantee for any specific product properties.

Changes since the last version are highlighted in the margin. This version replaces all previous versions.

Previous Issue Date: 06/18/2012

Prepared by Honeywell Performance Materials and Technologies Product Stewardship Group