

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 01/27/2015

Version 1.5

#### **SECTION 1.Identification**

## **Product identifier**

Product number 109081

Product name Silver nitrate solution c(AgNO₃) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph

Eur, Reag. USP

## Relevant identified uses of the substance or mixture and uses advised against

Identified uses Reagent for analysis

# Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

#### SECTION 2. Hazards identification

## **GHS Classification**

Skin irritation, Category 2, H315 Eye irritation, Category 2A, H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

# **GHS-Labeling**

Hazard pictograms



Signal Word Warning

#### Hazard Statements

H315 Causes skin irritation.

H319 Causes serious eye irritation.

## Precautionary Statements

P264 Wash skin thoroughly after handling.

P280 Wear protective gloves/ eye protection/ face protection.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO₃) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact

lenses, if present and easy to do. Continue rinsing.

P321 Specific treatment (see supplemental first aid instructions on this label).

P332 + P313 If skin irritation occurs: Get medical advice/ attention.

P337 + P313 If eye irritation persists: Get medical advice/ attention.

P362 Take off contaminated clothing and wash before reuse.

#### Other hazards

None known.

#### SECTION 3. Composition/information on ingredients

Chemical nature Aqueous solution

## Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Silver nitrate (>= 1 % - < 5 %)

7761-88-8

Exact percentages are being wihtheld as a trade secret.

#### **SECTION 4. First aid measures**

## Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eve contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a

physician.

Never give anything by mouth to an unconscious person.

#### Most important symptoms and effects, both acute and delayed

Gastrointestinal discomfort

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

The following applies to soluble silver compounds: only slightly absorbed via the gastrointestinal tract. Strong irritations after contact with eyes and skin.

# Indication of any immediate medical attention and special treatment needed

No information available.

## **SECTION 5. Fire-fighting measures**

### Extinguishing media

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO<sub>3</sub>) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

#### Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

### Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

Suppress (knock down) gases/vapors/mists with a water spray jet.

#### SECTION 6. Accidental release measures

# Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

# **Environmental precautions**

Do not empty into drains.

# Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® H\*, Art. No. 101595).

Dispose of properly. Clean up affected area.

#### SECTION 7. Handling and storage

## Precautions for safe handling

Observe label precautions.

## Conditions for safe storage, including any incompatibilities

Tightly closed. Protected from light.

Store at  $+15^{\circ}$ C to  $+25^{\circ}$ C ( $+59^{\circ}$ F to  $+77^{\circ}$ F).

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO<sub>3</sub>) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

# SECTION 8. Exposure controls/personal protection

#### Exposure limit(s)

Ingredients

Basis Value Threshold Remarks

limits

Silver nitrate 7761-88-8

ACGIH Time Weighted Average 0.01 mg/m³ Expressed as: as Ag

(TWA):

NIOSH/GUIDE Recommended 0.01 mg/m³ Expressed as: as Ag

exposure limit (REL):

OSHA\_TRANS PEL: 0.01 mg/m³ Expressed as: as Ag

Z1A Time Weighted Average 0.01 mg/m³ Expressed as: as Ag

(TWA):

#### **Engineering measures**

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

#### Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

#### Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

#### Eye/face protection

Safety glasses

# Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

## Other protective equipment:

protective clothing

#### Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

## SECTION 9. Physical and chemical properties

Physical state liquid

Color colorless

Odor odorless

Odor Threshold Not applicable

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO₃) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

pH ca. 4 - 5

at 68 °F (20 °C)

Melting point No information available.

Boiling point No information available.

Flash point Not applicable

Evaporation rate No information available.

Flammability (solid, gas) Not applicable

Lower explosion limit No information available.

Upper explosion limit No information available.

Vapor pressure No information available.

Relative vapor density No information available.

Density 1.01 g/cm<sup>3</sup>

at 68 °F (20 °C)

Relative density No information available.

Water solubility at 68 °F (20 °C)

soluble

Partition coefficient: n-

octanol/water

No information available.

Autoignition temperature No information available.

Decomposition temperature No information available.

Viscosity, dynamic No information available.

Explosive properties Not classified as explosive.

Oxidizing properties none

# SECTION 10. Stability and reactivity

#### Reactivity

See below

## Chemical stability

Sensitivity to light

# Possibility of hazardous reactions

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO₃) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

Because of low concentration of the dissolved substance(s): none; exception: the generally known reaction partners of water.

#### Conditions to avoid

Exposure to light.

## Incompatible materials

no information available

## Hazardous decomposition products

no information available

# **SECTION 11. Toxicological information**

## Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Target Organs

Mucous membranes

Skin

Eves

Cornea

Nose

Kidney

Lungs

Digestive organs

Gastro-intestinal system

head

Respiratory organs

Acute oral toxicity

Symptoms: Possible damages:, Irritations of mucous membranes in the mouth, pharynx,

oesophagus and gastrointestinal tract., Gastrointestinal discomfort

Acute inhalation toxicity

Symptoms: Possible damages:, mucosal irritations

Skin irritation

Mixture causes skin irritation.

Eve irritation

Mixture causes serious eye irritation.

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

## Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO<sub>3</sub>) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

#### **Further information**

Quantitative data on the toxicity of this product are not available.

Other information

The following applies to soluble silver compounds: only slightly absorbed via the gastrointestinal tract. Strong irritations after contact with eyes and skin.

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

Further data:

Handle in accordance with good industrial hygiene and safety practice.

#### Ingredients

Silver nitrate

Skin irritation In vitro study Result: Corrosive OECD Test Guideline 431

Eye irritation Rabbit

Result: Causes burns. (External MSDS)

Germ cell mutagenicity Genotoxicity in vitro Ames test

Salmonella typhimurium Result: negative (External MSDS)

## **SECTION 12. Ecological information**

# **Ecotoxicity**

No information available.

### Persistence and degradability

No information available.

## Bioaccumulative potential

No information available.

Mobility in soil

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO<sub>3</sub>) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

No information available.

Additional ecological information

Discharge into the environment must be avoided.

### Ingredients

Silver nitrate

Toxicity to fish

NOEC Leuciscus idus (Golden orfe): 0.011 mg/l; 96 h

OECD Test Guideline 203

flow-through test LC50 Pimephales promelas (fathead minnow): 0.0067 mg/l; 96 h

Analytical monitoring: yes

**US-EPA** 

flow-through test NOEC Pimephales promelas (fathead minnow): 0.00037 mg/l; 28 d

OECD Test Guideline 210

Toxicity to daphnia and other aquatic invertebrates

semi-static test LC50 Daphnia magna (Water flea): 0.0069 - 0.0082 mg/l; 48 h

Analytical monitoring: yes OECD Test Guideline 202

Toxicity to algae

IC50 Desmodesmus subspicatus (green algae): 0.008 mg/l; 8 d (External MSDS)

semi-static test Pseudokirchneriella subcapitata (green algae): 0.19 mg/l; 96 h

US-EPA

Toxicity to bacteria

EC10 Pseudomonas putida: 0.006 mg/l; 16 h (External MSDS)

Biodegradability

The methods for determining the biological degradability are not applicable to inorganic substances.

*M-Factor* 100

## **SECTION 13. Disposal considerations**

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

109081 Product number Version 1.5

Silver nitrate solution c(AgNO₃) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag. Product name

**USP** 

# **SECTION 14. Transport information**

Land transport (DOT)

**UN number** UN 1760

Proper shipping name CORROSIVE LIQUID, N.O.S. (SILVER NITRATE)

Class 8 Ш Packing group **Environmentally hazardous** 

Air transport (IATA)

**UN number** UN 1760

Proper shipping name CORROSIVE LIQUID, N.O.S. (SILVER NITRATE

SOLUTION)

Class Ш Packing group **Environmentally hazardous** Special precautions for user no

Sea transport (IMDG)

**UN number** UN 1760

CORROSIVE LIQUID, N.O.S. (SILVER NITRATE Proper shipping name

SOLUTION)

Class Packing group Ш **Environmentally hazardous** Special precautions for user yes

F-A S-B **EmS** 

### **SECTION 15. Regulatory information**

## **United States of America**

#### **SARA 313**

The following components are subject to reporting levels established by SARA Title III, Section 313:

Ingredients

1.7 % Silver nitrate 7761-88-8

### **SARA 302**

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO<sub>3</sub>) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

#### **Clean Water Act**

The following Hazardous Substances are listed under the U.S. CleanWater Act, Section 311, Table 116.4A:

*Ingredients*Silver nitrate

The following Hazardous Chemicals are listed under the U.S. CleanWater Act, Section 311, Table 117.3:

*Ingredients*Silver nitrate

**DEA List I** 

Not listed

DEA List II

Not listed

#### **US State Regulations**

# Massachusetts Right To Know

Ingredients

Silver nitrate

# Pennsylvania Right To Know

*Ingredients*Silver nitrate

## **New Jersey Right To Know**

*Ingredients*Silver nitrate

# California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

### **Notification status**

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

KOREA: Not in compliance with the inventory

# **SECTION 16. Other information**

## Training advice

Provide adequate information, instruction and training for operators.

## Labeling

Hazard pictograms





# according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109081 Version 1.5

Product name Silver nitrate solution c(AgNO<sub>3</sub>) = 0.1 mol/l (0.1 N) Titripur® Reag. Ph Eur,Reag.

**USP** 

Signal Word Warning

Hazard Statements

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H410 Very toxic to aquatic life with long lasting effects.

Precautionary Statements

Prevention

P273 Avoid release to the environment.

Response

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact

lenses, if present and easy to do. Continue rinsing.

P313 Get medical advice/ attention.

## Full text of H-Statements referred to under sections 2 and 3.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

## Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date01/27/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.