SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 05/05/2014 Version 1. 2

SECTION 1.Identification

Product identifier

Product number	102952
Product name	Dimethyl sulfoxide for analysis EMSURE® ACS
Synonyms	Methanesulfinylmethane, Methyl sulfoxide, Dimethyl(oxido)sulfur, DMSO
CAS-No.	67-68-5

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis, Chemical production

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 4, H227

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Signal Word
Warning

Hazard Statements
H227 Combustible liquid.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200). This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS and may deviate from the GHS information.

Other hazards

May accelerate skin absorption of other materials.

SECTION 3. Composition/information on ingredients

Formula	$(CH_3)_2SO$ C_2H_6OS (Hill)
Synonyms	Methanesulfinylmethane, Methyl sulfoxide, Dimethyl(oxido)sulfur, DMSO
Molar mass	78.13 g/mol

Hazardous ingredients

Chemical Name (Concentration)
CAS-No.
dimethyl sulphoxide (>= 90 % - <= 100 %)
67-68-5

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation
After inhalation: fresh air.

Skin contact
After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact
After eye contact: rinse out with plenty of water.

Ingestion
After swallowing: immediately make victim drink water (two glasses at most). Subsequently administer: activated charcoal (20 - 40 g in 10% slurry).

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, CNS disorders, Nausea, Headache, Tiredness

Indication of any immediate medical attention and special treatment needed

Laxative: Sodium sulfate (1 tablespoon/1/4 l water). Get medical attention.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media
Water, Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media
For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.
Vapors are heavier than air and may spread along floors.
Forms explosive mixtures with air on intense heating.
Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:
Sulfur oxides

Advice for firefighters

Special protective equipment for fire-fighters
In the event of fire, wear self-contained breathing apparatus.

Further information
Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures
Change contaminated clothing. Wash hands after working with substance.

Eye/face protection
Safety glasses

Hand protection
Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:
protective clothing

Respiratory protection
required when vapors/aerosols are generated.
Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	characteristic
Odor Threshold	No information available.
pH	No information available.
Melting point	18.5 °C
Boiling point/boiling range	372 °F (189 °C) at 1,013 hPa
Flash point	189 °F (87 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	1.8 %(V)
Upper explosion limit	63.0 %(V)
Vapor pressure	0.6 hPa at 68 °F (20 °C)
Relative vapor density	2.7
Density	1.10 g/cm³ at 68 °F (20 °C)

Relative density	No information available.
Water solubility	1,000 g/l at 68 °F (20 °C)
Partition coefficient: n-octanol/water	log Pow: -1.35 (experimental) (Lit.) Bioaccumulation is not expected.
Autoignition temperature	No information available.
Decomposition temperature	> 374 °F (> 190 °C)
Viscosity, dynamic	2.14 mPa.s at 68 °F (20 °C)
Explosive properties	Not classified as explosive.
Oxidizing properties	none
Ignition temperature	572 - 576 °F (300 - 302 °C)
Saturated vapor concentration	8.0 g/m³ at 68 °F (20 °C)
Viscosity, kinematic	2.14 mm²/s

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.
A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Chemical stability

hygroscopic

Possibility of hazardous reactions

Risk of explosion with:

acetylidene, organic halides, perchlorates, Acid chlorides, nonmetallic halides, iron(III) compounds, nitrates, fluorides, chlorates, hydrides, perchloric acid, Oxides of phosphorus, Nitric acid, silver compounds, silicon compounds, silanes, acid halides

Exothermic reaction with:

boron compounds, oxyhalogenic compounds, Potassium, sodium, Strong oxidizing agents, phosphorus halides, strong reducing agents, Acid chlorides, Strong acids, silver salt, nitrogen dioxide

Risk of ignition or formation of inflammable gases or vapors with:

potassium permanganate

Conditions to avoid

Strong heating.

Incompatible materials
various plastics, Metals

Hazardous decomposition products
in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Inhalation, Eye contact, Skin contact

Target Organs
Skin
Eyes

Acute oral toxicity
LD50 rat: 14,500 mg/kg (RTECS)

Acute dermal toxicity
LD50 rat: 40,000 mg/kg
(RTECS)

Skin irritation
Possible damages: slight irritation

Eye irritation
Possible damages: slight irritation

Sensitization
Sensitization test: guinea pig
Result: negative
(IUCLID)

Genotoxicity in vitro
Ames test
Result: negative
(IUCLID)

Mutagenicity (mammal cell test): chromosome aberration.
Result: negative
(National Toxicology Program)

Carcinogenicity
No indication of carcinogenic activity. (IUCLID)

Teratogenicity
Did not show teratogenic effects in animal experiments. (IUCLID)

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Possible symptoms:
After uptake:
CNS disorders, Nausea, Tiredness, Headache
Possible damages:
Damage to:
Liver, Kidney
However, when the product is handled appropriately, hazardous effects are unlikely to occur.
Handle in accordance with good industrial hygiene and safety practice.
May accelerate skin absorption of other materials.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish
LC50 Oncorhynchus mykiss (rainbow trout): 38,500 mg/l; 96 h (ECOTOX Database)

Toxicity to bacteria
EC10 Pseudomonas putida: 7,100 mg/l; 16 h (IUCLID)

EC50 activated sludge: 10 - 100 mg/l; 30 min (IUCLID)

Persistence and degradability

Biodegradability
3.1 %; 14 d
OECD Test Guideline 301C
Not readily biodegradable.

Bioaccumulative potential

Partition coefficient: n-octanol/water
log Pow: -1.35
(experimental)
(Lit.) Bioaccumulation is not expected.

Mobility in soil

No information available.

Additional ecological information
Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Combustible Liquid
Target organ effects

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard
Chronic Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I
Not listed

DEA List II
Not listed

US State Regulations

Massachusetts Right To Know
Remarks
No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know
Ingredients
dimethyl sulphoxide

New Jersey Right To Know
Ingredients
dimethyl sulphoxide

California Prop 65 Components
This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	All components of the product are listed in the TSCA-inventory.
DSL:	All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice
Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H227	Combustible liquid.

Key or legend to abbreviations and acronyms used in the safety data sheet
Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 05/05/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.