



# HISTOLOGY & CYTOLOGY COLLECTION

*Manufactured by*

**Simport<sup>®</sup>**

*Canadian and Family Owned Since 1975*



# Introducing



**The CoreDish™**  
Multiple Biopsy Containers

**MORE ECO-FRIENDLY** Using up to **75% Less** Formalin and **40% Less** Plastic

**A NEW approach had to be developed to help increase productivity in the laboratory**

**Another Innovation by Simport®**

**Simport CoreDish™**  
PROSTATE BIOPSY ORGANIZER

100% NEUTRAL  
BUFFERED  
FORMALIN 10%  
pH 6.5-7.2 @ 25°C

☐ LEFT SIDE

Patient: \_\_\_\_\_ Date: \_\_\_\_\_

ID #: \_\_\_\_\_ Time: \_\_\_\_\_

Dr.: \_\_\_\_\_

CAUTION: Contains Formaldehyde. Toxic by inhalation and if swallowed; irritating to the eyes, respiratory system and skin. May cause sensitization by inhalation or skin contact. Risk of serious damage to eyes. Gaseous formaldehyde released in biological specimens for fixation. The risk. Made in Canada. Patent Pending.

100% NEUTRAL  
BUFFERED  
FORMALIN 10%  
pH 6.5-7.2 @ 25°C

☐ RIGHT SIDE

Labels on the CoreDish include: L Lateral Base, L Base, Base, Lateral Apex, L Lateral Medium, L Medium, Medium, Lateral Medium, L Lateral Apex, L Apex, Apex, and Lateral Apex.

See pages 34 - 36 for further details



# Table of Contents

Base Molds	20-21
Biopsy Bags	22
Biopsy Foam Pads	22
Biopsy Cassettes	6-19

Cabinets, Cassette	21
Capinsert™	30
Capsules, Tissue	23
Cassettes, Biopsy	6-19
Cassettes, Tissue	6-20
Cassette Cover, Metal	5
Cassettes for printers	.5, 16-19
CoreDish™	34-36
Cytology Funnels	38-43
CytoSep™ Cyto Funnels	38-43

DrainRack™	24-25
Dissecting Boards	26-27

EasyDip™	28
Embedding Rings	23
Embedding Cassettes	5-20

Foam Pads	22
Funnels, Cytology	38-43

Histosette® Cassettes	6-9
HistoTainer™	32-33

Jars, Microscope Slides	28, 30
-------------------------	--------

LockMailer™	30
-------------	----

Macrosette® Cassette	20
Marker Pen	23
Microsette™ Cassettes	10
Micromesh™ Cassettes	12
Microscope Slide Folder	37
Microscope Slide Mailer	30-31
Microscope Slide Storage	24-25, 37
Microscope Slide Tray	37

Paraffin Block Mailer	22
-----------------------	----

QuickLoad™ Cassettes	.5, 16-19
----------------------	-----------

Rings, Embedding	23
------------------	----

SlideFile™	24-25
SlideFolder™	37
SlideTray™	37
Slimsette™ Cassettes	13
Specimen Containers, Formalin Prefilled	32-36
StainTray™	29
Storage Cabinets	21
Swingsette™ Cassettes	14-15

Tissue Capsules	23
Tissue Cassettes	.5-20

UniMailer™	31
Uniset™ Cassettes	11

Write-on™ Marker Pen	23
----------------------	----



# HISTOLOGY & CYTOLOGY COLLECTIONS

## ACCEPT NO IMITATIONS

Thanks to years of experience in precision plastic molding, Simport® offers you the widest choice of Histology Disposables on the market. By choosing Simport®, you will be sure to find a cassette especially suited to fill your specific needs when processing regular tissue samples, single and multiple biopsies and also large specimens. Most models can be used with automated labeling machines. Simport® also manufactures many products to assist you with transportation, storage and staining of microscope slides.

Here is a list of available products:

Biopsy Foam Pads  
Cassettes for Printers  
Cytology Funnels  
Disposable Base Molds  
Dissecting Boards  
Drain Racks  
Embedding Rings  
Microscope Slide Folder  
Microscope Slide Mailers

Microscope Slide Staining Systems  
Microscope Slide Storage Boxes  
Microscope Slide Tray  
Modular Storage Drawers  
Prefilled Specimen Containers  
Tissue Capsules  
Tissue Cassettes with Metal Lid  
Tissue/Biopsy Cassettes with Plastic Lid






## Embedding Cassettes

Made of acetal

Disposable plastic tissue cassettes are suitable for holding and identifying tissue samples in processing, embedding, and sectioning procedures. The cassettes fit securely in microtome chuck adapters. Cassette is totally resistant to the chemical action of histological solvents. These cassettes are designed to accept standard metal lids and will keep specimens in complete safety during processing. The slanted writing surface accepts markings easily, permitting sample identification throughout all stages of embedding and long afterwards when in archives. They are available in 11 colors. Each case contains 3 dispenser boxes of 500 cassettes.



Cat. No.	Color	Qty/Cs	Cat. No.	Color	Qty/Cs
60872-502	White	1500	60872-514	Tan	1500
82028-092	Pink	1500	60872-516	Gray	1500
60872-506	Green	1500	82028-094	Lilac	1500
60872-508	Yellow	1500	82028-096	Orange	1500
60872-510	Blue	1500	82028-098	Aqua	1500
60872-512	Peach	1500			

Cat. No.	Description	Qty/pk
87002-382	Metal Process Cover	25

## Metal Lid for Embedding Cassette



For IVD use



## Cassettes in QuickLoad™ Sleeves and Stacks

Made of acetal

The sleeved cassettes are especially made to be used with ThermoFisher printers. Molded from a special high density acetal polymer, they keep specimens safely submerged and are totally resistant to the chemical action of most solvents used in histology laboratories. The efficient flow-through slots maximize fluid exchange and ensure proper reagent drainage.

### In Sleeves

Cat. No.	Color	Qty/Cs
10033-496	White	750
10033-498	Pink	750
10033-500	Green	750
10033-502	Yellow	750
10033-504	Blue	750
10033-506	Peach	750
10033-508	Tan	750
10033-510	Gray	750
10033-512	Lilac	750
10033-514	Orange	750
10033-516	Aqua	750

For IVD use



Compatible with Thermo  
Fisher cassette printers



# CASSETTES



## HISTOSETTE® I Tissue Processing / Embedding Cassettes

Made of acetal

Disposable plastic cassettes hold tissue specimens during the embedding process, as well as in a storage file. Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. **The efficient flow-through slots maximize fluid exchange and ensure proper drainage.** The one-piece integral lid eliminates the need for separate steel lids. Just snap apart and conveniently lock the lid into the base of the cassette. They can be opened or closed as often as necessary and they always relock securely without danger of specimen loss. Anterior writing area at a 30° angle. Not suitable for automated printers.

Each case contains 3 dispenser boxes of 500 cassettes.

For IVD use

Tissue Cat. No.	Biopsy Cat. No.	Color	Qty/Cs
87002-384	87002-412	White	1500
87002-386	87002-414	Pink	1500
87002-388	87002-416	Green	1500
87002-390	87002-418	Yellow	1500
87002-392	87002-420	Blue	1500
87002-394	87002-422	Peach	1500
87002-396	87002-424	Tan	1500
87002-398	87002-426	Gray	1500
87002-400	87002-428	Lilac	1500
87002-402	87002-430	Orange	1500
87002-404	87002-432	Aqua	1500

## HISTOSETTE® I Biopsy Processing / Embedding Cassettes

Made of acetal


Disposable plastic cassettes similar to Tissue Cassettes series but specially designed to hold biopsy specimens during the embedding process, as well as in a storage file. Anterior writing area at a 30° angle. Not suitable for automated printers.

Each case contains 3 dispenser boxes of 500 cassettes.


For IVD use



### Anatomy of a Histosette® I




Because it has a back mounted locking device, it will never open during processing.





## HISTOSETTE® I

### Tissue & Biopsy Processing / Embedding Cassettes



Made of acetal

These cassettes are identical to previous series but the anterior writing area has a 45° instead of a 30° angle. The more acute angle makes these cassettes more suitable to be used with some models of cassette labeling instruments.

These disposable plastic cassettes hold tissue specimens very efficiently during the embedding process, as well as in a storage file. Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. **The efficient flow-through slots maximize fluid exchange and ensure proper drainage.** The one-piece integral lid eliminates the need for separate steel lids. Just snap apart and conveniently lock the lid into the base of the cassette. They can be opened or closed as often as necessary and they always relock securely without danger of specimen loss. Each case contains 3 dispenser boxes of 500 cassettes.

For IVD use

## HISTOSETTE® I

### Biopsy Processing / Embedding Cassettes

Made of acetal

This model of cassette is similar to Tissue series and is specially designed to hold biopsy specimens during the embedding process.

Each case contains 3 dispenser boxes of 500 cassettes.


For IVD use

Tissue Cat. No.	Biopsy Cat. No.	Color	Qty/Cs
87002-476	87002-538	White	1500
87002-478	87002-540	Pink	1500
87002-480	87002-542	Green	1500
87002-482	87002-544	Yellow	1500
87002-484	87002-546	Blue	1500
87002-486	87002-548	Peach	1500
87002-488	87002-550	Tan	1500
87002-490	87002-552	Gray	1500
87002-492	87002-554	Lilac	1500
87002-494	87002-556	Orange	1500
87002-496	87002-558	Aqua	1500



Compatible with all  
cassette printers

## How to use a Histosette® I



Separate cover by folding it forward and backward.

Identify in front or sides.

Insert sample.

Slide cover in place and lock it.

After processing, remove cover by pulling on back tab.





## HISTOSETTE® II Tissue Processing / Embedding Cassettes

Made of acetal

Disposable plastic cassettes hold tissue specimens during processing and embedding, as well as in storage. Molded from a special high-density polymer, these patented cassettes keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. **The efficient flow-through slots maximize fluid exchange and ensure proper drainage.** The one-piece integral lid eliminates the need for separate steel lids. They can be opened and closed as often as necessary and will always relock securely without danger of specimen loss.

The anterior writing area is slanted at a 45° angle to make the cassette more suitable to be used with certain types of cassette labeling instruments. Available in 11 colors. Each case contains 3 dispenser boxes of 500 cassettes.

For IVD use

Tissue Cat. No.	Biopsy Cat. No.	Color	Qty/Cs
60872-518	60872-540	White	1500
60872-520	60872-542	Pink	1500
60872-522	60872-544	Green	1500
60872-524	60872-546	Yellow	1500
60872-526	60872-548	Blue	1500
60872-528	60872-550	Peach	1500
60872-530	60872-552	Tan	1500
60872-532	60872-554	Gray	1500
60872-534	87002-460	Lilac	1500
60872-536	60872-558	Orange	1500
87002-452	60872-560	Aqua	1500



Compatible with most cassette printers

## HISTOSETTE® II Biopsy Processing / Embedding Cassettes


Made of acetal

Similar to Tissue model but specially designed to hold biopsy specimens during the embedding process, as well as in a storage cabinet. Anterior writing area is at a 45° angle to make the cassette more suitable to be used with certain types of cassette labeling instruments. Each case contains 3 dispenser boxes of 500 cassettes.

For IVD use




### Anatomy of a Histosette® II



Unique front hinge design allows single handed cassette manipulation.

Unobstructed front writing surface sloped at 45° makes the cassette compatible with most automated cassette labeling machines.



Back mounted locking device securely holds the lid in place and will never open during processing.

Efficient flow-through slots in lid and base maximize fluid exchange, thereby ensuring proper drainage.



Patented



## HISTOSETTE® II Tissue Processing / Embedding Cassettes

Made of acetal

Most convenient for cassette labeling instruments since covers are already removed from cassettes and are packaged separately in the case. Disposable plastic cassettes hold tissue specimens during processing and embedding, as well as in storage. Molded from a special high-density polymer, these patented cassettes keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. **The efficient flow-through slots maximize fluid exchange and ensure proper drainage.**

The anterior writing area is slanted at a 45° angle to make the cassette more suitable to be used with certain types of cassette labeling instruments. Available in 11 colors. Each case contains 2 dispenser boxes of 500 cassettes and 1 dispenser box of 1000 covers.

For IVD use CE

Tissue Cat. No.	Biopsy Cat. No.	Color	Qty/Cs
14230-470	87002-346	White	1000
14230-472	87002-348	Pink	1000
14230-474	87002-350	Green	1000
14230-476	87002-352	Yellow	1000
14230-478	87002-354	Blue	1000
14230-480	87002-356	Peach	1000
14230-482	87002-358	Tan	1000
14230-484	87002-360	Gray	1000
14230-486	87002-362	Lilac	1000
14230-488	87002-364	Orange	1000
14230-490	87002-366	Aqua	1000



Cassettes and lids packaged separately



Compatible with all cassette printers



## HISTOSETTE® II Biopsy Processing / Embedding Cassettes


Made of acetal

Most convenient for cassette labeling instruments but specially designed to hold biopsy specimens during the embedding process, as well as in a storage file. The covers are already removed from cassettes and are packaged separately in the case.

Anterior writing area is at a 45° angle to make the cassette more suitable to be used with certain types of cassette labeling instruments. Each case contains 2 dispenser boxes of 500 cassettes and 1 dispenser box of 1000 covers.

For IVD use CE

### How to use a Histosette® II







## MICROSETTE™ I Biopsy Processing / Embedding Cassettes

Made of acetal

Biopsy pads are no longer necessary with these innovative disposable plastic biopsy cassettes with a large compartment measuring 25 x 30 mm. Perfect even with needle biopsies since mesh holes have a diameter of only 0.26 mm while still allowing for maximum fluid exchange and drainage. Molded from a special high density polymer, these patented cassettes keep specimens safely submerged in liquid and are resistant to most histological solvents. They can be opened and closed as often as necessary and they always relock securely without danger of specimen loss. Available in 11 colors. Anterior writing area is at a 45° angle to make the cassette more suitable, to be used with certain types of cassette labeling instruments.

Each case contains four dispenser boxes of 250 cassettes with covers assembled.

For IVD use




Compatible with most  
cassette printers

### Anatomy of a Microsette™ I

Cover and base have over 2000, 0.26 mm square openings to maximize fluid exchange and ensure proper drainage.


Excellent fluid exchange through slots.



Back mounted locking device securely holds the lid in place and will never open during processing.

No biopsy pads necessary.

Air vents allowing more efficient filling with paraffin.



Biopsy Cassette  
with one  
compartment

Biopsy Cassette  
with six  
compartments

Cat. No.	Cat. No.	Color	Qty/Pk	Qty/Cs
87002-504	14230-492	White	250	1000
87002-506	14230-494	Pink	250	1000
87002-508	14230-496	Green	250	1000
87002-510	14230-498	Yellow	250	1000
87002-512	14230-500	Blue	250	1000
87002-514	14230-502	Peach	250	1000
87002-516	14230-504	Tan	250	1000
87002-518	14230-506	Gray	250	1000
87002-520	14230-508	Lilac	250	1000
87002-522	14230-510	Orange	250	1000
87002-524	14230-512	Aqua	250	1000

## MICROSETTE™ I Biopsy Processing / Embedding Cassettes

Made of acetal

This model can hold up to six tissue specimens, each one placed in its own 7 x 12 mm (1/4 x 7/16 in.) compartment, numbered from 1 to 6.

No biopsy pads necessary. Cover and base have over 2000 square openings to maximize fluid exchange and ensure proper drainage. Approximately 170 holes (each having a diameter of 0.26 mm) per compartment.

Each case contains four dispenser boxes of 250 cassettes with covers assembled.

For IVD use





## UNISETTE™

### Biopsy & Tissue Processing / Embedding Cassettes

Made of acetal



Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are resistant to the chemical action of most histological solvents. The efficient flow-through slots maximize fluid exchange and ensure proper drainage. The one-piece integral lid eliminates the need for separate steel lids. The snap-latch and hinge-lock design of the UNISETTE™ prevent early separation of base and lid and allow for one-hand operation. Lids can be opened and closed as often as necessary and they always relock securely without danger of specimen loss. Anterior writing area is at a 35° angle.

Available in 11 colors. Each case contains 3 dispenser boxes of 500 cassettes.


For IVD use

Tissue Cat. No.	Biopsy Cat. No.	Color	Qty/Cs
87002-290	87002-318	White	1500
87002-292	87002-320	Pink	1500
87002-294	87002-322	Green	1500
87002-296	87002-324	Yellow	1500
87002-298	87002-326	Blue	1500
87002-300	87002-328	Peach	1500
87002-302	87002-330	Tan	1500
87002-304	87002-332	Gray	1500
87002-306	87002-334	Lilac	1500
87002-308	87002-336	Orange	1500
87002-310	87002-338	Aqua	1500




Compatible with Leica and  
Sakura cassette printers


## How to use a UNISETTE™




The cover of the Unisetite is attached to the back of the base in an open position.



To close, simply tilt cover forward, holding it by the front tab.



Push cover down until a click is heard.



To open, tilt cover backward. It will remain attached to the base and can be closed again.





## MICROMESH™ Biopsy Processing / Embedding Cassettes

Made of acetal

This version of the Micromesh™ offers 1676 square openings (0.38 mm) allowing for a greatly improved fluid exchange and drainage without having to use biopsy pads. Large anterior slots in both cassette and cover ensure that the Micromesh™ biopsy cassette will sink rapidly. A large square compartment measuring 27 mm is perfect even for needle biopsies. The cover does not protrude above the cassette, a great space saving feature allowing more cassettes to be stacked in automatic labeling machines and tissue processors.

Molded from a special high density polymer, these patented cassettes keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. They can be opened and closed as often as necessary and they always relock securely without danger of specimen loss. Anterior writing area is at a 45° angle to make the cassette more suitable to be used with automated cassette printers. Available in 11 colors.


Each case contains four dispenser boxes of 250 cassettes with covers assembled.

**NO BIOPSY PADS REQUIRED**

For IVD use

Biopsy Cassette with one compartment	Biopsy Cassette with four compartments		
Cat. No.	Cat. No.	Color	Qty/Cs
87002-566	97000-390	White	1000
87002-568	97000-392	Pink	1000
87002-570	97000-394	Green	1000
87002-572	97000-396	Yellow	1000
87002-574	97000-398	Blue	1000
87002-576	97000-400	Peach	1000
87002-578	97000-402	Tan	1000
87002-580	97000-404	Gray	1000
87002-582	97000-406	Lilac	1000
87002-584	97000-408	Orange	1000
87002-586	97000-410	Aqua	1000

## Anatomy of Micromesh™ Cassettes



## MICROMESH™ Biopsy Processing / Embedding Cassettes

Made of acetal


This model is similar to the one above but cassettes have four square compartments each measuring 13 mm. Cover and base have about 1676 square openings maximizing fluid exchange and ensuring proper drainage.

Each case contains four dispenser boxes of 250 cassettes with covers assembled.

For IVD use



Compatible with all  
cassette printers





## SLIMSETTE™ Tissue Processing / Embedding Cassettes

Made of acetal

The SLIMSETTE™, a new generation emerging in the Simport® Histology Family. More compact, easier to use and more efficient than ever. Similar to the design of the Micromesh model, it incorporates a unique recessed cover, a great space saving feature allowing more cassettes to be stacked in automatic labeling machines and in storage cabinets.

Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are resistant to the chemical action of histological solvents. The SLIMSETTE™ ensures efficient fluid exchange and drainage thanks to 114 openings each measuring 1 x 5 mm. They can be opened and closed as often as necessary and they always relock securely without danger of specimen loss. Large labeling areas for easy identification. The anterior writing area is slanted at a 45° angle. Available in 11 colors.

Each case contains 3 dispenser boxes of 500 cassettes with covers assembled. Patent pending. Dimensions: 41 x 28.5 x 6 mm H (1 5/8 x 1 1/8 x 1/4 in. H)



For IVD use CE

Compatible with all cassette printers




## SLIMSETTE™ Biopsy Processing / Embedding Cassettes



Made of acetal

Similar to model above but specially designed to hold biopsy specimens during the embedding process, as well as in a storage cabinet. Anterior writing area is at a 45° angle to make the cassette more suitable to be used with certain types of cassette labeling instruments. This biopsy model ensures efficient fluid exchange and drainage thanks to 392 openings

For IVD use CE



Tissue Cassette with one compartment	Biopsy Cassette with one compartment	Tissue Cassette with four compartments		
Cat. No.	Cat. No.	Cat. No.	Color	Qty/Cs
82028-744	82028-772	97000-418	White	1500
82028-746	82028-774	97000-420	Pink	1500
82028-748	82028-776	97000-422	Green	1500
82028-750	82028-778	97000-424	Yellow	1500
82028-752	82028-780	97000-426	Blue	1500
82028-754	82028-782	97000-428	Peach	1500
82028-756	82028-784	97000-430	Tan	1500
82028-758	82028-786	97000-432	Gray	1500
82028-760	82028-788	97000-434	Lilac	1500
82028-762	82028-790	97000-436	Orange	1500
82028-764	82028-792	97000-438	Aqua	1500

## SLIMSETTE™ Tissue Processing / Embedding Cassettes

Made of acetal

This model is similar to Tissue model but cassettes have four square compartments each measuring 13 mm. Cover and base have openings maximizing fluid exchange and ensuring proper drainage. Each case contains 3 dispenser boxes of 500 cassettes with covers assembled.





## SWINGSETTE™ Tissue Processing / Embedding Cassettes

Made of acetal

These disposable plastic cassettes hold tissue specimens during processing and embedding, as well as in storage. Molded from a special high-density polymer, they keep specimens safely submerged in liquid and are resistant to the chemical action of histological solvents. The efficient flow-through slots maximize fluid exchange and ensure proper drainage.


This new model differs by the special hinge holding the base and cover together. This hinge allows cassettes to be opened and closed as often as necessary. The cover can be removed and re-inserted easily without danger of specimen loss.

Available in 11 colors.

Each case contains 3 dispenser boxes of 500 cassettes.

For IVD use

### Anatomy of a Swingsette™



Tissue Cat. No.	Biopsy Cat. No.	Color	Qty/Cs
97000-446	97000-474	White	1500
97000-448	97000-476	Pink	1500
97000-450	97000-478	Green	1500
97000-452	97000-480	Yellow	1500
97000-454	97000-482	Blue	1500
97000-456	97000-484	Peach	1500
97000-458	97000-486	Tan	1500
97000-460	97000-488	Gray	1500
97000-462	97000-490	Lilac	1500
97000-464	97000-492	Orange	1500
97000-466	97000-494	Aqua	1500

## SWINGSETTE™ Biopsy Processing / Embedding Cassettes

Made of acetal

These biopsy cassettes are similar but especially designed to hold biopsy specimens during the processing / embedding process as well as in storage cabinets.

Each case contains three dispenser boxes of 500 cassettes.

For IVD use





## SWINGSETTE™ Tissue Processing / Embedding Cassettes

Made of acetal

Most convenient for cassette labeling instruments since the covers are packaged separately in the case. These disposable plastic cassettes hold tissue specimens during processing and embedding, as well as in storage. Molded from a special high-density polymer, they keep specimens safely submerged in liquid and are resistant to the chemical action of histological solvents. The efficient flow-through slots maximize fluid exchange and ensure proper drainage.

This model differs by the special hinge that holds the base and cover together. This hinge allows cassettes to be opened and closed as often as necessary. The cover can be removed and re-inserted easily without danger of specimen loss. Available in 11 colors.


Each case contains two dispenser boxes of 500 cassettes and one dispenser box of 1000 covers.

For IVD use CE

Tissue Cat. No.	Biopsy Cat. No.	Color	Qty/Cs
97000-502	97000-530	White	1000
97000-504	97000-532	Pink	1000
97000-506	97000-534	Green	1000
97000-508	97000-536	Yellow	1000
97000-510	97000-538	Blue	1000
97000-512	97000-540	Peach	1000
97000-514	97000-542	Tan	1000
97000-516	97000-544	Gray	1000
97000-518	97000-546	Lilac	1000
97000-520	97000-548	Orange	1000
97000-522	97000-550	Aqua	1000



Cassettes and lids packaged separately



## SWINGSETTE™ Biopsy Processing / Embedding Cassettes

Made of acetal

Most convenient for cassette labeling instruments since the covers are packaged separately in the case. These biopsy cassettes are similar to the tissue series but are especially designed to hold biopsy specimens during the processing/embedding process as well as in storage cabinets.

Each case contains two dispenser boxes of 500 cassettes and one box of 1000 covers.

For IVD use CE

### Close-up of the hinge




Cassettes on page 14  
The cover is connected to the base.

Cassettes on this page  
The special hinge makes it easy to attach lid to base.



# CASSETTES IN SLEEVES

## HISTOSETTE® II Cassettes in E-Z Load™ Stacks



Made of acetal

This stack of cassettes allows you to load the Shur/Mark® Cassette Labeling Instruments in one simple operation. Save time and money with these convenient stacks of 50 unique Simport® cassettes. No more manual insertion, one cassette at a time. Just load the stack in the hopper, cut and remove the holding tie and you are ready for printing.

These specially designed cassettes belong to the world-wide known Simport® Histosette® II design. Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. The efficient flow-through slots maximize fluid exchange and ensure proper drainage.

Two types of cassettes are offered in order to suit your particular needs: a regular tissue cassette and a biopsy model designed to hold small biopsy samples securely during the embedding process. Anterior printing area is at a 45° angle.

### TISSUE CASSETTES (In stacks of 50)

Base Cat. No.	Cover Cat. No.	Color	Qty/Cs
14236-432	14236-454	White	2000
14236-434	14236-456	Pink	2000
14236-436	14236-458	Green	2000
14236-438	14236-460	Yellow	2000
14236-440	14236-462	Blue	2000
14236-442	14236-464	Peach	2000
14236-444	14236-466	Tan	2000
14236-446	14236-468	Gray	2000
14236-448	14236-470	Lilac	2000
14236-450	14236-472	Orange	2000
14236-452	14236-474	Aqua	2000

### BIOPSY CASSETTES (In stacks of 50)

Base Cat. No.	Cover Cat. No.	Color	Qty/Cs
14236-476	14236-498	White	2000
14236-478	14236-500	Pink	2000
14236-480	14236-502	Green	2000
14236-482	14236-504	Yellow	2000
14236-484	14236-506	Blue	2000
14236-486	14236-508	Peach	2000
14236-488	14236-510	Tan	2000
14236-490	14236-512	Gray	2000
14236-492	14236-514	Lilac	2000
14236-494	14236-516	Orange	2000
14236-496	14236-518	Aqua	2000

For IVD use




CASSETTE BASES AND LIDS  
ARE ORDERED SEPARATELY.



These cassettes can be used in this automatic labeling instrument.



## MICROMESH™ Biopsy Cassettes in QuickLoad™ Sleeves



Made of acetal

Suitable for hoppers accepting plastic sleeves, these cassettes will load in cassette labeling instruments in one simple operation. Just load the 75-cassette QuickLoad™ sleeve in the hopper and you are ready for printing.

The Micromesh™ offers 0.38 mm square openings, and large anterior slots allowing for increased fluid exchange and faster sinking in liquids. No biopsy pads are necessary. These cassettes feature a recessed cover and a large square 27 mm compartment, perfect even for needle biopsies.


Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are resistant to the chemical action of histological solvents. The lid can be opened and closed as often as necessary and always relocks securely without danger of specimen loss. Anterior writing area is at a 45° angle to make the cassette more suitable to be used with automated cassette printers. Available in 11 colors. Each case contains 10 sleeves.

For IVD use

Cat. No.	Color	Qty/Cs
10057-822	White	750
10057-834	Pink	750
10057-836	Green	750
10057-838	Yellow	750
10057-840	Blue	750
10057-842	Peach	750
10057-844	Tan	750
10057-846	Gray	750
10057-848	Lilac	750
10057-850	Orange	750
10057-852	Aqua	750

**NO BIOPSY PADS REQUIRED**


Lids are pre-mounted  
on cassettes



Compatible with  
ThermoFisher  
cassette printers

## Anatomy of a Micromesh™

A recessed cover is a great space saving feature, allowing more cassettes to be stacked in automatic labeling machines and storage drawers



Large anterior slots in both cassette and cover ensure that the Micromesh™ biopsy cassette will be submerged rapidly



Base and cover together have 1676 square openings (0.38 mm) allowing for a greatly improved fluid exchange



# CASSETTES IN SLEEVES



## SLIMSETTE™ Tissue Cassettes in QuickLoad™ Sleeves

Made of acetal

The transparent sleeve allows viewing of cassettes in order to confirm there is no jam in the sleeve during the printing process.

This model is similar to the Micromesh™ cassette but is intended for tissue processing/embedding procedures. The efficient flow-through slots maximize fluid exchange and ensure proper drainage. Lids can be opened and closed as often as necessary and they always relock securely without danger of specimen loss. When ready for the embedding process, covers can conveniently be snapped off and discarded.

Anterior writing area at a 45° angle. Available in 11 colors. Each case contains 10 sleeves of 75 cassettes.

For IVD use



Compatible with  
ThermoFisher  
cassette printers

Lid already installed  
on cassette base

Tissue Cassette Cat. No.	Biopsy Cassette Cat. No.	Color	Qty/Cs
95030-230	95030-258	White	750
95030-232	95030-260	Pink	750
95030-234	95030-262	Green	750
95030-236	95030-264	Yellow	750
95030-238	95030-266	Blue	750
95030-240	95030-268	Peach	750
95030-242	95030-270	Tan	750
95030-244	95030-272	Gray	750
95030-246	95030-274	Lilac	750
95030-248	95030-276	Orange	750
95030-250	95030-278	Aqua	750

## SLIMSETTE™ Biopsy Cassettes in QuickLoad™ Sleeves


Made of acetal

Suitable for hoppers accepting plastic sleeves, these biopsy cassettes will load in cassette labeling instruments in one simple operation. Just load the 75-cassette QuickLoad™ sleeve in the hopper and you are ready for printing.

Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. The lid can be opened and closed as often as necessary and always relocks securely without danger of specimen loss. Anterior writing area is at a 45° angle to make the cassette more suitable to be used with automated cassette printers. Available in 11 colors.

Cassettes are packaged in sleeves of 75. Each case contains 10 sleeves.

For IVD use





## SWINGSETTE™ Tissue Cassettes in QuickLoad™ Sleeves

Made of acetal


Suitable for hoppers accepting plastic sleeves, these tissue cassettes will load in cassette labeling instruments in one simple operation. Just load the 75-cassette QuickLoad™ sleeve in the hopper and you are ready for printing.

Molded from a special high density polymer, these cassettes keep specimens safely submerged in liquid and are resistant to the chemical action of histological solvents. The lid can be opened and closed as often as necessary and always relocks securely without danger of specimen loss. Anterior writing area is at a 45° angle to make the cassette more suitable to be used with automated cassette printers. Available in 11 colors.

Each case contains 10 sleeves of 75 cassettes and 10 bags of 75 lids.

For IVD use 

Tissue Cassette Cat. No.	Biopsy Cassette Cat. No.	Color	Qty/Cs
95030-286	95030-314	White	750
95030-288	95030-316	Pink	750
95030-290	95030-318	Green	750
95030-292	95030-320	Yellow	750
95030-294	95030-322	Blue	750
95030-296	95030-324	Peach	750
95030-298	95030-326	Tan	750
95030-300	95030-328	Gray	750
95030-302	95030-330	Lilac	750
95030-304	95030-332	Orange	750
95030-306	95030-334	Aqua	750



## SWINGSETTE™ Biopsy Cassettes in QuickLoad™ Sleeves

Made of acetal

These disposable plastic cassettes hold biopsy specimens during processing and embedding, as well as in storage. Molded from a special high-density polymer, they keep specimens safely submerged in liquid and are totally resistant to the chemical action of histological solvents. The efficient flow-through slots maximize fluid exchange and ensure proper drainage.

This new model differs by the special hinge holding the base and cover together. This hinge allows cassettes to be opened and closed as often as necessary. The cover can be removed and re-inserted easily without danger of specimen loss. Available in 11 colors.

Each case contains 10 sleeves of 75 cassettes and 10 bags of 75 lids.

For IVD use 



## MACROSETTE®

### Processing / Embedding Cassettes (with lid)

Made of acetal

Disposable plastic cassettes designed to hold larger tissue specimens during the embedding process, as well as in a storage cabinet. Dimensions are exactly the same as the ones of a regular HISTOSETTE® cassette but the MACROSETTE® is twice as high (13 mm).

The one-piece integral lid eliminates the need for separate steel lids. It can be opened and closed as often as necessary and will always relock securely without danger of specimen loss. Large labeling areas are located on three sides of the cassettes for your convenience. Each case contains three dispenser boxes of 250 cassettes.

Dimensions: 40.1 x 28.5 x 13 mm H (1<sup>9</sup>/<sub>16</sub> x 1<sup>1</sup>/<sub>8</sub> x 1/2 in. H)



Cat. No.	Color	Qty/Cs
87002-472	White	750

For IVD use

## Disposable Deep Base Mold



Made of PVC

Designed especially for the MACROSETTE®. Thanks to the specially formulated plastic material, it offers excellent thermal exchange. It has a smooth interior finish and rounded corners facilitating specimen removal.

Cat. No.	Size (mm)	Vol	Qty/Cs
87002-474	37 x 24 x 10	5 ml	500

## JUMBOSETTE®

### Processing / Embedding Cassettes (with lid)

Made of acetal

The JUMBOSETTE™ is suitable for extra large tissue samples such as eyes, animal organs etc, thanks to its larger size. Will ensure efficient fluid exchange during the processing cycle. When utilised with a specially designed Base Mold, the cassette becomes the supporting structure of the paraffin block. A clamp adapter is available in order to support the JUMBOSETTE™. Dimensions: 3" x 2" x 3/4" (75 x 52 x 18 mm).

For IVD use



Cat. No.	Color	Qty/Cs
10058-996	White	100

## Reusable Base Mold for the JUMBOSETTE®

Made of Stainless Steel

This mold is suited for all applications in specimen embedding with the JUMBOSETTE™. Manufactured from high-quality stainless steel for optimal thermal conductivity, the mold has a highly polished surface for easy paraffin block removal. Reusable. Stackable for easy storage.



Cat. No.	Size (mm)	Qty/Pk
10058-998	66 x 45 x 15	10





## Modular Storage Drawer

Made of high impact polystyrene

This drawer provides permanent storage & identification of up to 165 embedding rings or 250 cassettes per drawer. It is stackable to any convenient height, thanks to interlocking ridges on top and bottom. Made of high impact resistant plastic. Identification labels included.

Cat. No.	Dimensions	Qty/Cs
60872-562	40.5 cm x 23 cm x 5.1 cm H (15 7/8 x 9 1/8 x 2 1/8 in. H)	6



## Storage Drawer

Made of durable, waterproof, heavy-duty cardboard for long term storage. Requires minimal space. Label and cardboard separators are provided for each box allows recording of specimen number, date and type of specimen. Each box can store up to 165 embedding rings or 250 cassettes. Dimensions: 40.5 cm x 23 cm x 5.1 cm H (15 7/8 x 9 1/8 x 2 1/8 in. H)

Cat. No.	Material	Qty/Cs
87002-598	Heavy-duty cardboard	12

## Base Molds



Made of Stainless Steel

Sizes fit most cassettes. Superior thermal exchange. These molds are for all applications in specimen embedding with all styles of Embedding Rings and Cassettes. Manufactured from high-quality stainless steel for optimal thermal conductivity, the molds have a highly polished surface for easy paraffin block removal. Well corners are rounded for optimal paraffin ribboning.


Cat. No.	Size (mm)	Qty/Pk
89498-708	7 x 7 x 5	12
89498-710	15 x 15 x 5	12
89498-712	24 x 24 x 5	12
89498-714	30 x 24 x 5	12
89498-716	37 x 24 x 5	12

## Disposable Base Molds

Made of PVC

Simport® disposable base molds offer ease and convenience of operation. They are inexpensive enough to be discarded after use, yet strong enough to be reused. Thanks to the specially formulated plastic material, they offer excellent thermal exchange. They have a smooth interior finish and rounded corners facilitating specimen removal. Also, they are available in the same variety of sizes as metal molds and can be used with the same styles or types of cassettes and embedding rings. Each case contains two dispenser boxes of 500 base molds.

Cat. No.	Size (mm)	Qty/Cs
60872-486	7 x 7 x 5	1000
60872-488	15 x 15 x 5	1000
60872-490	24 x 24 x 5	1000
60872-498	30 x 24 x 5	1000
60872-500	37 x 24 x 5	1000





## Biopsy Foam Pads

Made of polyester urethane foam

Simport® biopsy foam pads are used to hold biopsies in place and prevent them from being lost during processing. They are made of a specially formulated foam which is always verified for consistency throughout in order to achieve optimum solvent flow. Biopsy samples are sandwiched between two foam pads and are placed either in tissue capsules or cassettes\* with metal or plastic lids. 95039-818 model is to be used with the Micromesh™ and Slimsette™ Cassettes. 89495-246 is specially suited for the Histosette® II. Will resist temperatures from -40 °C to 121 °C.

Cat. No.	For use with	Size (mm)	Qty/Pk	Qty/Cs
60872-492	Cassettes	30.2 x 25.4 x 2	1000	10 000
60872-494	Small capsules	25.4 x 2.7	1000	10 000
60872-496	Large capsules	34.6 x 2	1000	10 000
95039-818	Slimsette	27.4 x 25.4 x 2	1000	10 000
89495-246	Histosette® II	30.2 x 25.4 x 2	1000	10 000



89495-246 is specially suited for the Histosette® II Cassettes on page 8 & 9.

## Biopsy Bags

Made of nylon

These sturdy biopsy bags are made of white nylon thin mesh (0.3 mm diameter), reducing the risk of specimen loss during processing. While solvent resistant, they provide great tissue safety and excellent fluid exchange. In order to ease specimen removal, bags can be peeled open. All seams are heat-sealed. Available in three sizes.



1. Transfer the biopsy in the bag with a pair of forceps OR empty both fixative and specimen in the bag. Let the fixative drip out of the bag in a container, close the bag and insert in a cassette.
2. After processing, remove bag from cassette. Open with care, extending the edges.
3. Extract biopsy and proceed with your embedding.

Cat. No.	Dimensions (mm)	Qty/Pk
10154-038	30 X 50	1000
10154-040	45 X 75	1000
10154-076	75 X 95	500



While providing maximum tissue safety, you can conveniently see through the biopsy bag.



## Paraffin Block Mailer, 6 compartments

Made of PVC

At last, a transport container made especially for paraffin blocks. Sturdy and easy to use, the Simport® mailer is transparent for easy viewing of contents. It can be used for handling and shipping up to 6 blocks as needed, while having to keep only one model of block mailer in inventory. The attached cover is easy to close but very secure when closed. Suitable for all regular models of tissue and biopsy cassettes.

Cat. No.	Dimensions	Qty/Cs
89201-982	134 x 141 x 29 mm H ( 5 1/4 x 5 5/8 x 1 1/8 in. H )	50






## Tissue Capsules

Made of polypropylene

These capsules are suitable for holding tissue samples during processing. The lids have a frosted write-on area for sample identification and an open mesh area to facilitate fluid exchange. The entire surface of the base is also an open mesh. The lid snaps securely on the base, eliminating the risk of tissue loss during processing.

For IVD use

Cat. No.	Size (mm)	Color	Qty/Cs
87002-378	28 x 5 H	White	1000
87002-380	38 x 10 H	White	1000



## Embedding Rings

Made of high impact polystyrene

For IVD use

Embedding rings are suitable for holding and identifying tissue sample blocks and fit well in microtome chuck adapters. The etched writing surface on the ring is marked with an identification number and placed on top of the sample block. Additional paraffin is poured into the base mold to cement the ring onto the tissue block. The embedding ring securely holds the tissue sample in the microtome chuck adapter for sectioning and then identifies the sample while in storage. Rings are available in different colors. Each case contains 4 dispenser boxes of 250 rings.

Cat. No.	Color	Qty/Box	Qty/Cs
87002-368	White	250	1000
87002-370	Pink	250	1000
87002-372	Green	250	1000
87002-374	Yellow	250	1000
87002-376	Blue	250	1000

## Write-ON™ Marker Pen

This pen is specially suited to be used on anterior surfaces and sides of Histology Cassettes. Ink will dry almost instantly. Ink withstands temperatures up to 195 °C and is resistant to solvents.

Cat. No.	Color	Qty/Pk
89413-180	Black	10





# SLIDE STORAGE

## A MODERN APPROACH TO SLIDE FILING

### SlideFile™ Jr. Storage System

This rack is also  
available separately

Unobstructed front  
writing surface

Base made of high impact polystyrene / Cover made of polystyrene

The Junior model can hold up to 200 slides per unit in just 860 cm<sup>3</sup> (53 cu. in.) and is stackable for space efficient storage. Each SlideFile™ Jr. includes a slide box and a removable tray. A tinted hinged cover makes the contents of the box easy to see at a glance. The base is available in five different colors to help slide classification and to minimize the possibility of sample mix-up.

The key to the SlideFile™ Jr. is a removable tray inside the storage box having fifty individual numbered slots. All slides are stored upright for easier insertion and removal. Simply tilt them forward and backward with one finger to easily and rapidly pick up the slide you need. A unique feature with this system is to be able to read bar codes without having to remove slides from the box.

For space saving purposes, you can double the amount of slides simply by storing two slides per slot. And for maximum storage space, simply remove the tray and line up 200 slides in 3 rows for long term storage. Will resist temperatures between -80 °C and +80 °C. Not autoclavable.

Dimensions: 82 x 140 x 86 mm H (3 1/4 x 5 1/2 x 3 3/8 in. H)



Read bar codes  
without having to  
remove slides from  
tray.



Simply tilt slides  
forward or  
backward with  
one finger to  
easily and rapidly  
pick up the one  
you need.



Remove slide tray  
and it will store up  
to 200 slides.



Removable tray  
makes it easy  
to carry slides  
around and store  
up to 50 slides  
vertically (1 per  
slot) or 100 slides  
vertically (2 per  
slot)



Two index cards  
numbered from  
1 to 50 are  
supplied with  
each box.

Cat. No.	Color	Qty/Pk	Qty/Cs
89039-708	Blue	1	10
89039-710	Green	1	10
89039-712	Pink	1	10
89039-714	White	1	10
89039-716	Yellow	1	10

### DrainRack™ Jr.

Made of high impact polystyrene

Can hold up to 100 microscope slides in 50 individual numbered slots. Will resist temperatures between -80 °C and +80 °C. Not autoclavable.

Cat. No.	Color	Qty/Pk	Qty/Cs
89039-728	Blue	1	10
89039-730	Green	1	10
89039-732	Pink	1	10
89039-734	White	1	10
89039-736	Yellow	1	10



Each position  
is numbered  
for easy slide  
identification.

Drain holes  
will completely  
empty bottom of  
rack.

Dimensions: 75 x 125 x 25 mm H (3 x 5 x 1 in. H)



## SlideFile™ Storage System

The most convenient, organized and versatile way of storing 75 x 25 mm or 3 x 1 in. microscope slides. This impact resistant SlideFile™ Storage System can hold up to 400 slides per unit in just 1720 cm³ (105 cu. in.) and is stackable for space efficient storage.

This rack is also available separately.

Base made of high impact polystyrene / Cover made of polystyrene

Each SlideFile™ Storage System includes a slide box and a removable tray. A tinted hinged cover makes the contents of the box easy to see at a glance. The base is available in five different colors to help in slide classification and to minimize the possibility of sample mix-up.

The key to the SlideFile™ System is a removable tray inside the storage box having a hundred individual numbered slots. All slides are stored upright for easier insertion and removal. Simply tilt them forward and backward with one finger to easily and rapidly pick up the slide you need. A unique feature with this system is to be able to read bar codes without having to remove the slides from the box.

For space saving purposes, you can double the amount of slides simply by storing two slides per slot. For maximum storage space, simply remove the tray and line up 400 slides in 3 rows for long term storage. Will resist temperatures between -80 °C and +80 °C. Not autoclavable.

Dimensions: 82 x 245 x 86 mm H (3 1/4 x 9 5/8 x 3 3/8 in. H)

Cat. No.	Color	Qty/Pk	Qty/Cs
14231-896	Blue	1	10
14231-898	Green	1	10
14231-900	Pink	1	10
14231-902	White	1	10
14231-904	Yellow	1	10



Read bar codes without having to remove slides from tray.



Simply tilt slides forward or backward with one finger to easily and rapidly pick up the one you need.



Remove slide tray and store up to 400 slides.



Removable tray makes it easy to carry slides around and store up to 100 slides vertically (1 per slot) or 200 slides vertically (2 per slot)



Two index cards numbered from 1 to 100 are supplied with each box.

## DrainRack™



Dimensions: 75 x 231 x 25 mm H (3 x 9 x 1 in. H)

Easy-to-read numbers from 1 to 100 identifying each slot

Made of high impact polystyrene


This rugged tray used as a drain rack can hold up to 200 microscope slides in 100 individual numbered slots. All slides are stored upright for easier insertion and removal. Simply tilt them forward and backward with one finger to easily and rapidly pick up the slide you need. A unique feature with the DrainRack™ is to be able to read bar codes without having to remove the slides from the box.

For space saving purposes, you can double the amount of slides simply by storing 2 slides per slot, giving you a capacity of 200 slides instead of 100. Not autoclavable.

Cat. No.	Color	Qty/Pk	Qty/Cs
89039-718	Blue	1	10
89039-720	Green	1	10
89039-722	Pink	1	10
89039-724	White	1	10
89039-726	Yellow	1	10



## DissecTable™ Dissecting Board



Patent applied for

Made of high-density polyethylene


A new and unique approach makes this dissecting board more convenient than any other found on the market today. It is no more necessary to buy different sizes as this board offers a large surface on one side and two smaller ones on the other side.

Made of heavy-duty stain resistant thick polyethylene, it will last for years to come without changing shape, bending or swelling. Will not dull fine surgical blades. In order to contain fluids, a drain groove is carved all around the edge of the DissecTable™.

On one side, you will find a large cutting area including dimensional scales in inches and centimeters, along with a 60 x 80 mm grid made of 48 x 10 mm squares. Six dimensional circles are also printed from  $\frac{1}{8}$  to  $\frac{5}{8}$  in. and 4 to 14 mm in diameter. Flip it over and the other side offers two cutting boards half the size with the same dimensional features printed on each one of them. All corners have rubber feet giving more stability to the working surface.

Dimensions: 575 mm x 400 mm x 12.5 mm (23 x 16 x  $\frac{1}{2}$  in H)

Cat. No.	Description	Qty/Cs
89041-170	DissecTable™	1



## DissecTable™ Jr. Dissecting Board

Made of high-density polyethylene

A smaller DissecTable™ is also available with the same features and benefits as the larger model. Perfect for smaller counter area. Dimensions: 330.2 mm x 279.4 mm x 12.5 mm (13 x 11 x  $\frac{1}{2}$  in H)

Cat. No.	Description	Qty/Cs
89215-470	DissecTable™ Jr.	1



Each base raises the DissecTable™ by 91 mm (3  $\frac{5}{8}$  in.)

## Board Base (for use with 89041-170)

Made of high impact polystyrene

To make dissecting more comfortable, this heavy-duty base is used to elevate the DissecTable™ Board to the right height. The bases are stackable and will not move sideways during the dissecting work. The base will also retain excess fluid if necessary.



Dimensions: 481 mm x 656 mm x 91 mm (19  $\frac{1}{4}$  x 26  $\frac{1}{4}$  x 3  $\frac{5}{8}$  in H)

Cat. No.	Description	Qty/Cs
89041-172	DissecTable™ Board Base	1



Can be used  
on both sides

THE *DispoCut*<sup>TM</sup>  
DISSECTING BOARD



## Disposable Dissecting Board

The DispoCut<sup>TM</sup> Disposable Dissecting Board is strong yet inexpensive enough to throw away. It is especially developed to provide a clean, safer and more efficient way of handling infectious tissue specimens for the pathologist. It can be used on both sides, a great money saving feature. Printed with helpful imperial and metric dimensional scales in inches, centimeters and millimeters. Available in three sizes to accommodate small biopsies to large gross anatomy procedures.

DispoCut<sup>TM</sup> is extrusion made using a copolymer resin in order to increase impact and temperature performance. Copolymer resins are also used because they retain the ability to be flexed an unlimited number of times without breaking. Chemically, DispoCut is inert. At regular temperatures most oils, solvents and water have no effect, allowing it to perform under adverse weather conditions or as a product component exposed to harsh chemicals.

Each surface has many conveniently located rulers including seven dimensional circles from 4 to 16 mm in diameter and five larger ones from 2 to 6 cm in diameter. Surface will not dull knives. Perfect for use with dissecting pins. All sizes of DispoCut<sup>TM</sup> Disposable Dissecting Boards are ideal for pathology labs, medical schools, classroom dissections, forensic labs, medical research labs, pharmaceutical labs, surgery and more.

Temperature performance range: -27 °C to 71 °C (17 °F to 160 °F)

Melting point: 162 °C (324 °F)

Sterilization: DispoCut<sup>TM</sup> may be wiped down with alcohol with no effect on the material. DispoCut<sup>TM</sup> is being autoclaved (in excess of 3 years) in many situations. There are some extreme settings which will be damaging and we suggest a trial to determine performance in your equipment. Ethylene oxide gas sterilization has no effect of any kind on DispoCut<sup>TM</sup> and may be repeated any number of times.

Physical Data: Specific Gravity 0.90 - 0.96. Essentially insoluble in water.

Cat. No.	Description	Qty/Pk	Qty/Cs
89201-984	152 x 203 mm (6 x 8 in.)	24	96
89201-986	229 x 305 mm (9 x 12 in.)	12	48
89201-988	305 x 483 mm (12 x 19 in.)	12	24



# SLIDE STAINING

## EasyDip™ Slide Staining System



Slide Staining  
Rack sold  
separately

Made of acetal

Finally a user-friendly approach for staining your microscope slides, the EasyDip™ Slide Staining System has two components: a square staining jar and a 12-position vertical slide rack. As an extra benefit, they are available in 5 different colors to help better identifying contents or applications.

The staining jar being made of resistant acetal plastic will not break like most glass jars do. It will resist to most staining agents including alcohol and xylene (but not phenol, iodine or ferric chloride). The wide stable base offers greater stability while the inside is recessed, allowing for a smaller reagent volume of only 80 ml. Easy to clean and no metals to corrode. Ideal for special stains, frozen sections and special processes. Dimensions: 64 x 76 x 92 mm H (2 1/2 x 3 x 3 5/8 in. H).

### EasyDip™ Slide Staining Jar

Cat. No.	Color	Qty/Cs
87000-120	Blue	6
87000-122	Green	6
87000-124	Pink	6
87000-126	White	6
87000-128	Yellow	6
87000-130	Assorted*	1 Kit

\*This kit includes 5 jars (one of each color) and 1 rack (87000-132).



## EasyDip™ Slide Staining Kit



425 x 102 x 38 mm H  
(16 3/4 x 4 x 1 1/2 in. H)

This kit includes one anodized aluminum rack along with six assorted color jars (two white ones) and one 87000-132 Slide Staining Rack. Also available without staining jars and staining rack (see 490010-317)

Cat. No.	Description	Qty/Cs
10154-052	EasyDip Kit	1
490010-317	Aluminum Holder only	1

## EasyDip™ Slide Staining Rack



Made of acetal

The EasyDip™ Slide Staining Rack will hold up to 12 microscope slides with dimensions such as 75 x 25 mm (3 x 1 in.) and even 76 x 26 mm and with a thickness of 1.0 and 1.2 mm. The slides fit into individual slots for free passage and rapid drainage of staining fluids. Available in dark gray only. Dimensions: 60 x 64 x 97 mm H (2 1/4 x 2 1/2 x 3 3/4 in. H)

Cat. No.	Color	Qty/Cs
87000-132	Dark Gray	6



A handle is permanently attached to the rack for easy insertion and removal.



Staining rack is placed at an angle to facilitate draining of slides.



Vertical rack eases slide removal without using forceps.



Slides are fully secured when lid is upright. Rotate it sideways to allow their easy removal.



## StainTray™ Slide Staining System

Made of ABS Plastic

Another user friendly approach to immunohisto-chemistry staining. This tray is also suitable not only for routine staining requiring a humid chamber but is also ideal for Hematology, Cytology and Microbiology laboratories. Manipulation is made safe and easy by using only one hand.

The StainTray™ has a black base made of tough ABS plastic withstanding a wide range of chemicals (Avoid chlorinated hydrocarbons). It will accept up to 20 slides on four plastic rails covered with a polymer strip to perfectly hold slides even if tray is held at an angle. When humidity is needed, wells between rails will hold up to one ml of water securely without splashing. Middle wells will hold up to 2 ml each. Rails are raised not only to avoid water touching the slides but to make them more easily retrieveable. The base will also hold excess stain solution dripping from the slides. Four rubber feet ensure greater base stability. Units are stackable for space saving purposes.

Two covers are available:

- A clear one allowing for visual examination. Made of PETG with a temperature range of -20 °C to +60 °C.
- A black lid for fluorescent work. Made of ABS with a temperature range of -80 °C to +80 °C



**DO NOT USE  
WITH ACETONE**

Dimensions: 38 x 24 x 4.5 cm H. (15 x 9 3/8 x 1 3/4 in. H)

Cat. No.	Description	Capacity	Qty/Cs
87000-134	Base with Clear Lid	20 slides	1
87000-136	Base with Black Lid	20 slides	1
87000-138	Clear Lid only	—	1
87000-140	Black Lid only	—	1

## StainTray™ Slide Staining System

Made of ABS Plastic

This 10-slide StainTray™ offers the same great features and benefits as the larger Model. Dimensions with cover: 24 x 24 x 4.5 cm H (9 3/8 x 9 3/8 x 1 3/4 in. H)

Cat. No.	Description	Capacity	Qty/Cs
97000-382	Base with Clear Lid	10 slides	1
97000-384	Base with Black Lid	10 slides	1
97000-386	Clear Lid only	—	1
97000-388	Black Lid only	—	1



Plastic rails are covered with a polymer strip holding slides perfectly even if tray is held at an angle.



Wells between rails can be used to hold water for techniques needing a humid environment.



A black lid for fluorescent work. Made of ABS with a temperature range of -80 °C to +80 °C.



If you **TRULY** care about your sample,  
let us help you **PROTECT** its integrity!



Can also be used as a slide staining jar

## LockMailer™ Microscope Slide Jar

95kPa  
TESTED

Jar made of Polypropylene  
Closure made of High Density Polyethylene

At last a tamper evident multi purpose container for mailing, staining or storing microscope slides.

Constructed of extra-strong and clear polypropylene, it will hold up to 4 standard 3 x 1 in. or 75 x 25 mm slides vertically. Inside channels are slotted to keep slides safely separated. Perfect also for slide conveyors and specimen slide transport between the doctor's office and the lab.

It incorporates a unique tamper evident leakproof screw cap ensuring your peace of mind during transport or storage situations where someone might have manipulated your slides without your prior knowledge. Can also be used without the tamperproof locking mechanism. For color coding purposes, use a Capinsert™ (see below) that may be inserted on top of closure. Ten different colors are available.

The container is designed for maximum stability on a bench top while having an internal volume of only 12 ml.

Dimensions: 35 x 87 mm H (1 3/8 in. x 3 7/16 in. H)

Cat. No.	Color	Qty/Pk	Qty/Cs
89129-506	Magenta	100	500

## How to use the LockMailer™



Push up the attached tab on side of vial.



Make sure it firmly clicks in place.



Screw on tamperproof cap all the way.



When opening the vial, the tamper evident ring will detach itself from the cap.



The LockMailer™ can also be used without the tamper evident feature.

## Color Coding CAPINSERT™

Made of polypropylene

The Capinsert™ is used to color code a multitude of Simport® products according to your specific needs. It is inserted on top of the closure and has a write-on frosted area for sample identification.



Cat. No.	Color	Cat. No.	Color	Qty/Bag
95038-738	Blue	95038-748	Pink	500
95038-740	Gray	95038-750	Red	500
95038-742	Green	95038-752	Violet	500
95038-744	Lilac	95038-754	White	500
95038-746	Orange	95038-756	Yellow	500
* Blue, lilac, red, yellow and white		89500-344	Assorted*	500



## UniMailer™ Slide Mailer

Made of high impact polystyrene



- 1 Slides fit perfectly to avoid any vibrations and breaking during transport.
- 2 Ship as many slides as needed, using only one type of slide mailer.
- 3 A special locking tab keeps UniMailer™ slide mailers securely in place.
- 4 Through holes, you can attach ID label or tamper evident tie.
- 5 Three writing surfaces for proper slide identification.
- 6 Strong plastic ensures rigidity and avoids any slide breakage.
- 7 Great for accessing one slide at a time while other slides are being kept well protected.

For many years now, noticeable improvements on the design of slide mailers have been scarce. Following many suggestions from users in the lab field, Simport® is now proud to come out with the UniMailer™, a truly versatile model which can easily be used for handling and shipping one or as many slides as needed, while having to keep only one model in inventory.

The UniMailer™ is a one-slide tray allowing the use of as many as necessary according to the number of slides to be mailed. Not only do they fit snugly on top of each other but they are also secured by an innovative locking mechanism. You may also want to insert a tamper evident tie or attach an ID label.

Designed to accommodate 25 x 75 mm and 1 x 3 in. slides with or without cover glasses, they can also be used to provide safe storage for those valuable slides you want to protect. It provides for multiple reuse or single use disposability.


Each tray allows placing the slide in a horizontal position for full visibility. Slides can easily be inserted with an exact fit to avoid any breaking during transport. When pressed on either side while in the UniMailer™, they will pop-up for easy removal.

Identification can be made on three sides or on top. Made of an almost unbreakable plastic, they are available in many popular pastel colors for easy identification. Packed in bag of fifty slide mailers. Will resist temperatures between -80 °C and +80 °C.


Dimensions: 89 x 29 x 6 mm H (3 1/2 x 1 3/8 x 1/4 in. H)

Cat. No.	Color	Qty/Pk	Qty/Cs
89039-738	Blue	50	200
89039-740	Green	50	200
89039-742	Pink	50	200
89039-744	White	50	200
89039-746	Yellow	50	200


Not only do UniMailer™ slide mailers fit snugly on top of each other but are secured by an innovative locking mechanism.



To close, slide upper UniMailer™ forward until locking pins are engaged.



Locking mechanism is now functional.



To open, insert finger between two locking tabs and slide back upper UniMailer™.

## The UniMailer™ is easy to use



Identify content by writing on sides.



Place slide in UniMailer™



Place another slide mailer on top and slide forward until a click is heard.



If desired, you can attach a tamper evident tie.



To open, slightly lift front tab to disconnect lock and slide back upper UniMailer™.



Press on slide to lift and remove.



## Tamper Evident



## HISTOTAINER™ I

### TAMPER EVIDENT Prefilled Specimen Containers, 50% Filled with 10% Neutral Buffered Formalin

Container made of polypropylene  
Closure made of polyethylene

Especially designed for collection, transport and storage of histology specimens, Simport® offers shatter resistant polypropylene containers, eliminating most problems of leakage and evaporation. The magenta lids are ribbed for easy opening when hands are wet or gloved while the jars are stackable for easy, safe storage and translucent to allow specimens to be viewed without opening. The closures are manufactured from virgin polyethylene with a unique integrated leak-resistant seal. Container's vertical walls offer excellent rigidity.

The uniqueness of the HistoTainer™ I is that it incorporates an innovative

tamper evident screw cap ensuring your peace of mind during transport or storage situations where someone might have manipulated the specimen without your prior knowledge. Can also be used without using the tamper evident locking mechanism. For color coding purposes, use a Capinsert™ (see series on page 30) on top of closure. Ten different colors are available.

Both containers and caps are manufactured without the use of plasticisers or mold release agents. All material used in manufacture are free from latex. All containers are 95 kPa compliant. Available in many sizes from 20 to 120 ml. Packaging in trays of 24, cases of 96.

The Simport® HistoTainer™ I is half filled with 10% Neutral Buffered Formalin as a fixative. 10% Neutral Buffered Formalin penetrates quickly, but fixes slowly. The Formalin is enhanced by a buffering capacity optimizing histological results by light microscopy and immunohistochemistry.

Cat. No.	Packaging	Volume	Qty/Tray	Qty/Cs
89499-252	Tamper Evident – Internal Trays	20 ml	24	96
89499-254	Tamper Evident – Internal Trays	40 ml	24	96
89499-256	Tamper Evident – Internal Trays	60 ml	24	96
89499-258	Tamper Evident – Internal Trays	90 ml	24	96
89499-250	Tamper Evident – Internal Trays	120 ml	24	96



## How to use the HistoTainer™ I



Remove Screw Cap.



Place sample in container.



Push up the attached tab on side of container. Make sure it firmly clicks in place.



Screw cap completely on container.



When opening the container, the tamper evident ring will detach itself from the cap.



The HistoTainer™ can also be used without the tamper evident feature.



As a cassette holder, the 40 ml HistoTainer™ 89499-254 containing 20 ml of 10% Formalin, is the ideal size container to transport up to four tissue samples pre-inserted in processing / embedding cassettes.



Packaged in sturdy cardboard boxes with handles for easy carrying.

## Anatomy of the HistoTainer™ I

1. Ridges around base offer a better grip during opening and closing.
2. Warning label has space for patient identification.
3. Insertion of a Capinsert™ allows color coding identification of contents.
4. Molded ridges around lid make it easy to open and close.
5. Tamper evident sealing ring for better sample protection.
6. Specially designed locking tab to ensure a perfect tamper evident seal.
7. 10% Neutral Buffered Formalin helps to protect sample integrity.





## With Conventional Closure



## HISTOTAINER™ II

### NON Tamper Evident Prefilled Specimen Containers, 50% Filled with a 10% Neutral Buffered Formalin



Container made of polypropylene / Closure made of polyethylene

Especially designed for collection, transport and storage of histology specimens, Simport® offers shatter resistant polypropylene containers, eliminating most problems of leakage and evaporation. Containers are manufactured from virgin, translucent polypropylene. The white lids are ribbed for easy opening when hands are wet or gloved while the jars are stackable for easy, safe storage. Jars are translucent and specimens can be viewed without having to open the lid. Closures are manufactured from virgin polyethylene with a unique integrated leak-resistant seal. Container's vertical walls offer excellent rigidity. For color coding purposes, use a Capinsert™ (see details on page 30) on top of closure. Ten different colors are available.

Both containers and caps are manufactured without the use of plasticisers or mold release agents. All materials used in manufacturing are free from latex. Containers are 95 kPa compliant. Available in many sizes from 20 to 120 ml. Packaging is offered in trays of 24, cases of 96.

The HistoTainer™ II is half filled with a choice of fixatives. 10% Neutral Buffered Formalin penetrates quickly, but fixes slowly. The Formalin is enhanced by a buffering capacity optimizing histological results by light microscopy and immunohistochemistry.



Packaged in sturdy cardboard boxes with handles for easy carrying.



Warning label has space for patient identification

Cat. No.	Volume	Fixative	Qty/Tray	Qty/Cs
10662-320	20 ml	Formalin	24	96
10662-322	40 ml	Formalin	24	96
10662-324	60 ml	Formalin	24	96
10662-326	90 ml	Formalin	24	96
10662-328	120 ml	Formalin	24	96

For Capinsert™ details, please refer to page 30.





# CoreDish™

## Multiple Biopsy Containers

Half Prefilled with 10% Formalin



Made of polystyrene

Few recommendations concerning how the biopsies should be handled have been published. Performing a large number of biopsies means an increase in the number of containers handled and consequently a technical overload of the transmission network, which occurs without any financial counterpart. A new approach had to be developed in order to increase productivity.

Simport® is proud to offer a multi-compartment container in the shape of a dish and half prefilled with 10% Neutral Buffered Formalin, for holding and transporting biopsies. It is supplied with a leakproof closure with o-ring ensuring total protection of contents. **The Simport® CoreDish® measures only 15 x 95 mm in diameter.** Each compartment is clearly identified to allow proper placement and visualization of the biopsy being inserted. **Thanks to the CoreDish® it is no more necessary to use a multitude of individual containers, thereby reducing risks of confusion.** The Simport® CoreDish® offers many configurations in order to hold different biopsies of the breast, prostate, upper GI tract and lower GI tract. A label allows essential information to be written such as patient I.D., doctor, date and time. **The CoreDish® is also available without formalin.**



Bar Code printing available.  
Contact Simport® for more details.

For IVD use





## BREAST BIOPSY CONTAINER

Simport® is proud to offer a multi-compartment container (out of five compartments, four are labelled: Left Upper Quadrant, Right Upper Quadrant, Left Lower Quadrant, Right Lower Quadrant) in the shape of a dish and half prefilled with 10% Neutral Buffered Formalin, for holding and transporting biopsies. It conforms to OSHA directives. Each compartment is clearly identified to allow proper placement and visualization of the breast biopsy being inserted. A writing area for patient information is provided. Leakproof seal, thanks to o-ring lid, allows for safe and easy transport of the specimens from collection to analysis.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-774	Breast	5	YES	1	10
89176-824	Breast	5	NO	1	10



## UPPER GI TRACK BIOPSY CONTAINER

For upper GI track biopsies. Eight compartments. Leakproof seal thanks to o-ring lid. An area for patient information is provided. Seven labeled compartments: Gastric Card, Gastric Body, GE Junction, Gastric ATR, Distal Esophagus, Pylorus, Duodenum. Leakproof seal, thanks to o-ring lid, allows for safe and easy transport of the specimens from collection to analysis.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-778	Upper Gi Tract	8	YES	1	10
89176-828	Upper Gi Tract	8	NO	1	10



## LOWER GI TRACK BIOPSY CONTAINER

For lower GI track biopsies. Twelve compartments. Leakproof seal thanks to o-ring lid. An area for patient information is provided. Ten labeled compartments: Proximal Flexure Colon, Hepatic Flexure Colon, Distal Transverse Colon, Ascending Colon, Splenic flexure Colon, Cecum, Descending Colon, Terminal Ileum, Rectum, Sigmoid Colon. Leakproof seal, thanks to o-ring lid, allows for safe and easy transport of the specimens from collection to analysis.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-780	Lower Gi Tract	12	YES	1	10
89176-830	Lower Gi Tract	12	NO	1	10



## PROSTATE BIOPSY CONTAINER

For prostate biopsies. Twelve compartments. Leakproof seal thanks to o-ring lid. An area for patient information is provided. Twelve labeled compartments: L Base, R Base, L Lateral Base, R Lateral Base, L Lateral Medial, L Medial, R Medial, R Lateral Medial, L Lateral Apex, L Apex, R Apex, R Lateral Apex. Leakproof seal, thanks to o-ring lid, allows for safe and easy transport of the specimens from collection to analysis.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-782	Prostate	12	YES	1	10
89176-832	Prostate	12	NO	1	10



## PROSTATE BIOPSY CONTAINER

For prostate biopsies. Eight compartments. Leakproof seal thanks to o-ring lid. An area for patient information is provided. Six labeled compartments: Base, Lateral Base, Medial, Lateral Medial, Apex, Lateral Apex. Leakproof seal, thanks to o-ring lid, allows for safe and easy transport of the specimens from collection to analysis.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-776	Prostate	8	YES	1	10
89176-826	Prostate	8	NO	1	10



## CoreDish™

### GENERAL PURPOSE MULTIPLE BIOPSY CONTAINERS



#### 5 COMPARTMENT BIOPSY CONTAINER

Made of polystyrene

Performing a large number of biopsies means an increase in the number of containers handled and consequently a technical overload of the transmission network, which occurs without any financial counterpart. A new approach had to be developed in order to increase productivity. Simport® is proud to offer a five-compartment container in the shape of a dish and half prefilled with 10% Neutral Buffered Formalin, for holding and transporting biopsies. It is supplied with a leakproof screw closure with o-ring ensuring total protection of contents. A writing area for patient information is provided. Compartments are numbered from 1 to 5.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-784	General purpose	5	YES	1	10
89176-834	General purpose	5	NO	1	10



#### 8 COMPARTMENT BIOPSY CONTAINER

Made of polystyrene

Simport® is proud to offer a multi-compartment container for up to 8 biopsies. The screw on lid incorporates an o-ring in order to make it leakproof and protect its contents. The CoreDish® conforms to OSHA directives. An area for patient information is provided on the label. Compartments are numbered from 1 to 8.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-786	General purpose	8	YES	1	10
89176-836	General purpose	8	NO	1	10



#### 12 COMPARTMENT BIOPSY CONTAINER


Made of polystyrene

This model will contain up to twelve biopsies. The screw on lid incorporates an o-ring in order to make it leakproof and protect its contents. The CoreDish® conforms to OSHA directives. Compartments are numbered from 1 to 12.

Cat. No.	For	Compartments	Prefilled	Qty/Pk	Qty/Cs
89137-788	General purpose	12	YES	1	10
89176-838	General purpose	12	NO	1	10



A security label is supplied to ensure integrity of contents from collection stage to reopening of CoreDish®.



To close, turn clockwise until you feel a firm stop.



#### The CorePicker™

Made of polystyrene

A practical tool and a great help to pick up and handle biopsies out of the CoreDish™. Packed in tamperproof resealable bags.



#### Shipping Box for CoreDish®

Made of cardboard

This sturdy and easy-to-assemble shipping box is most convenient for transporting or mailing the Simport CoreDish®.

Cat. No.	Length	Qty/Bag	Qty/Pk
89215-472	53 mm (2 1/8 in.)	25	125

Cat. No.	Description	Qty/Pk
89215-474	Cardboard Box	10





## SlideFolder™

Base made of high impact polystyrene / Hinged doors made of polystyrene

The SlideFolder™ will hold up to twenty standard microscope slides 75 mm x 25 mm (3 x 1 in.) and is made of two parts: a base holding the slides horizontally offering numbered spaces for easy identification, and transparent doors which can either cover the slides or be swung behind the SlideFolder™ for space saving purposes.


The base is available in 5 different colors, allowing color-coding classification of the slides. Each slide location is identified with a number from 1 to 20. Removal of slides is made easy simply by pressing on one end, which will automatically lift the other end.

The two transparent hinged covers offer a full view of each slide without having to remove it from its position in the SlideFolder™ and allows easy reading of ID labels with or without an optical bar code reader. All units are stackable and take minimum space on laboratory tables or shelves. Will resist temperatures between -80 °C and +80 °C. Not autoclavable.

Dimensions: 192 x 295 x 11 mm H (7 <sup>9</sup>/<sub>16</sub> x 11 <sup>11</sup>/<sub>16</sub> x <sup>7</sup>/<sub>16</sub> in. H)



For light sensitive slides, use 89039-698 SlideFolder™ with opaque doors.



For easier access to slides, simply swing the transparent hinged covers behind the SlideFolder™.



Easy slide removal by pressing down on one end and lifting it from the other.

Cat. No.	Color	Qty/Cs
89039-686	Blue	10
89039-688	Green	10
89039-690	Gray	10
89039-692	White	10
89039-694	Yellow	10
89039-696	Assorted (two of each color)	10

Cat. No.	Color	Qty/Cs
89039-698	Opaque doors and white base	10

## SlideTray™

Made of HIPS

The SlideTray™ is a convenient microscope slide holder made of heavy-duty plastic lasting many years even under the most adverse conditions. The SlideTray™ will hold up to 20 microscope slides in an almost horizontal position. Each slide can be easily removed and placed back in its position. The SlideTray™ is easily stackable and will take minimum space on any shelf or laboratory counter. Even when trays are stacked, slides are well protected and will not touch the tray above.

Dimensions: 206 x 299 x 18 mm H (8 <sup>1</sup>/<sub>8</sub> x 11 <sup>3</sup>/<sub>4</sub> x <sup>11</sup>/<sub>16</sub> in. H)



Slides are easily inserted and removed.

Cat. No.	Color	Qty/Cs
10154-034	White	10





# CytoSep™ Family



The Simport® CytoSep™ Family is a series of Cytology Funnel sample chambers specially designed to concentrate cells into thin-layer preparations. Simport® is one of the most trusted names in the disposable plasticware marketplace, providing quality products since 1975 and is proud to offer the largest choice of Cytology Funnels on the market by manufacturing numerous models for use with the Shandon Cytospin® 4 Cyto centrifuge, the Sakura Cyto-Tek® Cyto centrifuge, the Hettich Cyto-System, the Unitech (Wescor) Cytopro® Cyto centrifuge and finally the StatSpin Cytofuge® 2 Cyto centrifuge. They are safer than reusable sample chambers and lower your risk of contamination to pathogenic samples. After use, they are simply discarded. The CytoSep™ Cytology Funnels are a time saver compared to cleaning and sterilizing reusable sample chambers. The Simport® CytoSep™ Cytology Funnels are recommended for the following applications:

- Bronchial alveolar lavage washes
- Cerebrospinal fluids
- Exudates and transudates
- Fine needle aspirates, and other aspirates
- Gastric washes
- Oral cavity washes
- Pericardial fluids
- Peritoneal fluids
- Pleural fluids
- Sputum
- Synovial fluids
- Urine

For IVD use 



## Consumables for the Shandon Cytospin® Cytocentrifuges Single CytoSep™ Cytology Funnel



Fully compatible with the Shandon CytoSpin® Centrifuge, Simport® CytoSep™ Cytology Funnels can be used to deposit a thin layer of cells in a clearly defined area of a microscope slide. The filter card absorbs any excess fluid. These Cytology Funnels have the filter cards pre-attached for consistent, reliable results. No alignment necessary! All disposable Funnels are packaged with closure caps to seal in specimen for added protection. All components also available separately.

For sample volumes of up to 0.5 ml, use the Simport® Single CytoSep™ Cytology Funnel with a White Filter Card and Cap. It provides a cell deposition area of 6 mm (28 mm squared). Can be use with all stainless steel slide clips.

For samples volumes of up to 0.4 ml, such as Spinal Fluids for example, use the Single CytoSep™ Cytology Funnel with Brown Filter Card and Cap. It allows for a slower absorption of fluids. All the individual components are also available separately.

Now available!  
Individually wrapped

For IVD use



Cat. No.	Description	Qty/Pk	Qty/Cs
89305-072	Single Funnel with White Filter & Cap	50	500
89429-112	<b>Individually wrapped</b> Single Funnel with White Filter & Cap	100	500
89305-070	Single Funnel with Tan Filter & Cap	50	500
89305-068	Single Funnel only	—	500
89305-080	Cap only	50	500
89305-078	White Filter Paper for Single Funnel	200	—
89305-082	Tan Filter Paper for Single Funnel	200	—

## Double CytoSep™ Cytology Funnel



The Simport® Double CytoSep™ Cytology Funnel with disposable sample chamber allows for two samples to be run simultaneously on a single slide and is ideal for immunohistochemistry work. The Double CytoSep™ Cytology Funnel provides a cell deposition area of 6 mm (28 mm square) for sample volumes of up to 0.5 ml. The filter card comes pre-attached. Cap is included. Can be use with all stainless steel slide clips. Each component is also available separately.

Now available!  
Individually wrapped

For IVD use



Cat. No.	Description	Qty/Pk	Qty/Cs
89305-076	Double Funnel with White Filter & Cap	50	500
89429-114	<b>Individually wrapped</b> Double Funnel with White Filter & Cap	100	500
89305-074	Double Funnel only	—	500
89305-080	Cap only	50	500
89305-084	White Filter Paper for Double Funnel	200	—



## Consumables for the Shandon Cytospin® Cytocentrifuges

### ALL PLASTIC Single and Double **CytoSep™** Cytology Funnels



These are so easy to use, and improve turn-around time while giving more diagnostic information. Being totally disposable, they eliminate time-consuming decontamination and cleaning. They are safe to use and reduce the risk of exposure to pathogenic samples. They also decrease the possibility of cross-contamination.

This series of Simport® Single CytoSep™ Cytology Funnels is single-use. The disposable sample chambers do not need metal clips and are designed to meet any processing requirement. They are capable of producing high quality thin-layer slide preparations while improving laboratory efficiency.

The disposable Sample Chambers with White Filter Cards are used for sample volumes up to 0.5 ml; the ones with the Brown Filter Cards are for sample volumes up to 0.4 ml. The cell deposition area is 6 mm in diameter (28 mm squared). Filter cards are pre-attached. Excellent for scanty specimens such as CSF. All components also available separately.

This CytoSep™ Cytology Funnel allows two sample deposition areas on a single slide. The disposable sample chambers do not need metal clips. Inserted filter card. This Sample Chamber is also disposable.

Cat. No.	Description	Qty/Pk	Qty/Cs
89305-088	Single Funnel with White Filter & Cap	40	480
89305-086	Single Funnel with Tan Filter & Cap	40	480
89305-090	Double Funnel with White Filter & Cap	40	480

For IVD use

**MORE  
ECO-FRIENDLY**

## YOU CAN ALSO REUSE OR ACQUIRE ANY INDIVIDUAL COMPONENTS WHEN NEEDED



Cat. No.	Description	Qty/Pk	Qty/Cs
89305-092	Single Funnel only	50	500
89305-094	Double Funnel only	50	500
89305-096	Base only	50	500
89305-080	Cap only	50	500
89305-078	White Filter Paper for Single Funnel	200	—
89305-082	Tan Filter Paper for Single Funnel	200	—
89305-084	White Filter Paper for Double Funnel	200	—

Each component is strong enough to be reused.

For IVD use



Insert funnel into base.



Insert microscope slide.



Place new filter onto microscope slide.



Clip top of funnel and base together.



Your CytoSep ALL PLASTIC Cytology Funnel is now ready to use.



## Consumables for the Shandon Cytospin® Cytocentrifuges MEGA CytoSep™ Cytology Funnel



The Simport® ALL PLASTIC CytoSep™ MEGA Funnel provides an easy, efficient and cost effective method of producing high quality thin-layer slide preparations. It eliminates the need for stainless steel slide clips, offering laboratory workflow improvements. It is dedicated for convenient preparation of larger volume samples.

This larger funnel is quick and easy to remove. The large rectangular cell deposition area of 22 x 14.75 mm (325 mm square) provides for up to 12 times the sample volume (6 ml) of the single CytoSep™ Cytology Funnel. It produces more cost-effective thin layer preparations when compared to other thin layer methods. Strategically placed baffles inhibit cell settling which results in uniform cell deposition and excellent quality slide preparations. Simport® ALL PLASTIC CytoSep™ Cytology MEGA Funnel and Cap minimize user exposure to pathogens while reducing the risk of specimen cross-contamination. Can prepare both air-dried and fixed preparations.

	Cat. No.	Description	Qty/Pk	Qty/Cs
<b>For IVD use</b> 	10154-036	MEGA Funnel & Cap	40	480

## Consumables for the Sakura Cyto-Tek® Cytocentrifuge CytoSep™ Cytology Funnel for Sakura Cyto-Tek® Cytocentrifuge



All components are available separately. The Simport® CytoSep™ Cytology Funnel offers the 1 ml fluid chamber, the base holder, the chamber cap, and the filter paper.

	Cat. No.	Description	Qty/Pk	Qty/Cs
	89305-098	Fluid Chamber only, 1 ml	50	200
	89305-100	Base Holder only	50	200
	89305-106	Cap only	50	200
<b>For IVD use</b> 	89305-102	White Filter Card only	—	200



Consumables for  
the Unitech (Wescor) Cyto-System

Single CytoSep™ Cytology Funnels for the Unitech (Wescor) Cytopro® Cytocentrifuge




These funnels will snap quickly in place, allowing the pad to align correctly with the sample tunnel. Made with a compression ring around the sample hole in order to better control the rate of absorption and to ensure more consistent results.

Two ports, one in the sample well and one in the tunnel, provide great versatility. Samples are loaded directly through the chamber caps to prevent spilling of hazardous ones. Caps provide added safety to the operator. A large, centered cell deposit area makes screening easier and more sensitive.

	Cat. No.	Description	Qty/Pk	Qty/Cs
For IVD use 	89305-110	Single Sample Chamber With White Filter Paper & Cap	48	—
	89305-120	White Filter Paper for Single Funnel	—	100

Dual CytoSep™ Cytology Funnels for the Unitech (Wescor) Cytopro® Cytocentrifuge



With two chambers, cell deposit areas are close together and easy to find, helping to speed sample analysis. Two deposit areas on one slide enhance all of the advantages of the popular single chambers. Reduced time spent loading and unloading slides.

- Two cell deposit areas on the same slide means true cost reduction.
- Two deposit areas on one slide enhance productivity for those under regulatory workload limitations.
- Reduced time spent loading and unloading slides between the rotor, stainer and microscope.
- Cell deposit areas are close together and easy to find, helping to speed sample analysis.
- Cytopro's 7 mm diameter spot provides a 37% larger area to collect cells.

	Cat. No.	Description	Qty/Pk	Qty/Cs
For IVD use 	89305-114	Double Sample Chamber With White Filter Paper & Cap	48	—
	89305-122	White Filter Paper for Double Funnel	—	100



## Consumables for the Hettich Cyto-System



The Simport® CytoSep™ Funnel Chambers for the Hettich Cyto-System optimize lab throughput with multiple funnel options in 2, 3, or 4 funnels per slide. These funnels are perfect for every application such as CSF, Viral infections, bronchial secretions and come in four sizes from 1 ml to 8 ml. The 1 ml chamber is for small-volume samples of low cell contents. Both 2 and 4 ml chambers are suggested for cell-rich samples, e.g. pleura, ascites and bronchial washings while the 8 ml chamber is perfect for large-volume samples such as urine.

Cat. No.	Description	Qty/Pk	Qty/Cs
89305-124	One-Funnel Chamber, 1 ml	10	50
89305-126	One-Funnel Chamber, 2 ml	10	50
89305-128	One-Funnel Chamber, 4 ml	10	50
89305-130	One-Funnel Chamber, 8 ml	10	50
89305-132	Filter for 1, 2 and 4 ml Chambers	200	—
89305-134	Filter for the 8 ml Chamber	200	—

For IVD use 




*Manufactured by*

**Simport®**

2588 Bernard-Pilon  
Beloeil, QC J3G 4S5  
Canada

*Canadian and Family Owned Since 1975*



Histosette, Macrosette are registered trademarks of Simport® Scientific / CoreDish, CytoSep, DispoCut, DissecTable, DrainRack, DrainRack Jr., E-Z Load, HistoTainer, LockMailer, Micromesh, Microsette, SlideFile, SlideFile Jr., SlideFolder, SlideTray, Slimsette, Swingsette, UniMailer, Unisette, Write-On are trademarks of Simport® Scientific / Shurk/Mark is registered trademark by Triangle Biomedical Sciences, Inc. USA. / Micro Write is registered trademark by Raymond Lam, England.

**VWR**  
We Enable Science

**1.800.932.5000 | [vwr.com](http://vwr.com)**



Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products. Any claims concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US, void where prohibited by law or company policy, while supplies last. | VWR, the VWR logo and variations on the foregoing are registered (®) or unregistered trademarks and service marks, of VWR International, LLC and its related companies. All other marks referenced are registered by their respective owner(s). | Visit [vwr.com](http://vwr.com) to view our privacy policy, trademark owners and additional disclaimers. ©2015 VWR International, LLC. All rights reserved.