

MICROFLEX®

▲ SUPRENO® EC



BLUE
NITRILE
NON-STERILE
AMBIDEXTROUS
TEXTURED FINGERS
EXTENDED BEADED CUFF
FOR SINGLE USE ONLY
NON-LATEX

POWDER-FREE EXTENDED CUFF EXAMINATION GLOVES

Supreno® EC provides extended-cuff protection of the wrists and arms for high-risk applications. Designed to maintain a comfortable fit while providing reliable hazard protection, these gloves are also adhesive-resistant. Tested for use with chemotherapy drugs.

- Lowest pinhole rates (AQL 0.65) set a new standard for protection
- Textured fingers for enhanced grip
- Meets or exceeds NFPA requirements



MEETS OR EXCEEDS



TESTED FOR USE WITH CHEMOTHERAPY DRUGS

SIZE	VWR CAT. NO.	MFG. CAT NO.	PACKAGING	
S	32916-670	SEC-375-S	50+	Gloves/Box
M	32916-672	SEC-375-M	10	Boxes/Case
L	32916-674	SEC-375-L		
XL	32916-676	SEC-375-XL		
XXL	32916-678	SEC-375-XXL		
XXXL	89135-222	SEC-375-3XL		

+ XXXL contains
40 gloves/box

GLOVE PROFILE		ASTM D 6319	SUPRENO® EC
Length	mm (inches)	min. 220 (8.7)	295 (11.6)
Cuff Thickness	mm (mils)	n/a	0.11 (4.3)
Palm Thickness	mm (mils)	min. 0.05 (2.0)	0.14 (5.5)
Finger Thickness	mm (mils)	min. 0.05 (2.0)	0.20 (7.9)
Tensile Strength	Before Aging After Aging	min. 14 min. 14	30 27
Elasticity/Elongation	Before Aging After Aging	min. 500 min. 400	500 500
Pinhole Defect Rate*	(AQL)	max. 2.5	0.65

* Pinhole Defect Rate is FDA minimum requirement.