

Safety Data Sheet

acc. to OSHA HCS

Printing date 01/22/2014

Reviewed on 04/12/2013

1 Identification**Product identifier****Product name:** Dimethyl fumarate**Stock number:** A10402**CAS Number:**

624-49-7

EC number:

210-849-0

Relevant identified uses of the substance or mixture and uses advised against.

No further relevant information available.

Identified use: SU24 Scientific research and development**Details of the supplier of the safety data sheet****Manufacturer/Supplier:**

Alfa Aesar, A Johnson Matthey Company

Johnson Matthey Catalog Company, Inc.

30 Bond Street

Ward Hill, MA 01835-8099

Tel: 800-343-0660

Fax: 800-322-4757

Email: tech@alfa.com

www.alfa.com

Information Department: Health, Safety and Environmental Department**Emergency telephone number:**

During normal hours the Health, Safety and Environmental Department at (800) 343-0660. After normal hours call Carechem 24 at (866) 928-0789.

2 Hazard(s) identification**Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008**

GHS07

Acute Tox. 4 H312 Harmful in contact with skin.

Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2A H319 Causes serious eye irritation.

Skin Sens. 1 H317 May cause an allergic skin reaction.

STOT SE 3 H335 May cause respiratory irritation.

Classification according to Directive 67/548/EEC or Directive 1999/45/EC

Xn; Harmful

R21: Harmful in contact with skin.



Xi; Irritant

R36/37/38: Irritating to eyes, respiratory system and skin.



Xi; Sensitizing

R43: May cause sensitization by skin contact.

Information concerning particular hazards for human and environment: Not applicable**Hazards not otherwise classified** No information known.**Label elements****Labelling according to Regulation (EC) No 1272/2008**

The substance is classified and labeled according to the CLP regulation.

Hazard pictograms

GHS07

Signal word Warning**Hazard statements**

H312 Harmful in contact with skin.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H317 May cause an allergic skin reaction.

H335 May cause respiratory irritation.

(Contd. on page 2)

USA

Safety Data Sheet

acc. to OSHA HCS

Printing date 01/22/2014

Reviewed on 04/12/2013

Product name: Dimethyl fumarate

(Contd. of page 1)

Precautionary statements

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P302+P352 IF ON SKIN: Wash with plenty of water/...
 P321 Specific treatment (see on this label).
 P405 Store locked up.
 P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

WHMIS classification

D2B - Toxic material causing other toxic effects

**Classification system****HMIS ratings (scale 0-4)****(Hazardous Materials Identification System)**

HEALTH	2
FIRE	1
REACTIVITY	1

Health (acute effects) = 2
 Flammability = 1
 Physical Hazard = 1

Other hazards**Results of PBT and vPvB assessment****PBT:** Not applicable.**vPvB:** Not applicable.**3 Composition/information on ingredients****Chemical characterization: Substances****CAS# Description:**

624-49-7 Dimethyl fumarate

Identification number(s):**EC number:** 210-849-0**4 First-aid measures****Description of first aid measures****After inhalation**

Supply fresh air. If required, provide artificial respiration. Keep patient warm.
 Seek immediate medical advice.

After skin contact

Immediately wash with water and soap and rinse thoroughly.
 Seek immediate medical advice.

After eye contact

Rinse opened eye for several minutes under running water. Then consult a doctor.

After swallowing Seek medical treatment.**Information for doctor****Most important symptoms and effects, both acute and delayed**

No further relevant information available.

Indication of any immediate medical attention and special treatment needed

No further relevant information available.

5 Fire-fighting measures**Extinguishing media****Suitable extinguishing agents**

Carbon dioxide, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

Special hazards arising from the substance or mixture

If this product is involved in a fire, the following can be released:

Carbon monoxide and carbon dioxide

Advice for firefighters**Protective equipment:**

Wear self-contained respirator.

Wear fully protective impervious suit.

USA

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 01/22/2014

Reviewed on 04/12/2013

Product name: Dimethyl fumarate

(Contd. of page 2)

6 Accidental release measures**Personal precautions, protective equipment and emergency procedures**

Wear protective equipment. Keep unprotected persons away.

Ensure adequate ventilation

Environmental precautions:

Do not allow material to be released to the environment without proper governmental permits.

Do not allow product to reach sewage system or any water course.

Do not allow to penetrate the ground/soil.

Methods and material for containment and cleaning up:

Dispose contaminated material as waste according to item 13.

Ensure adequate ventilation.

Prevention of secondary hazards: No special measures required.**Reference to other sections**

See Section 7 for information on safe handling

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage**Handling****Precautions for safe handling**

Keep container tightly sealed.

Store in cool, dry place in tightly closed containers.

Ensure good ventilation at the workplace.

Information about protection against explosions and fires: No information known.**Conditions for safe storage, including any incompatibilities****Storage****Requirements to be met by storerooms and receptacles:** No special requirements.**Information about storage in one common storage facility:**

Do not store together with acids.

Store away from strong bases.

Store away from oxidizing agents.

Store away from reducing agents.

Further information about storage conditions:

Keep container tightly sealed.

Store in cool, dry conditions in well sealed containers.

Specific end use(s) No further relevant information available.**8 Exposure controls/personal protection****Additional information about design of technical systems:**

Properly operating chemical fume hood designed for hazardous chemicals and having an average face velocity of at least 100 feet per minute.

Control parameters**Components with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

Additional information: No data**Exposure controls****Personal protective equipment****General protective and hygienic measures**

The usual precautionary measures for handling chemicals should be followed.

Keep away from foodstuffs, beverages and feed.

Remove all soiled and contaminated clothing immediately.

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

Maintain an ergonomically appropriate working environment.

Breathing equipment: Use suitable respirator when high concentrations are present.**Recommended filter device for short term use:**

Use a respirator with type P100 (USA) or P3 (EN 143) cartridges as a backup to engineering controls. Risk assessment should be performed to determine if air-purifying respirators are appropriate. Only use equipment tested and approved under appropriate government standards.

Protection of hands:

Impervious gloves

Check protective gloves prior to each use for their proper condition.

The selection of suitable gloves not only depends on the material, but also on quality.

Quality will vary from manufacturer to manufacturer.

Material of gloves Nitrile rubber, NBR**Eye protection:** Safety glasses

(Contd. on page 4)

USA

Safety Data Sheet

acc. to OSHA HCS

Printing date 01/22/2014

Reviewed on 04/12/2013

Product name: Dimethyl fumarate

(Contd. of page 3)

Body protection: Protective work clothing.

9 Physical and chemical properties

Information on basic physical and chemical properties

General Information

Appearance:

Form:	Crystalline powder
Color:	White to pale cream
Odor:	Not determined
Odor threshold:	Not determined.

pH-value:	Not applicable.
-----------	-----------------

Change in condition

Melting point/Melting range:	102-105 °C (216-221 °F)
Boiling point/Boiling range:	192-193 °C (378-379 °F)
Sublimation temperature / start:	Not determined
Flammability (solid, gaseous)	Not determined.
Ignition temperature:	Not determined
Decomposition temperature:	Not determined
Auto igniting:	Not determined.

Danger of explosion:	Not determined.
----------------------	-----------------

Explosion limits:

Lower:	Not determined
Upper:	Not determined
Vapor pressure:	Not applicable.
Density at 20 °C (68 °F):	1.37 g/cm ³ (11.433 lbs/gal)
Relative density	Not determined.
Vapor density	Not applicable.
Evaporation rate	Not applicable.
Solubility in / Miscibility with	
Water:	Insoluble
Partition coefficient (n-octanol/water):	Not determined.
Viscosity:	
dynamic:	Not applicable.
kinematic:	Not applicable.
Other information	No further relevant information available.

10 Stability and reactivity

Reactivity No information known.

Chemical stability Stable under recommended storage conditions.

Thermal decomposition / conditions to be avoided:

Decomposition will not occur if used and stored according to specifications.

Possibility of hazardous reactions Reacts with strong oxidizing agents

Incompatible materials:

Acids

Bases

Oxidizing agents

Reducing agents

Hazardous decomposition products: Carbon monoxide and carbon dioxide

11 Toxicological information

Information on toxicological effects

Acute toxicity:

Harmful in contact with skin.

Danger through skin absorption.

The Registry of Toxic Effects of Chemical Substances (RTECS) contains acute toxicity data for this substance.

LD/LC50 values that are relevant for classification:

Oral	LD50	2240 mg/kg (rat)
Dermal	LD50	1250 mg/kg (rabbit)

Skin irritation or corrosion: Causes skin irritation.

Eye irritation or corrosion: Causes serious eye irritation.

Sensitization: May cause an allergic skin reaction.

Germ cell mutagenicity: No effects known.

(Contd. on page 5)

USA

Safety Data Sheet

acc. to OSHA HCS

Printing date 01/22/2014

Reviewed on 04/12/2013

Product name: Dimethyl fumarate

(Contd. of page 4)

Carcinogenicity:

No classification data on carcinogenic properties of this material is available from the EPA, IARC, NTP, OSHA or ACGIH.

Reproductive toxicity: No effects known.**Specific target organ system toxicity - repeated exposure:** No effects known.**Specific target organ system toxicity - single exposure:** May cause respiratory irritation.**Aspiration hazard:** No effects known.**Subacute to chronic toxicity:**

The Registry of Toxic Effects of Chemical Substances (RTECS) contains multiple dose toxicity data for this substance.

Additional toxicological information:

To the best of our knowledge the acute and chronic toxicity of this substance is not fully known.

12 Ecological information**Toxicity****Aquatic toxicity:** No further relevant information available.**Persistence and degradability** No further relevant information available.**Behavior in environmental systems:****Bioaccumulative potential** No further relevant information available.**Mobility in soil** No further relevant information available.**Additional ecological information:****General notes:**

Do not allow material to be released to the environment without proper governmental permits. Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Avoid transfer into the environment.

Results of PBT and vPvB assessment**PBT:** Not applicable.**vPvB:** Not applicable.**Other adverse effects** No further relevant information available.**13 Disposal considerations****Waste treatment methods****Recommendation** Consult state, local or national regulations to ensure proper disposal.**Uncleaned packagings:****Recommendation:** Disposal must be made according to official regulations.**14 Transport information**

UN-Number	
DOT, ADR, ADN, IMDG, IATA	Not applicable
UN proper shipping name	
DOT, ADR, ADN, IMDG, IATA	Not applicable
Transport hazard class(es)	
DOT, ADR, ADN, IMDG, IATA	
Class	Not applicable
Packing group	
DOT, ADR, IMDG, IATA	Not applicable
Environmental hazards:	Not applicable.
Special precautions for user	Not applicable.
Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
Transport/Additional information:	
DOT	
Marine Pollutant (DOT):	No
UN "Model Regulation":	-

USA

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 01/22/2014

Reviewed on 04/12/2013

Product name: Dimethyl fumarate

(Contd. of page 5)

15 Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

All components of this product are listed in the U.S. Environmental Protection Agency Toxic Substances Control Act Chemical substance Inventory.

All components of this product are listed on the Canadian Non-Domestic Substances List (NDSL).

SARA Section 313 (specific toxic chemical listings) Substance is not listed.

California Proposition 65

Prop 65 - Chemicals known to cause cancer Substance is not listed.

Prop 65 - Developmental toxicity Substance is not listed.

Prop 65 - Developmental toxicity, female Substance is not listed.

Prop 65 - Developmental toxicity, male Substance is not listed.

Information about limitation of use: For use only by technically qualified individuals.

Other regulations, limitations and prohibitive regulations

Substances of very high concern (SVHC) according to REACH, Article 57

Substance is not listed.

REACH - Pre-registered substances Substance is listed.

Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

16 Other information

Employers should use this information only as a supplement to other information gathered by them, and should make independent judgement of suitability of this information to ensure proper use and protect the health and safety of employees. This information is furnished without warranty, and any use of the product not in conformance with this Material Safety Data Sheet, or in combination with any other product or process, is the responsibility of the user.

Department issuing SDS: Health, Safety and Environmental Department.

Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

DOT: US Department of Transportation

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

HMIS: Hazardous Materials Identification System (USA)

WHMIS: Workplace Hazardous Materials Information System (Canada)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

USA