

SAFETY DATA SHEET

1. Identification

Product identifier: HYDRAZINE SULFATE

Other means of identification

Product No.: 2177

Recommended use and restriction on use

Recommended use: Not available.

Restrictions on use: Not known.

Manufacturer/Importer/Supplier/Distributor information

Manufacturer

Company Name: Avantor Performance Materials, Inc.
Address: 3477 Corporate Parkway, Suite 200
Center Valley, PA 18034

Telephone: Customer Service: 855-282-6867

Fax:
Contact Person: Environmental Health & Safety
e-mail: info@avantormaterials.com

Emergency telephone number:

24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

2. Hazard(s) identification

Hazard classification

Health hazards

Acute toxicity (Oral)	Category 4
Acute toxicity (Dermal)	Category 3
Acute toxicity (Inhalation - dust and mist)	Category 3
Skin sensitizer	Category 1
Carcinogenicity	Category 1B

Environmental hazards

Acute hazards to the aquatic environment	Category 1
Chronic hazards to the aquatic environment	Category 1

Label elements

Hazard symbol:



Signal word: Danger

Hazard statement: Toxic in contact with skin or if inhaled.
Harmful if swallowed.
May cause an allergic skin reaction.
May cause cancer.
Very toxic to aquatic life with long lasting effects.

Precautionary statement

Prevention: Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wear protective gloves/protective clothing/eye protection/face protection. Do not breathe dust/fume/gas/mist/vapors/spray. Use only outdoors or in a well-ventilated area. Keep away from heat/sparks/open flames. - No smoking. Avoid release to the environment.

Response: Specific treatment (see this label). IF SWALLOWED: Call a POISON CENTER/doctor/ if you feel unwell. Rinse mouth. IF ON SKIN: Wash with plenty of soap and water. Call a POISON CENTER or doctor/physician if you feel unwell. If skin irritation or rash occurs: Get medical advice/attention. Take off immediately all contaminated clothing and wash it before reuse. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF exposed or concerned: Get medical advice/attention.

Storage: Store in a well-ventilated place. Keep container tightly closed. Store locked up.

Disposal: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Other hazards which do not result in GHS classification: None.

3. Composition/information on ingredients

Substances

Chemical identity	Common name and synonyms	CAS number	Content in percent (%)*
HYDRAZINE, SULFATE (1:1)		10034-93-2	99 - 100%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

General information: Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.

Ingestion: Call a physician or poison control center immediately. Do not induce vomiting without advice from poison control center.

Inhalation: Move to fresh air. Call a physician or poison control center immediately. If breathing stops, provide artificial respiration.

Skin contact: Immediately flush with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Call a physician or poison control center immediately. Wash contaminated clothing before reuse. Destroy or thoroughly clean contaminated shoes.

Eye contact: Flush thoroughly with water. If irritation occurs, get medical assistance.

Most important symptoms/effects, acute and delayed

Symptoms: Toxic in contact with skin. Toxic if inhaled. Harmful if swallowed. May cause allergic skin reaction.

Indication of immediate medical attention and special treatment needed

Treatment: Treat symptomatically. Symptoms may be delayed.

5. Fire-fighting measures

General fire hazards: In case of fire and/or explosion do not breathe fumes.

Suitable (and unsuitable) extinguishing media

Suitable extinguishing media: Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media: None known.

Specific hazards arising from the chemical: During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool. Cool containers exposed to flames with water until well after the fire is out.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: Keep unauthorized personnel away. Use personal protective equipment. See Section 8 of the MSDS for Personal Protective Equipment. Ventilate closed spaces before entering them. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.

Methods and material for containment and cleaning up: Sweep up and place in a clearly labeled container for chemical waste. Clean surface thoroughly to remove residual contamination. Dike far ahead of larger spill for later recovery and disposal.

Notification Procedures: Dike for later disposal. Prevent entry into waterways, sewer, basements or confined areas. Stop the flow of material, if this is without risk. Inform authorities if large amounts are involved.

Environmental precautions: Do not contaminate water sources or sewer. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling:	Use personal protective equipment as required. Do not get in eyes, on skin, on clothing. Do not breathe mist or vapor. Do not taste or swallow. Do not eat, drink or smoke when using the product. Use only with adequate ventilation. Wash hands thoroughly after handling. See Section 8 of the MSDS for Personal Protective Equipment.
Conditions for safe storage, including any incompatibilities:	Keep container tightly closed. Keep in a cool, well-ventilated place. Store in a dry place.

8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

None of the components have assigned exposure limits.

Appropriate engineering controls

No data available.

Individual protection measures, such as personal protective equipment

General information:	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. An eye wash and safety shower must be available in the immediate work area.
Eyeface protection:	Wear safety glasses with side shields (or goggles) and a face shield.
Skin protection	
Hand protection:	Chemical resistant gloves
Other:	Wear suitable protective clothing.
Respiratory protection:	In case of inadequate ventilation use suitable respirator.
Hygiene measures:	Provide eyewash station and safety shower. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.

9. Physical and chemical properties

Appearance

Physical state:	Solid
Form:	Crystalline Powder.
Color:	White
Odor:	Odorless
Odor threshold:	No data available.
pH:	1.3 (0.2 molar aqueous solution)
Melting point/freezing point:	254 °C
Initial boiling point and boiling range:	No data available.
Flash Point:	No data available.
Evaporation rate:	No data available.
Flammability (solid, gas):	No data available.

Upper/lower limit on flammability or explosive limits

Flammability limit - upper (%):	No data available.
Flammability limit - lower (%):	No data available.
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	No data available.
Vapor density:	No data available.
Relative density:	1.37 (20 °C)
Solubility(ies)	
Solubility in water:	30 g/l (20 °C)
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	No data available.
Auto-ignition temperature:	No data available.
Decomposition temperature:	No data available.
Viscosity:	No data available.

Other information

Molecular weight:	130.12 g/mol (H4N2)
-------------------	---------------------

10. Stability and reactivity

Reactivity:	No dangerous reaction known under conditions of normal use.
Chemical stability:	Material is stable under normal conditions.
Possibility of hazardous reactions:	Hazardous polymerization does not occur.
Conditions to avoid:	Excessive heat. Contact with incompatible materials.
Incompatible materials:	Strong oxidizing agents. Metals. Acids.
Hazardous decomposition products:	Oxides of sulfur. Nitrogen Oxides

11. Toxicological information

Information on likely routes of exposure

Ingestion:	Harmful if swallowed.
Inhalation:	Toxic by inhalation.
Skin contact:	Toxic in contact with skin.
Eye contact:	May cause irritation.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral	
Product:	LD 50 (Rat): 601 mg/kg
Dermal	
Product:	No data available.
Inhalation	
Product:	No data available.

Repeated dose toxicity

Product: No data available.

Skin corrosion/irritation

Product: May cause skin irritation.

Serious eye damage/eye irritation

Product: May irritate eyes.

Respiratory or skin sensitization

Product: May cause allergic skin reaction.

Carcinogenicity

Product: May cause cancer.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:

No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:

HYDRAZINE, Reasonably Anticipated to be a Human Carcinogen.
SULFATE (1:1)

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):

No carcinogenic components identified

Germ cell mutagenicity
In vitro

Product: No mutagenic components identified

In vivo

Product: No mutagenic components identified

Reproductive toxicity

Product: No components toxic to reproduction

Specific target organ toxicity - single exposure

Product: No data available.

Specific target organ toxicity - repeated exposure

Product: No data available.

Aspiration hazard

Product: Not classified

Other effects: None known.

12. Ecological information

Ecotoxicity:
Acute hazards to the aquatic environment:
Fish

Product: No data available.

Aquatic invertebrates

Product: No data available.

Chronic hazards to the aquatic environment:
Fish

Product: No data available.

Aquatic invertebrates

Product: No data available.

Toxicity to Aquatic Plants

Product: No data available.

Persistence and degradability
Biodegradation

Product: There are no data on the degradability of this product.

BOD/COD ratio

Product: No data available.

Bioaccumulative potential
Bioconcentration factor (BCF)

Product: No data available on bioaccumulation.

Partition coefficient n-octanol / water (log Kow)

Product: No data available.

Mobility in soil: No data available.

Known or predicted distribution to environmental compartments

HYDRAZINE, SULFATE
(1:1) No data available.

Other adverse effects: Very toxic to aquatic life with long lasting effects.

13. Disposal considerations

Disposal instructions: Discharge, treatment, or disposal may be subject to national, state, or local laws.

Contaminated packaging: Since emptied containers retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN number:	UN 3260
UN proper shipping name:	Corrosive solid, acidic, inorganic, n.o.s.(HYDRAZINE SULFATE)
Transport hazard class(es)	
Class(es):	8
Label(s):	8
Packing group:	III
Marine Pollutant:	No

IMDG

UN number:	UN 3260
UN proper shipping name:	CORROSIVE SOLID, ACIDIC, INORGANIC, N.O.S.(HYDRAZINE SULFATE)
Transport hazard class(es)	
Class(es):	8
Label(s):	8
EmS No.:	F-A, S-B
Packing group:	III
Marine Pollutant:	No

IATA

UN number:	UN 3260
Proper Shipping Name:	Corrosive solid, acidic, inorganic, n.o.s.(HYDRAZINE SULFATE)
Transport hazard class(es):	
Class(es):	8
Label(s):	8
Marine Pollutant:	No
Packing group:	III

15. Regulatory information
US federal regulations
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

None present or none present in regulated quantities.

Superfund amendments and reauthorization act of 1986 (SARA)
Hazard categories

☒ Acute (Immediate)	☒ Chronic (Delayed)	☐ Fire	☐ Reactive	☐ Pressure Generating
---	---	-------------------------------	-----------------------------------	--

SARA 302 Extremely hazardous substance

None present or none present in regulated quantities.

SARA 304 Emergency release notification

None present or none present in regulated quantities.

SARA 311/312 Hazardous chemical

Chemical identity	Threshold Planning Quantity
HYDRAZINE, SULFATE (1:1)	500 lbs

SARA 313 (TRI reporting)

Chemical identity	Reporting threshold for other users	Reporting threshold for manufacturing and processing
HYDRAZINE, SULFATE (1:1)	10000 lbs	25000 lbs.

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

None present or none present in regulated quantities.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

None present or none present in regulated quantities.

US state regulations

US. California Proposition 65

HYDRAZINE, SULFATE Carcinogenic.
(1:1)

US. New Jersey Worker and Community Right-to-Know Act

HYDRAZINE, SULFATE (1:1) Listed

US. Massachusetts RTK - Substance List

HYDRAZINE, SULFATE Listed
(1:1)

US. Pennsylvania RTK - Hazardous Substances

HYDRAZINE, SULFATE Listed
(1:1)

US. Rhode Island RTK

HYDRAZINE, SULFATE Listed
(1:1)

Inventory Status:

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	On or in compliance with the inventory
Japan (ENCS) List:	On or in compliance with the inventory
China Inv. Existing Chemical Substances:	Not in compliance with the inventory.
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Japan ISHL Listing:	On or in compliance with the inventory
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.

16. Other information, including date of preparation or last revision

NFPA Hazard ID



Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe

Issue date:	09-15-2014
Revision date:	No data available.
Version #:	1.1
Further information:	No data available.

Disclaimer:

THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED "AS IS," AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION<(>,<)> WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.