SAFETY DATA SHEET

1. Identification

Product identifier: 1,1,1,3,3,3-Hexafluoro-2-propanol

Other means of identification
Product No.: N151

Recommended use and restriction on use

Recommended use: Not available.
Restrictions on use: Not known.

Manufacturer/Importer/Supplier/Distributor Information

Manufacturer

Company Name:	Avantor Performance Materials, Inc.
Address:	3477 Corporate Parkway, Suite 200 Center Valley, PA 18034
Telephone:	Customer Service: 855-282-6867
Fax:	
Contact Person:	Environmental Health & Safety
e-mail:	info@avantormaterials.com

Emergency telephone number:
24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

2. Hazard(s) identification

Hazard Classification

Health Hazards

Acute toxicity (Oral)	Category 4
Acute toxicity (Inhalation - vapor)	Category 4
Skin Corrosion/Irritation	Category 1B
Serious Eye Damage/Eye Irritation	Category 1

Label Elements

Hazard Symbol:



Signal Word: Danger

Hazard Statement:
Harmful if swallowed.
Harmful if inhaled.
Causes severe skin burns and eye damage.

Precautionary Statement

Prevention: Wash hands thoroughly after handling. Do not eat, drink or smoke when

using this product. Use only outdoors or in a well-ventilated area. Do not breathe dust/fume/gas/mist/vapors/spray. Wear face protection and protective gloves/protective clothing

Response: IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell. IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Remove/take off immediately all contaminated clothing. Rinse skin with water/shower. Wash contaminated clothing before reuse. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor/physician.

Storage: Store locked up.

Disposal: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Other hazards which do not result in GHS classification: None.

3. Composition/information on ingredients

Substances

Chemical Identity	Common name and synonyms	CAS number	Content in percent (%)*
1,1,1,3,3,3-HEXAFLUORO-2-PROPANOL		920-66-1	60 - 100%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

General information: Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.

Ingestion: Get medical attention if symptoms occur. Do not induce vomiting without advice from poison control center. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.

Inhalation: Move to fresh air. Get medical attention if symptoms persist. If breathing stops, provide artificial respiration.

Skin Contact: Immediately flush with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Call a physician or poison control center immediately. Wash contaminated clothing before reuse. Destroy or thoroughly clean contaminated shoes.

Eye contact: Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Get medical attention immediately.

Most important symptoms/effects, acute and delayed

Symptoms: Causes severe skin and eye burns.

Indication of immediate medical attention and special treatment needed

Treatment: Treat symptomatically. Symptoms may be delayed.

5. Fire-fighting measures

General Fire Hazards: In case of fire and/or explosion do not breathe fumes.

Suitable (and unsuitable) extinguishing media

Suitable extinguishing media: Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media: None known.

Specific hazards arising from the chemical: Contact with metals may evolve flammable hydrogen gas. Fire may produce irritating, corrosive and/or toxic gases.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool. Cool containers exposed to flames with water until well after the fire is out.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: Keep unauthorized personnel away. Use personal protective equipment. See Section 8 of the MSDS for Personal Protective Equipment. Ventilate closed spaces before entering them. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.

Methods and material for containment and cleaning up: Absorb spill with vermiculite or other inert material, then place in a container for chemical waste. Clean surface thoroughly to remove residual contamination. Dike far ahead of larger spill for later recovery and disposal.

Notification Procedures: Dike for later disposal. Prevent entry into waterways, sewer, basements or confined areas. Stop the flow of material, if this is without risk. Inform authorities if large amounts are involved.

Environmental Precautions: Do not contaminate water sources or sewer. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling: Use personal protective equipment as required. Do not breathe mist or vapor. Do not taste or swallow. Do not eat, drink or smoke when using the product. Use only with adequate ventilation. Wash hands thoroughly after handling. See Section 8 of the MSDS for Personal Protective Equipment. Avoid contact with eyes. Avoid contact with skin. Do not breathe dust/fume/gas/mist/vapors/spray. Wear protective gloves/protective clothing/eye protection/face protection. Wash contaminated clothing before reuse.

Conditions for safe storage, including any incompatibilities: Store locked up. Keep in a cool, well-ventilated place. Store in a dry place.

8. Exposure controls/personal protection

Control Parameters

Occupational Exposure Limits

None of the components have assigned exposure limits.

Appropriate Engineering Controls No data available.

Individual protection measures, such as personal protective equipment

General information: Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. An eye wash and safety shower must be available in the immediate work area.

Eye/face protection: Wear safety glasses with side shields (or goggles) and a face shield.

Skin Protection

Hand Protection: Chemical resistant gloves

Other: Wear suitable protective clothing.

Respiratory Protection: In case of inadequate ventilation use suitable respirator.

Hygiene measures: Provide eyewash station and safety shower. Observe good industrial hygiene practices. Wash hands before breaks and immediately after handling the product. Do not eat, drink or smoke when using the product. Wash contaminated clothing before reuse.

9. Physical and chemical properties

Appearance

Physical state:	Liquid
Form:	No data available.
Color:	Colorless
Odor:	No data available.
Odor threshold:	No data available.
pH:	No data available.
Melting point/freezing point:	-4 °C
Initial boiling point and boiling range:	59 °C
Flash Point:	> 93 °C
Evaporation rate:	No data available.
Flammability (solid, gas):	No data available.
Upper/lower limit on flammability or explosive limits	
Flammability limit - upper (%):	No data available.
Flammability limit - lower (%):	No data available.
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	21.20 kPa (25 °C) 13.6 kPa (20 °C)
Vapor density:	No data available.
Relative density:	1.62 (20 °C)
Solubility(ies)	
Solubility in water:	7.77 g/l (25 °C) Appreciable

Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	1.66
Auto-ignition temperature:	No data available.
Decomposition temperature:	No data available.
Viscosity:	No data available.

Other information

Molecular weight:	168.04 g/mol (C3H2F6O)

10. Stability and reactivity

Reactivity:	No dangerous reaction known under conditions of normal use.
Chemical Stability:	Material is stable under normal conditions.
Possibility of Hazardous Reactions:	Hazardous polymerization does not occur.
Conditions to Avoid:	Heat, sparks, flames. Contact with incompatible materials.
Incompatible Materials:	Strong oxidizing agents. Acids. Bases. Alkalies. Aluminum. Chlorides. Zinc.
Hazardous Decomposition Products:	Thermal decomposition may release oxides of carbon. Hydrogen fluoride. By heating and fire, toxic vapors/gases may be formed.

11. Toxicological information

Information on likely routes of exposure

Ingestion:	Harmful if swallowed.
Inhalation:	Harmful if inhaled.
Skin Contact:	Causes severe skin burns.
Eye contact:	Causes serious eye damage.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral

Product:	LD 50 (Mouse): 600 mg/kg

Dermal

Product:	No data available.

Inhalation

Product:	LC 50 (Rat, 4 h): 1974 ppm

Repeated Dose Toxicity

Product:	No data available.

Skin Corrosion/Irritation

Product:	Causes severe skin burns.

Serious Eye Damage/Eye Irritation

Product:	Causes serious eye damage.

Respiratory or Skin Sensitization

Product:	Not a skin sensitizer.

Carcinogenicity

Product: This substance has no evidence of carcinogenic properties.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:
No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:
No carcinogenic components identified

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):
No carcinogenic components identified

Germ Cell Mutagenicity

In vitro
Product: No mutagenic components identified

In vivo
Product: No mutagenic components identified

Reproductive Toxicity
Product: No components toxic to reproduction

Specific Target Organ Toxicity - Single Exposure
Product: No data available.

Specific Target Organ Toxicity - Repeated Exposure
Product: No data available.

Aspiration Hazard
Product: Not classified

Other Effects: None known.

12. Ecological information

Ecotoxicity:

Acute hazards to the aquatic environment:

Fish
Product: No data available.

Specified substance(s):

1,1,1,3,3,3-HEXAFLUORO-2-PROPANOL	LC 50 (Fathead minnow (Pimephales promelas), 96 h): 224 - 266 mg/l Mortality

Aquatic Invertebrates
Product: No data available.

Chronic hazards to the aquatic environment:

Fish
Product: No data available.

Aquatic Invertebrates
Product: No data available.

Toxicity to Aquatic Plants
Product: No data available.

Persistence and Degradability

Biodegradation
Product: There are no data on the degradability of this product.

BOD/COD Ratio
Product: No data available.

Bioaccumulative Potential
Bioconcentration Factor (BCF)
Product: No data available on bioaccumulation.

Partition Coefficient n-octanol / water (log Kow)
Product: Log Kow: 1.66

Mobility in Soil: The product is water soluble and may spread in water systems.

Other Adverse Effects: The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

13. Disposal considerations

Disposal instructions: Discharge, treatment, or disposal may be subject to national, state, or local laws. Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Contaminated Packaging: Since emptied containers retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN Number:	UN 1760
UN Proper Shipping Name:	Corrosive liquids, n.o.s.(HEXAFLUORO-2-PROPANOL)
Transport Hazard Class(es)	
Class(es):	8
Label(s):	8
Packing Group:	II
Marine Pollutant:	No

IMDG

UN Number:	UN 1760
UN Proper Shipping Name:	CORROSIVE LIQUID, N.O.S.(HEXAFLUORO-2-PROPANOL)
Transport Hazard Class(es)	
Class(es):	8
Label(s):	8
EmS No.:	F-A, S-B
Packing Group:	II
Marine Pollutant:	No

IATA

UN Number:	UN 1760
Proper Shipping Name:	Corrosive liquid, n.o.s.(HEXAFLUORO-2-PROPANOL)
Transport Hazard Class(es):	
Class(es):	8
Label(s):	8
Marine Pollutant:	No
Packing Group:	II

15. Regulatory information

US Federal Regulations

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

None present or none present in regulated quantities.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

X	Acute (Immediate)		Chronic (Delayed)		Fire		Reactive		Pressure Generating

SARA 302 Extremely Hazardous Substance

None present or none present in regulated quantities.

SARA 304 Emergency Release Notification

None present or none present in regulated quantities.

SARA 311/312 Hazardous Chemical

Chemical Identity	Threshold Planning Quantity
1,1,1,3,3,3-HEXAFLUORO-2-PROPANOL	500 lbs

SARA 313 (TRI Reporting)

None present or none present in regulated quantities.

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

None present or none present in regulated quantities.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

None present or none present in regulated quantities.

US State Regulations

US. California Proposition 65

No ingredient regulated by CA Prop 65 present.

US. New Jersey Worker and Community Right-to-Know Act

No ingredient regulated by NJ Right-to-Know Law present.

US. Massachusetts RTK - Substance List

No ingredient regulated by MA Right-to-Know Law present.

US. Pennsylvania RTK - Hazardous Substances

No ingredient regulated by PA Right-to-Know Law present.

US. Rhode Island RTK

No ingredient regulated by RI Right-to-Know Law present.

Inventory Status:

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	On or in compliance with the inventory
Japan (ENCS) List:	On or in compliance with the inventory
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	Not in compliance with the inventory.
Japan ISHL Listing:	On or in compliance with the inventory
Japan Pharmacopoeia Listing:	On or in compliance with the inventory

16.Other information, including date of preparation or last revision

NFPA Hazard ID



Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe

Issue Date:	12-05-2014
Revision Date:	No data available.
Version #:	1.0
Further Information:	No data available.

Disclaimer:

THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED “AS IS,” AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION<(>,<)> WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.