



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 06/25/2014

Version 1.2

SECTION 1. Identification

Product identifier

Product number	807048
Product name	3-Methylpyridine for synthesis
CAS-No.	108-99-6

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 3, H226
Acute toxicity, Category 4, Inhalation, H332
Acute toxicity, Category 3, Dermal, H311
Acute toxicity, Category 4, Oral, H302
Specific target organ systemic toxicity - single exposure, Category 3, H335
Skin irritation, Category 2, H315
Eye irritation, Category 2, H319
For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807048
Product name 3-Methylpyridine for synthesis

Version 1.2

Hazard Statements

H226 Flammable liquid and vapor.
H302 + H332 Harmful if swallowed or if inhaled.
H311 Toxic in contact with skin.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

Precautionary Statements

P210 Keep away from heat.
P280 Wear protective gloves/ protective clothing.
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308 + P310 IF exposed or concerned: immediately call a POISON CENTER or doctor/ physician.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200). This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS and may deviate from the GHS information.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	3-(CH ₃)C ₅ H ₄ N	C ₆ H ₇ N (Hill)
Molar mass	93.13 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

3-methylpyridine (>= 90 % - <= 100 %)

108-99-6

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air. If breathing stops: mouth-to-mouth breathing or artificial respiration. Oxygen if necessary. Immediately call in physician.

Skin contact

In case of skin contact: Take off immediately all contaminated clothing. Rinse skin with water/ shower. Call a physician immediately.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807048
Product name 3-Methylpyridine for synthesis

Version 1.2

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Drowsiness, muscular weakness, irritant effects

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air at elevated temperatures.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

nitrous gases

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

Suppress (knock down) gases/vapors/mists with a water spray jet. Cool closed containers exposed to fire with water spray.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Keep away from heat and sources of ignition. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807048
Product name 3-Methylpyridine for synthesis

Version 1.2

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Work under hood. Do not inhale substance/mixture. Avoid generation of vapors/aerosols.

Observe label precautions.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition. Keep locked up or in an area accessible only to qualified or authorized persons.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Flame retardant antistatic protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807048
Product name 3-Methylpyridine for synthesis

Version 1.2

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	pyridine-like
Odor Threshold	No information available.
pH	10 at 100 g/l 68 °F (20 °C)
Melting point	-18 °C
Boiling point/boiling range	291 °F (144 °C) at 1,013 hPa
Flash point	104 °F (40 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	1.3 %(V)
Upper explosion limit	8.7 %(V)
Vapor pressure	6 hPa
Relative vapor density	3.21
Density	0.96 g/cm ³ at 68 °F (20 °C)
Relative density	No information available.
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	log Pow: 1.20 (experimental) Bioaccumulation is not expected. (Lit.)
Autoignition temperature	No information available.
Decomposition temperature	No information available.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	807048	Version 1.2
Product name	3-Methylpyridine for synthesis	

Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.
Oxidizing properties	none

SECTION 10. Stability and reactivity

Reactivity

Vapor/air-mixtures are explosive at intense warming.
A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Chemical stability

sensitive to moisture

Possibility of hazardous reactions

A risk of explosion and/or of toxic gas formation exists with the following substances:
Oxidizing agents, hydrogen peroxide, sulfuric acid, Metals, acids

Conditions to avoid

Heating.

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Inhalation, Eye contact, Skin contact

Acute oral toxicity

LD50 rat: 400 - 800 mg/kg (External MSDS)

absorption

Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract.

Acute inhalation toxicity

LC50 rat: 16.84 mg/l; 4 h (External MSDS)

absorption

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages:, damage of respiratory tract

Acute dermal toxicity

LD50 rabbit: 200 - 1,000 mg/kg
(External MSDS)

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807048
Product name 3-Methylpyridine for synthesis

Version 1.2

absorption

Skin irritation

rabbit

Result: Severe irritations
(RTECS)

Causes skin irritation.

Eye irritation

rabbit

Result: Severe irritations
(RTECS)

Causes serious eye irritation.

Genotoxicity in vitro

Mutagenicity (mammal cell test): micronucleus.

Result: negative
(National Toxicology Program)

Ames test

Salmonella typhimurium

Result: negative
(National Toxicology Program)

Specific target organ systemic toxicity - single exposure

May cause respiratory irritation.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

After absorption:

Drowsiness, muscular weakness, Lung edema

Other dangerous properties can not be excluded.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807048
Product name 3-Methylpyridine for synthesis

Version 1.2

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 Pimephales promelas (fathead minnow): 131 - 160 mg/l; 96 h (ECOTOX Database)

Toxicity to daphnia and other aquatic invertebrates

EC50 Tetrahymen pyriformis: 584 - 1,608 mg/l; 72 h (ECOTOX Database)

Persistence and degradability

No information available.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 1.20

(experimental)

Bioaccumulation is not expected. (Lit.)

Mobility in soil

No information available.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 2313
Proper shipping name	PICOLINES
Class	3
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 2313
Proper shipping name	PICOLINES
Class	3
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	807048	Version 1.2
Product name	3-Methylpyridine for synthesis	

UN number	UN 2313
Proper shipping name	PICOLINES
Class	3
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-E S-D

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Combustible Liquid
Toxic by ingestion
Highly toxic by skin absorption
Skin irritant
Eye irritant
Moderate respiratory irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard
Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 807048
Product name 3-Methylpyridine for synthesis

Version 1.2

Ingredients

3-methylpyridine

New Jersey Right To Know

Ingredients

3-methylpyridine

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H226	Flammable liquid and vapor.
H302	Harmful if swallowed.
H311	Toxic in contact with skin.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 06/25/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.