

# Safety Data Sheet

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

# **SECTION 1: Identification**

#### **Product identifier**

Trade name/designation: Fluoride standard 1 mg/ml

Product No.: BDH7406

Substance name:

CAS No.:

INDEX No.: 000-000-00-0

REACH registration No.: Not yet communicated down the supply chain.

Other means of identification:

# Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses: General chemical reagent

# Details of the supplier of the safety data sheet

#### VWR International, LLC

Street 100 Matsonford Road
Postal code/city Radnor, PA 19087-8660

Telephone 610-386-1700 E-mail www.vwr.com

### **Emergency telephone**

Telephone +1-800-424-9300 (Chemtrec, 24 hrs/day, 7 days/week, USA)

#### VWR International Co.

Street 2360 Argentia Road
Postal code/city Mississauga, ON, L5N 5Z7

Telephone 800-932-5000 E-mail www.vwr.com

#### **Emergency telephone**

Telephone +1-613-996-6666 (Canutec, 24 hrs/day, 7 days/week, Canada)



# SECTION 2: Hazards identification

# Classification of the substance or mixture Classification according GHS

Hazard classes and hazard categories			Hazard statements
Classification according to Directive 67/548/EEC or 1999/45/EC			
Label elements			
Labelling according GHS			
Hazard pictograms			
no data available			
Signal word: no data available			
Hazard statements			
Precautionary			
statements			
Labelling (67/548/EEC or 1999/45/EC)			
Hazard symbols			
no data available			
R-phrases			
S-phrases			
Other hazards			
SVHC No			



# **SECTION 3: Composition / information on ingredients**

Hazardous ingredients Classification according to the OSHA Hazard Communication Standard 29 CFR 1910.1200

This product does not contain any hazardous ingredients.

# **SECTION 4: First aid measures**

#### **General information**

When in doubt or if symptoms are observed, get medical advice. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### After inhalation

Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tract irritation, consult a physician.

#### In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

#### In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

#### Most important symptoms and effects, both acute and delayed

no data available

#### Indication of any immediate medical attention and special treatment needed

no data available

# Self-protection of the first aider

First aider: Pay attention to self-protection!

#### Information to physician

no data available

# **SECTION 5: Firefighting measures**

### **Extinguishing media**

#### Suitable extinguishing media

Co-ordinate fire-fighting measures to the fire surroundings.

#### Extinguishing media which must not be used for safety reasons

no data available

#### Special hazards arising from the substance or mixture

In case of fire may be liberated: Pyrolysis products, toxic

#### Advice for firefighters

DO NOT fight fire when fire reaches explosives. In case of fire: Wear self-contained breathing apparatus.



#### **Additional information**

Do not allow run-off from fire-fighting to enter drains or water courses. Do not inhale explosion and combustion gases. Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen. Use water spray jet to protect personnel and to cool endangered containers.

#### **SECTION 6: Accidental release measures**

#### Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety. Use personal protection equipment. Stop leak if safe to do so. Eliminate all ignition sources if safe to do so.

#### **Environmental precautions**

Do not allow to enter into surface water or drains. Discharge into the environment must be avoided. Ensure waste is collected and contained

# Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Clean contaminated objects and areas thoroughly observing environmental regulations. Collect in closed and suitable containers for disposal.

#### **Additional information**

Clear spills immediately.

# **SECTION 7: Handling and storage**

# Precautions for safe handling

All work processes must always be designed so that the following is as low as possible: Inhalation skin contact Eye contact Use extractor hood (laboratory). If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

#### Conditions for safe storage, including any incompatibilities

storage temperature:

Storage class:

Keep in a cool, well-ventilated place. Keep/Store only in original container.

#### Specific end use(s)

no data available

# SECTION 8: Exposure controls/personal protection

#### **Control parameters**

Does not contain substances above concentration limits fixing an occupational exposure limit.

# **Exposure controls**

#### **Appropriate engineering controls**

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

#### Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn. For the protection against direct skin contact, body protective clothing is essential (in addition to the usual working clothes).

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

Skin protection





#### no data available

#### By short-term hand contact

Suitable material:

Thickness of the glove material:

Breakthrough time (maximum wearing time):

Recommended glove articles:

no data available
no data available

#### By long-term hand contact

Suitable material:

Thickness of the glove material:

Breakthrough time (maximum wearing time):

Recommended glove articles:

no data available
no data available

#### Respiratory protection

no data available

Suitable respiratory protection apparatus:

Recommendation: no data available
Suitable material: no data available
Recommendation: no data available

# Additional information

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

Environmental exposure controls



# **SECTION 9: Physical and chemical properties**

# Information on basic physical and chemical properties

(a) Appearance

Physical state: liquid

Colour: no data available
(b) Odour: no data available
(c) Odour threshold: no data available

# Safety relevant basic data

(d) pH: no data available
(e) Melting point/freezing point: no data available
(f) Initial boiling point and boiling range: no data available
(g) Flash point: no data available
(h) Evaporation rate: no data available
(i) Flammability (solid, gas): not applicable

(j) Upper/lower flammability or explosive limits

Lower explosion limit:
Upper explosion limit:
no data available
no data available
(k) Vapour pressure:
no data available
(l) Vapour density:
no data available
(m) Relative density:
no data available

(n) Solubility(ies)

at 20 °C: no data available
Soluble (g/L) in: no data available
(o) Partition coefficient: n-octanol/water: no data available
(p) Auto-ignition temperature: no data available
(q) Decomposition temperature: no data available

(r) Viscosity

Kinematic viscosity: no data available
Dynamic viscosity: no data available
(s) Explosive properties: not applicable
(t) Oxidising properties: not applicable

#### Other information

Bulk density: no data available
Refraction index: no data available
Dissociation constant: no data available
Surface tension: no data available
Henry constant: no data available

# **SECTION 10: Stability and reactivity**

#### Reactivity

no data available

#### **Chemical stability**



# Possibility of hazardous reactions

no data available

#### **Conditions to avoid**

no data available

#### **Incompatible materials**

no data available

#### **Hazardous decomposition products**

no data available

#### **Additional information**

no data available

# SECTION 11: Toxicological information

# Information on toxicological effects

#### **Acute effects**

Acute oral toxicity: no data available

Acute dermal toxicity: no data available

Acute inhalation toxicity: no data available

#### Irritant and corrosive effects

Primary irritation to the skin: not applicable

Irritation to eyes:

not applicable

Irritation to respiratory tract: not applicable

#### Respiratory or skin sensitisation

In case of skin contact: not sensitising After inhalation: not sensitising

#### STOT-single exposure

not applicable

#### STOT-repeated exposure

not applicable

# CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

# Carcinogenicity

No indication of human carcinogenicity.

#### Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.



#### Reproductive toxicity

No indications of human reproductive toxicity exist.

#### **Aspiration hazard**

not applicable

#### Other adverse effects

no data available

#### Additional information

no data available

# **SECTION 12: Ecological information**

#### **Ecotoxicity**

#### Acute (short-term) fish toxicity:

no data available

#### Chronic (long-term) fish toxicity:

no data available

#### Acute (short-term) daphnia toxicity:

no data available

## Chronic (long-term) daphnia toxicity:

no data available

#### Acute (short-term) algae toxicity:

no data available

# Chronic (long-term) algae toxicity:

no data available

# Persistence and degradability

no data available

#### **Bioaccumulative potential**

Partition coefficient: n-octanol/water: no data available

# Mobility in soil:

no data available

# Results of PBT/vPvB assessment

no data available

# Other adverse effects



# **SECTION 13: Disposal considerations**

#### Waste treatment methods

#### Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

#### Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

#### Additional information

no data available

# **SECTION 14: Transport information**

#### Land transport (ADR/RID/DOT)

No dangerous good in sense of this transport regulation.

#### Sea transport (IMDG)

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code not relevant

#### Air transport (ICAO-TI / IATA-DGR)

No dangerous good in sense of this transport regulation.

# **SECTION 15: Regulatory information**

# Safety, health and environmental regulations/legislation specific for the substance or mixture

#### **General rules**

Water hazard class (WGK):

no data available

#### **California Prop 65 Components**

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

## **Chemical Safety Assessment**



# **SECTION 16: Other information**

#### Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygiensts

ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road

AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)

CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures

DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)

DOT – U.S. Department of Transportation

Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)

IATA-DGR - International Air Transport Association-Dangerous Goods Regulations

ICAO-TI - International Civil Aviation Organization-Technical Instructions

IMDG - International Maritime Code for Dangerous Goods

LTV - Long Term Value

NIOSH - National Institute for Occupational Safety and Health

OSHA - Occupational Safety & Health Administration

PBT - Persistent, Bioaccumulative and Toxic

RID - Regulation concerning the International Carriage of Dangerous Goods by Rail

STV - Short Term Value

SVHC - Substances of Very High Concern

vPvB - very Persistent, very Bioaccumulative

#### Additional information

Indication of changes: general update

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.