	Revision Date 04/18/2014	Version 1.2
SECTION 1.Identification		
Product identifier		
Product number	100921	
Product name	Diethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur	
Synonyms	Et2O	
CAS-No.	60-29-7	
Relevant identified uses of t	he substance or mixture and uses advised against	
Identified uses	Reagent for analysis, Chemical production	
Details of the supplier of the	e safety data sheet	
Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821 United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)	,
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week	

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 1, H224 Acute toxicity, Category 4, Oral, H302

Specific target organ systemic toxicity - single exposure, Category 3, Central nervous system, H336 For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word Danger

Hazard Statements H224 Extremely flammable liquid and vapor.

Product number	100921	Version
Product name	Diethyl ether for analysis EMSURE® ACS, ISO, Reag. Ph Eur	

H302 Harmful if swallowed. H336 May cause drowsiness or dizziness.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking. P240 Ground/bond container and receiving equipment. P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200). This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS and may deviate from the GHS information.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	(C₂H₅)₂O	C₄H₁₀O (Hill)
Synonyms	Et2O	
Molar mass	74.12 g/mol	

Hazardous ingredients

Chemical Name (Concentration) CAS-No. *Diethyl ether (>= 90 % - <= 100 %)* 60-29-7

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air. If necessary, apply artificial respiration. Keep respiratory tract clear.

Skin contact After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: caution if victim vomits. Risk of aspiration! Keep airways free. Pulmonary failure possible after aspiration of vomit. Call a physician immediately.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, respiratory paralysis, Drowsiness, Unconsciousness, inebriation, euphoria, collapse, drowziness, ataxia (impaired locomotor coordination), Salivation, Coma, death Repeated exposure may cause skin dryness or cracking.

Indication of any immediate medical attention and special treatment needed

1.2

Product number	100921	Version 1.2
Product name	Diethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur	

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible. Vapors are heavier than air and may spread along floors. Forms explosive mixtures with air at ambient temperatures. Pay attention to flashback. Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system. Remove container from danger zone and cool with water.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Keep away from heat and sources of ignition. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not let product enter drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Work under hood. Do not inhale substance/mixture. Avoid generation of vapors/aerosols.

Observe label precautions.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Product number	100921	Version 1.2
Product name	Diethyl ether for analysis EMSURE® ACS, ISO, Reag. Ph Eur	

Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition. Protected from light.

Store at +5°C to +30°C (+41°F to +86°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

 Ingredients			
Basis	Value	Threshold limits	Remarks
Diethyl ether 60	0-29-7		
ACGIH	Time Weighted Average (TWA):	400 ppm	
	Short Term Exposure Limit (STEL):	500 ppm	
OSHA_TRANS	PEL:	400 ppm	
		1,200 mg/m ³	
Z1A	Time Weighted Average	400 ppm	
	(TWA):	1,200 mg/m³	
	Short Term Exposure	500 ppm	
	Limit (STEL):	1,500 mg/m ³	

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Flame retardant antistatic protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

Product number Product name	100921 Diethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur	Version 1.2
ECTION 9. Physical and chemi	cal properties	
Physical state	liquid	
Color	colorless	
Odor	characteristic	
Odor Threshold	0.3 - 8.8 ppm	
рН	No information available.	
Melting point	-116.3 °C	
Boiling point/boiling range	94.3 °F (34.6 °C) at 1,013 hPa	
Flash point	-40 °F (-40 °C) Method: c.c.	
Evaporation rate	No information available.	
Flammability (solid, gas)	No information available.	
Lower explosion limit	1.7 %(V)	
Upper explosion limit	36 %(V)	
Vapor pressure	587 hPa at 68 °F (20 °C)	
Relative vapor density	No information available.	
Density	0.71 g/cm ³	
Relative density	No information available.	
Water solubility	69 g/l at 68 °F (20 °C)	
Partition coefficient: n- octanol/water	log Pow: 0.89 (experimental) (Lit.) Bioaccumulation is not expected.	
Autoignition temperature	No information available.	
Decomposition temperature	Distillable in an undecomposed state at normal pressure.	

Product number Product name	100921 Version 1.2 Diethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur Version 1.2	
Viscosity, dynamic	0.23 mPa.s at 68 °F (20 °C)	
Explosive properties	Not classified as explosive.	
Oxidizing properties	none	
Ignition temperature	356 °F (180 °C) Method: DIN 51794	

SECTION 10. Stability and reactivity

Reactivity

Vapors may form explosive mixture with air. Formation of peroxides possible.

Chemical stability

Sensitivity to light Sensitive to air.

Stabilizer butyl hydroxytoluene (BHT)

Possibility of hazardous reactions

Risk of explosion with:

azides, halogens, halogen-halogen compounds, nonmetals, nonmetallic oxyhalides, Strong oxidizing agents, chromium(VI) oxide, halogen oxides, peroxi compounds, perchloric acid, perchlorates, Nitric acid, nitrating acid, Oxygen, Ozone, turpentine oils and/or turpentine substitutes, nitrates, metallic chlorides

Risk of ignition or formation of inflammable gases or vapors with:

chromyl chloride, Peroxides

Conditions to avoid

Warming.

Incompatible materials

rubber, various plastics

Hazardous decomposition products

Peroxides

SECTION 11. Toxicological information

Information on toxicological effects *Likely route of exposure* Inhalation, Eye contact, Skin contact, Ingestion *Target Organs* Eyes Skin Respiratory system

oduct number oduct name	100921 Diethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur	Version 1
Central nervous system		
Acute oral toxicity		
LDLO human: 260 mg/k	g (RTECS)	
LD50 rat: 1,215 mg/kg (RTECS)	
absorption Symptoms: Risk of aspir pneumonitis.	ation upon vomiting., Aspiration may cause pulmonary edema and	
Acute inhalation toxicity absorption		
Symptoms: mucosal irrit	ations	
Acute dermal toxicity LD50 rabbit: > 2,000 mg (ECHA)	ŋ/kg	
Skin irritation		
rabbit		
Result: No irritation OECD Test Guideline 40)4	
Dermatitis Repeated exposure may	cause skin dryness or cracking.	
Eye irritation		
rabbit Result: No eye irritation		
OECD Test Guideline 40)5	
Sensitization		
Sensitization test: mouse	9	
Result: negative Method: OECD Test Gui	deline 429	
Human experience		
Result: negative		
(Lit.)		
<i>Genotoxicity in vivo</i> mouse		
Result: negative		
Method: OECD Test Gui	deline 474	
Genotoxicity in vitro		
Ames test Salmonella typhimurium		
Result: negative (IUCLID)		
Mutagenicity (mammal c	ell test): chromosome aberration.	
Human lymphocytes Result: negative		
i toount nogutivo	deline 405	

Product number	100921 Distbyl ather for apolysis EMSURE® ACS ISO Boog, Dh Eur	Version 1.2
Product name	Diethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur	
Mutagenicity (mammal co MOUSE LYMPHOMA TE Result: negative Method: OECD Test Guid	ST	
<i>Specific target organ sys</i> Target Organs: Central n May cause drowsiness o	•	
	<i>temic toxicity - repeated exposure</i> e is not classified as specific target organ toxicant, repeated exposure.	
<i>Aspiration hazard</i> Regarding the available	data the classification criteria are not fulfilled.	
Carcinogenicity		
IARC	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as probable, possible or confirmed	
	human carcinogen by IARC.	
OSHA	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as a carcinogen or potential	
	carcinogen by OSHA.	
NTP	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as a known or anticipated carcinogen	
	by NTP.	
ACGIH	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as a carcinogen or potential	
	carcinogen by ACGIH.	
Unconsciousness, Coma	kia (impaired locomotor coordination), inebriation, collapse,	
Cannot be excluded:		

respiratory paralysis, death

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish LC50 Leuciscus idus (Golden orfe): 2,840 mg/l; 48 h (ECOTOX Database) *Toxicity to daphnia and other aquatic invertebrates* EC50 Daphnia magna (Water flea): 1,380 mg/l; 48 h (IUCLID) *Toxicity to algae*

static test EC50 Desmodesmus subspicatus (green algae): > 100 mg/l; 72 h OECD Test Guideline 201

Product number	100921	Version 1.2
Product name	Diethyl ether for analysis EMSURE® ACS, ISO, Reag. Ph Eur	

Toxicity to bacteria static test EC50 activated sludge: 21,000 mg/l; 3 h OECD Test Guideline 209

static test NOEC activated sludge: 42 mg/l; 3 h OECD Test Guideline 209

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) semi-static test NOEC Daphnia magna (Water flea): > 100 mg/l; 21 d

OECD Test Guideline 211

Persistence and degradability

Biodegradability

Not readily biodegradable.

Bioaccumulative potential

Partition coefficient: n-octanol/water log Pow: 0.89 (experimental) (Lit.) Bioaccumulation is not expected.

Mobility in soil

No information available.

Other adverse effects

Henry constant 124.6 Pa*m³/mol Method: (experimental) (Lit.) Distribution preferentially in air.

Additional ecological information Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)	
UN number	UN 1155
Proper shipping name	DIETHYL ETHER
Class	3
Packing group	I
Environmentally hazardous	
Air transport (IATA)	

100921	Version 1.2
Diethyl ether for analysis EMSURE® ACS, ISO, Reag. Ph Eur	
UN 1155	
DIETHYL ETHER	
3	
I	
no	
UN 1155	
DIETHYL ETHER	
3	
I	
yes	
F-E S-D	
	Diethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur UN 1155 DIETHYL ETHER 3 I no UN 1155 DIETHYL ETHER 3 I yes

SECTION 15. Regulatory information

United States of America

OSHA Hazards Flammable Liquid Harmful if swallowed. Target organ effects Eye irritant Skin irritant Respiratory irritant Harmful if inhaled.

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard Acute Health Hazard Chronic Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SAFETY DATA SHEET
according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	100921	Version 1.2
Product name	Diethyl ether for analysis EMSURE® ACS, ISO, Reag. Ph Eur	

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I Not listed

DEA List II

Listed *Ingredients* Diethyl ether

60-29-7

US State Regulations

Massachusetts Right To Know

Ingredients Diethyl ether

Pennsylvania Right To Know

Ingredients Diethyl ether

New Jersey Right To Know Ingredients

Diethyl ether

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	All components of the product are listed in the TSCA-inventory.
DSL:	All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H224	Extremely flammable liquid and vapor.
H302	Harmful if swallowed.
H336	May cause drowsiness or dizziness.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Product number100921VerProduct nameDiethyl ether for analysis EMSURE® ACS,ISO,Reag. Ph Eur

Revision Date 04/18/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.

Version 1.2