



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 02/09/2015

Version 1.2

SECTION 1. Identification

Product identifier

Product number	814868
Product name	Trioctylphosphinoxide for synthesis
CAS-No.	78-50-2

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Eye irritation, Category 2A, H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word

Warning

Hazard Statements

H319 Causes serious eye irritation.

Precautionary Statements

P264 Wash skin thoroughly after handling.

P280 Wear protective gloves/ eye protection/ face protection.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 814868
Product name Trioctylphosphinoxide for synthesis

Version 1.2

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337 + P313 If eye irritation persists: Get medical advice/ attention.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	(C ₈ H ₁₇) ₃ PO	C ₂₄ H ₅₁ OP (Hill)
Molar mass	386.64 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

tri-n-octylphosphine oxide (>= 90 % - <= 100 %)

78-50-2

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Shortness of breath, gastric pain, Dizziness, Nausea, Vomiting, Irritation and corrosion

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Foam, Dry powder, Water

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 814868
Product name Trioctylphosphinoxide for synthesis

Version 1.2

Combustible material

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

phosphines, Oxides of phosphorus

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

Suppress (knock down) gases/vapors/mists with a water spray jet.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Avoid inhalation of dusts. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

814868

Version 1.2

Product name

Trioctylphosphinoxide for synthesis

Hygiene measures

Change contaminated clothing. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	crystals
Color	white
Odor	sweet
Odor Threshold	No information available.
pH	No information available.
Melting point	50 - 54 °C
Boiling point/boiling range	414 °F (212 °C) at 39.99 Pa
Flash point	486 °F (252 °C)
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	0.88 g/cm ³ at 77 °F (25 °C)

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

814868

Version 1.2

Product name

Trioctylphosphinoxide for synthesis

Relative density	No information available.
Water solubility	< 1 g/l at 68 °F (20 °C)
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	No information available.
Oxidizing properties	No information available.
Ignition temperature	608 °F (320 °C)

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

sensitive to moisture

Possibility of hazardous reactions

Violent reactions possible with:

Oxidizing agents

Conditions to avoid

Strong heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 814868
Product name Trioctylphosphinoxide for synthesis

Version 1.2

Acute oral toxicity

LD50 Rat: > 10,000 mg/kg (External MSDS)

Acute dermal toxicity

LD50 Rat: 2,830 mg/kg
(External MSDS)

Skin irritation

Rabbit

Result: slight irritation
(RTECS)

Eye irritation

Rabbit

Result: Eye irritation
(RTECS)

Causes serious eye irritation.

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

After uptake of large quantities:

Nausea, Vomiting, Dizziness, Shortness of breath, gastric pain

Further data:

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 814868
Product name Trioctylphosphin oxide for synthesis

Version 1.2

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 *Lepomis macrochirus* (Bluegill sunfish): > 11.3 mg/l; 96 h (Hommel)

Toxicity to daphnia and other aquatic invertebrates

EC50 *Daphnia magna* (Water flea): 4.11 mg/l; 48 h (Hommel)

Toxicity to algae

IC50 *Scenedesmus capricornutum* (fresh water algae): 1.87 mg/l; 96 h (Hommel)

Persistence and degradability

Biodegradability

62.6 %; 28 d; aerobic

(Hommel)

Not readily biodegradable.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number UN 3077

Proper shipping name ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.

Class 9

Packing group III

Environmentally hazardous --

Air transport (IATA)

UN number UN 3077

Proper shipping name ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (TRIOCTYLPHOSPHINE OXIDE)

Class 9

Packing group III

Environmentally hazardous --

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

814868

Version 1.2

Product name

Trioctylphosphin oxide for synthesis

Special precautions for user

no

Sea transport (IMDG)

UN number

UN 3077

Proper shipping name

ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID,
N.O.S. (TRIOCTYLPHOSPHINE OXIDE)

Class

9

Packing group

III

Environmentally hazardous

--

Special precautions for user

yes

EmS

F-A S-F

SECTION 15. Regulatory information

United States of America

SARA 313

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 814868
Product name Trioctylphosphinoxide for synthesis

Version 1.2

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.
DSL: All components of this product are on the Canadian DSL.
KOREA: Not in compliance with the inventory

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Labeling

Hazard pictograms



Signal Word

Warning

Hazard Statements

H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

Precautionary Statements

Prevention

P273 Avoid release to the environment.

Response

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Full text of H-Statements referred to under sections 2 and 3.

H319 Causes serious eye irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 02/09/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.