



VWR ANALYTICAL

SAFETY DATA SHEET

Issuing Date 05-Aug-2015

Revision Date 03-Aug-2015

Revision Number 1

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product Identifier

Product Name/Catalog ID 82025-944, 89800-018

Other means of identification

Product Description 1000 µg/mL Arsenic

Recommended use of the chemical and restrictions on use

Recommended Use Laboratory chemicals.

Uses advised against No information available

Details of the supplier of the safety data sheet

Company

VWR International, LLC
Radnor Corporate Center
Building One, Suite 200
P.O. Box 6660
100 Matsonford Road
Radnor, PA 19087-8660
Tel: 610-386-1700

Emergency Telephone Number

Chemtec 1-800-424-9300 (US)
Canutec - 1-613-996-6666 (Canada)

2. HAZARDS IDENTIFICATION

GHS

Classification

| | |
|-----------------------------------|-------------|
| Skin corrosion/irritation | Category 2 |
| Serious Eye Damage/Eye Irritation | Category 2A |
| Carcinogenicity | Category 1A |

Label Elements

Danger

Hazard Statements

Causes skin irritation
Causes serious eye irritation
May cause cancer

**Appearance** Clear / Colorless**Physical State** Liquid**Odor** Odorless**Precautionary Statements - Prevention**

Do not handle until all safety precautions have been read and understood
 Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response**Eyes**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention

Skin

IF ON SKIN: Wash with plenty of soap and water
 If skin irritation occurs: Get medical advice/attention
 Take off contaminated clothing and wash before reuse

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)**Other Information**

3. COMPOSITION/INFORMATION ON INGREDIENTS

| Chemical Name | CAS-No | Weight % |
|---------------|-----------|----------|
| Nitric acid | 7697-37-2 | 2 |
| Arsenic | 7440-38-2 | 0.1 |

4. FIRST AID MEASURES

First Aid Measures**General Advice**

Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.

Eye Contact

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Skin Contact

Wash skin with soap and water.

Inhalation

Immediate medical attention is required. Move to fresh air. Artificial respiration and/or oxygen may be necessary. Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation.

| | |
|--|---|
| Ingestion | Immediate medical attention is required. Do NOT induce vomiting. Clean mouth with water and afterwards drink plenty of water. Call a physician immediately. |
| Protection of First-aiders | Use personal protective equipment. Avoid contact with skin, eyes and clothing. |
| <u>Most important symptoms and effects, both acute and delayed</u> | |
| Most Important Symptoms/Effects | Difficulty breathing. |
| <u>Indication of any immediate medical attention and special treatment needed</u> | |
| Notes to Physician | Treat symptomatically |

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media Decomposition by contact with water may generate vapors which can be ignited by heat or open flame.

Special Exposure Hazards Arising from the Substance/Mixture

Thermal decomposition can lead to release of irritating and toxic gases and vapors

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Ensure adequate ventilation. Use personal protective equipment. Do not get in eyes, on skin, or on clothing.

Environmental Precautions

Environmental Precautions Prevent further leakage or spillage if safe to do so. Beware of vapors accumulating to form explosive concentrations. Vapors can accumulate in low areas.

Methods and material for containment and cleaning up

Methods for Cleaning up Dam up. Neutralise with lime; soda. Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Handling Wear personal protective equipment. Ensure adequate ventilation. In case of insufficient ventilation, wear suitable respiratory equipment. Do not get in eyes, on skin, or on clothing. Do not breathe vapors or spray mist.

Conditions for safe storage, including any incompatibilities

Technical measures/Precautions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible Products None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

| Chemical Name | ACGIH TLV | OSHA PEL | NIOSH IDLH |
|--------------------------|-----------------------------|---|---|
| Nitric acid 7697-37-2 | 4 ppm STEL TWA: 2 ppm | TWA: 2 ppm TWA: 5 mg/m ³ (vacated) TWA: 2 ppm (vacated) TWA: 5 mg/m ³ (vacated) STEL: 4 ppm (vacated) STEL: 10 mg/m ³ | IDLH: 25 ppm TWA: 2 ppm TWA: 5 mg/m ³ STEL: 4 ppm STEL: 10 mg/m ³ |
| Arsenic 7440-38-2 | TWA: 0.01 mg/m ³ | TWA: 10 µg/m ³ (vacated) TWA: 0.5 mg/m ³ | IDLH: 5 mg/m ³ Ceiling: 0.002 mg/m ³ |

Appropriate engineering controls

Engineering Measures Ensure adequate ventilation, especially in confined areas.

Individual protection measures, such as personal protective equipment

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice. Wear suitable gloves and eye/face protection. Avoid contact with skin, eyes and clothing. Do not eat, drink or smoke when using this product. Wash hands before breaks and immediately after handling the product. Remove and wash contaminated clothing before re-use. Contaminated work clothing should not be allowed out of the workplace. Provide regular cleaning of equipment, work area and clothing.

Section 9. Physical and Chemical Properties

Information on basic physical and chemical properties

| | |
|---|---------------------------|
| Physical State | Liquid |
| Appearance | Clear / Colorless |
| Odor | Odorless |
| Property | Values |
| pH VALUE | No data available |
| Melting Point/Range | No data available |
| Boiling Point/Range | 100 °C |
| Evaporation rate | No data available |
| Flammability (solid, gas) | No data available |
| Vapor Pressure | No data available |
| Vapor Density | No data available |
| Relative Density | No data available |
| Specific Gravity | No data available |
| Water Solubility | Miscible |
| Partition coefficient: n-octanol/water | No data available |
| Autoignition Temperature | No data available |
| Decomposition Temperature | No data available |
| Viscosity | No data available |
| Explosive Properties | No information available |
| Oxidizing Properties | No information available |
| Other information | |
| VOC Content | No information available. |

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to Avoid

None known.

Incompatible Materials

Reducing agents

Hazardous Decomposition ProductsNitrogen oxides (NO_x).**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure**

| | |
|----------------------------|--|
| Product Information | Harmful if swallowed Harmful by inhalation |
| Inhalation | Harmful by inhalation. |
| Eye Contact | There is no data available for this product. |
| Skin Contact | There is no data available for this product. |
| Ingestion | Harmful if swallowed. |

| Component | LD50 Oral | LD50 Dermal | LC50 Inhalation |
|--------------------------------|--|-------------|--|
| Nitric acid 7697-37-2 (2) | - | - | = 130 mg/m ³ (Rat) 4 h = 67 ppm (Rat) 4 h |
| Arsenic 7440-38-2 (0.1) | = 15 mg/kg (Rat) = 763 mg/kg (Rat) | - | - |

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.
Mutagenic Effects No information available.
Carcinogenic effects

| Chemical Name | ACGIH | IARC | NTP | OSHA |
|--------------------------|-------|----------|-------|------|
| Nitric acid 7697-37-2 | | Group 2A | | X |
| Arsenic 7440-38-2 | A1 | Group 1 | Known | X |

Reproductive Toxicity No information available.
STOT - single exposure No information available.
STOT - repeated exposure No information available.
Target Organ Effects Respiratory system.
Aspiration Hazard No information available.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (inhalation-dust/mist) 343.2 mg/L
ATEmix (inhalation-vapor) 3350 mg/L

12. ECOLOGICAL INFORMATION

Ecotoxicity

Ecotoxicity effects

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

| Chemical Name | Toxicity to Algae | Toxicity to Fish | Microtox | Daphnia Magna (Water Flea) |
|--------------------------|-------------------|--|----------|----------------------------|
| Nitric acid 7697-37-2 | | 72: 96 h Gambusia affinis mg/L LC50 | | |

Persistence and Degradability

No information available.

Bioaccumulation/Accumulation

No information available.

| Chemical Name | Log Pow |
|--------------------------|---------|
| Nitric acid 7697-37-2 | -2.3 |

Other Adverse Effects

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Waste from Residues/Unused Products Dispose of in accordance with federal, state and local regulations

Contaminated Packaging Do not re-use empty containers.

| Chemical Name | RCRA | RCRA - Basis for Listing | RCRA - D Series Wastes | RCRA - U Series Wastes |
|----------------------|------|---|---------------------------|------------------------|
| Arsenic 7440-38-2 | | Included in waste streams: F032, F034, F035, F039, K031, K060, K084, K101, K102, K161, K171, K172, K176 | 5.0 mg/L regulatory level | |

| Chemical Name | California Hazardous Waste Status |
|--------------------------|-----------------------------------|
| Nitric acid 7697-37-2 | Toxic Corrosive Ignitable |
| Arsenic 7440-38-2 | Toxic |

14. Transport information

IMDG/IMO

14.1. UN-No UN3264
14.2. Proper Shipping Name Corrosive liquid, acidic, inorganic, n.o.s
14.3. Hazard Class 8
14.4. Packing Group III
Description Not applicable.
14.5. Marine Pollutant None.
14.6. Special Provisions None

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code No information available.

RID

14.1. UN-No UN3264
 14.2. Proper Shipping Name Corrosive liquid, acidic, inorganic, n.o.s
 14.3. Hazard Class 8
 14.4. Packing Group III
 Description Not applicable.
 14.5. Environmental hazard None
 14.6. Special Provisions None

ADR

14.1. UN-No UN3264
 14.2. Proper Shipping Name Corrosive liquid, acidic, inorganic, n.o.s
 14.3. Hazard Class 8
 14.4. Packing Group III
 Description Not applicable.
 14.5. Environmental hazard None
 14.6. Special Provisions None

ICAO

14.1. UN-No UN3264
 14.2. Proper Shipping Name Corrosive liquid, acidic, inorganic, n.o.s
 14.3. Hazard Class 8
 14.4. Packing Group III
 Description Not applicable.
 14.5. Environmental hazard None
 14.6. Special Provisions None

IATA-DGR

14.1. UN-No UN3264
 14.2. Proper Shipping Name Corrosive liquid, acidic, inorganic, n.o.s
 14.3. Hazard Class 8
 14.4. Packing Group III
 Description Not applicable
 14.5. Environmental hazard None
 14.6. Special Provisions None

15. REGULATORY INFORMATION

International Inventories

| | |
|----------------------|----------|
| TSCA | Complies |
| DSL/NDL | Complies |
| EINECS/ELINCS | Complies |
| ENCS | Complies |
| IECSC | Complies |
| KECL | Complies |
| PICCS | Complies |
| AICS | Complies |

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

ENCS - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

AICS - Australian Inventory of Chemical Substances

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

SARA 311/312 Hazard Categories

| | |
|-----------------------------------|----|
| Acute Health Hazard | No |
| Chronic Health Hazard | No |
| Fire Hazard | No |
| Sudden Release of Pressure Hazard | No |
| Reactive Hazard | No |

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

| Chemical Name | CWA - Reportable Quantities | CWA - Toxic Pollutants | CWA - Priority Pollutants | CWA - Hazardous Substances |
|--------------------------|-----------------------------|------------------------|---------------------------|----------------------------|
| Nitric acid 7697-37-2 | 1000 lb | | | X |
| Arsenic 7440-38-2 | | X | X | |

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

| Chemical Name | Hazardous Substances RQs | Extremely Hazardous Substances RQs | RQ |
|--------------------------|--------------------------|------------------------------------|---|
| Nitric acid 7697-37-2 | 1000 lb | 1000 lb | RQ 1000 lb final RQ RQ 454 kg final RQ |
| Arsenic 7440-38-2 | 1 lb | | RQ 1 lb final RQ RQ 0.454 kg final RQ |

U.S. State Regulations**California Proposition 65**

This product contains the following Proposition 65 chemicals:

| Chemical Name | California Prop. 65 |
|---------------------|---------------------|
| Arsenic - 7440-38-2 | Carcinogen |

U.S. State Right-to-Know Regulations

| Chemical Name | New Jersey | Massachusetts | Pennsylvania |
|--------------------------|------------|---------------|--------------|
| Nitric acid 7697-37-2 | X | X | X |
| Arsenic 7440-38-2 | X | X | X |

U.S. EPA Label Information**16. OTHER INFORMATION**

Revision Date 03-Aug-2015

Revision Note

No information available

Disclaimer

The above information is believed to be correct but does not purport to be all-inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product. VWR International and its Affiliates shall not be held liable for any damage resulting from handling.

End of MSDS