SAFETY DATA SHEET

Issuing Date 04-Sep-2015 **Revision Date** 04-Sep-2015 **Revision Number** 1

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product Identifier
Product Name/Catalog ID 82026-122

Other means of identification
Product Description 10 µg/mL Aluminum

Recommended use of the chemical and restrictions on use
Recommended Use Laboratory chemicals.

Uses advised against No information available

Details of the supplier of the safety data sheet
Company
VWR International, LLC
Radnor Corporate Center
Building One, Suite 200
P.O. Box 6660
100 Matsonford Road
Radnor, PA 19087-8660
Tel: 610-386-1700

Emergency Telephone Number
Chemtrec 1-800-424-9300 (US)
Canutec - 1-613-996-6666 (Canada)

2. HAZARDS IDENTIFICATION

GHS

Classification

Skin corrosion/irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 1

Label Elements

Danger

Hazard Statements
Causes skin irritation
Causes serious eye damage



Appearance Clear / Colorless **Physical State** Liquid **Odor** Odorless

Precautionary Statements - Prevention
Wash face, hands and any exposed skin thoroughly after handling
Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

Eyes
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
Immediately call a POISON CENTER or doctor/physician
Skin
IF ON SKIN: Wash with plenty of soap and water
If skin irritation occurs: Get medical advice/attention
Take off contaminated clothing and wash before reuse

Hazards not otherwise classified (HNOC)
Other Information

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS-No	Weight %
Nitric acid	7697-37-2	3

4. FIRST AID MEASURES

First Aid Measures

Eye Contact Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Skin Contact Wash skin with soap and water.

Inhalation Move to fresh air.

Ingestion Clean mouth with water and afterwards drink plenty of water.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms/Effects No information available.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media Decomposition by contact with water may generate vapors which can be ignited by heat or open flame.

Special Exposure Hazards Arising from the Substance/Mixture

Thermal decomposition can lead to release of irritating gases and vapors

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Ensure adequate ventilation.

Environmental Precautions

Environmental Precautions Prevent further leakage or spillage if safe to do so. Beware of vapors accumulating to form explosive concentrations. Vapors can accumulate in low areas.

Methods and material for containment and cleaning up

Methods for Cleaning up Dam up. Neutralise with lime; soda. Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Conditions for safe storage, including any incompatibilities

Technical measures/Precautions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible Products None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines .

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Nitric acid 7697-37-2	4 ppm STEL TWA: 2 ppm	TWA: 2 ppm TWA: 5 mg/m^3 (vacated) TWA: 2 ppm (vacated) TWA: 5 mg/m^3 (vacated) STEL: 4 ppm (vacated) STEL: 10 mg/m^3	IDLH: 25 ppm TWA: 2 ppm TWA: 5 mg/m^3 STEL: 4 ppm STEL: 10 mg/m^3

Appropriate engineering controls

Engineering Measures Ensure adequate ventilation, especially in confined areas.

Individual protection measures, such as personal protective equipment

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical State	Liquid
Appearance	Clear / Colorless
Odor	Odorless

Property	**Values**
pH VALUE	No data available
Melting Point/Range	No data available
Boiling Point/Range	100 °C
Evaporation rate	No data available
Flammability (solid, gas)	No data available
Vapor Pressure	No data available
Vapor Density	No data available
Relative Density	No data available
Specific Gravity	No data available
Water Solubility	Miscible
Partition coefficient: n-octanol/water	No data available
Autoignition Temperature	No data available
Decomposition Temperature	No data available
Viscosity	No data available

Explosive Properties	No information available
Oxidizing Properties	No information available

Other information

VOC Content	No information available.

10. STABILITY AND REACTIVITY

Reactivity
No data available.

Chemical Stability
Stable under recommended storage conditions.

Possibility of Hazardous Reactions
None under normal processing.

Hazardous Polymerization Hazardous polymerization does not occur.

Conditions to Avoid
None known.

Incompatible Materials
Reducing agents

Hazardous Decomposition Products
Nitrogen oxides (NOx).

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information Product does not present an acute toxicity hazard based on known information

Inhalation There is no data available for this product.

Eye Contact There is no data available for this product.

Skin Contact There is no data available for this product.

Ingestion There is no data available for this product.

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Nitric acid 7697-37-2 (3)	-	-	= 130 mg/m³ (Rat) 4 h = 67 ppm (Rat) 4 h

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.
Mutagenic Effects No information available.
Carcinogenic effects

Chemical Name	ACGIH	IARC	NTP	OSHA
Nitric acid 7697-37-2		Group 2A		X

Reproductive Toxicity No information available.
STOT - single exposure No information available.
STOT - repeated exposure No information available.
Aspiration Hazard No information available.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document .
ATEmix (inhalation-dust/mist) 726.7 mg/L
ATEmix (inhalation-vapor) 2233 mg/L

12. ECOLOGICAL INFORMATION

Ecotoxicity

Ecotoxicity effects
0.001% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Toxicity to Algae	Toxicity to Fish	Microtox	Daphnia Magna (Water Flea)
Nitric acid 7697-37-2		72: 96 h Gambusia affinis mg/L LC50		

Persistence and Degradability
No information available.

Bioaccumulation/Accumulation
No information available.

Chemical Name	Log Pow
Nitric acid 7697-37-2	-2.3

Other Adverse Effects

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Waste from Residues/Unused Products Dispose of in accordance with federal, state and local regulations

Contaminated Packaging Do not re-use empty containers.

Chemical Name	California Hazardous Waste Status
Nitric acid 7697-37-2	Toxic Corrosive Ignitable

14. TRANSPORT INFORMATION

IMDG/IMO

14.1. UN-No	UN3264
14.2. Proper Shipping Name	Corrosive liquid, acidic, inorganic, n.o.s
14.3. Hazard Class	8
14.4. Packing Group	III
Description	Not applicable.
14.5. Marine Pollutant	None.
14.6. Special Provisions	None
14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	No information available.

RID

14.1. UN-No	UN3264
14.2. Proper Shipping Name	Corrosive liquid, acidic, inorganic, n.o.s
14.3. Hazard Class	8
14.4. Packing Group	III
Description	Not applicable.
14.5. Environmental hazard	None
14.6. Special Provisions	None

ADR

14.1. UN-No	UN3264
14.2. Proper Shipping Name	Corrosive liquid, acidic, inorganic, n.o.s
14.3. Hazard Class	8
14.4. Packing Group	III
Description	Not applicable.
14.5. Environmental hazard	None
14.6. Special Provisions	None

ICAO

14.1. UN-No	UN3264
14.2. Proper Shipping Name	Corrosive liquid, acidic, inorganic, n.o.s
14.3. Hazard Class	8
14.4. Packing Group	III
Description	Not applicable.
14.5. Environmental hazard	None
14.6. Special Provisions	None

IATA-DGR

14.1. UN-No	UN3264
14.2. Proper Shipping Name	Corrosive liquid, acidic, inorganic, n.o.s
14.3. Hazard Class	8
14.4. Packing Group	III
Description	Not applicable
14.5. Environmental hazard	None
14.6. Special Provisions	None

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies
EINECS/ELINCS	Complies
ENCS	Complies
IECSC	Complies
KECL	Complies
PICCS	Complies
AICS	Complies

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AICS - Australian Inventory of Chemical Substances

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Nitric acid 7697-37-2	1000 lb			X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	Extremely Hazardous Substances RQs	RQ
Nitric acid 7697-37-2	1000 lb	1000 lb	RQ 1000 lb final RQ RQ 454 kg final RQ

U.S. State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Nitric acid 7697-37-2	X	X	X

U.S. EPA Label Information

16. OTHER INFORMATION

Revision Date 04-Sep-2015

Revision Note

No information available

Disclaimer

The above information is believed to be correct but does not purport to be all-inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product. VWR International and its Affiliates shall not be held liable for any damage resulting from handling.

End of MSDS