LIFELINE CELL TECHNOLOGY SAFETY DATA SHEET

SECTION 1 – PRODUCT AND COMPANY INFORMATION

Product Name: FibroLife Xeno-Free Complete Medium

Product Number: LM-0013

Company Address: Lifeline Cell Technology

8415 Progress Drive, Suite T

Frederick, MD 21701

Technical Phone: (877) 845-7787

Fax: (443) 393-0393

Emergency Phone: (877) 845-7787

Product use: Cell/Tissue culture

SECTION 2 – HAZARDS IDENTIFICATION

Hazardous Components: Not a hazardous substance or mixture

Hazards not covered by GHS: This product contains raw material of human source. Each batch of Human Serum used in this medium was tested and found to be negative for Hepatitis B, Hepatitis C, HIV-1 and HIV-2 by FDA approved methods. These tests cannot offer complete assurance of the absence of these or other infectious agents.

SECTION 3 – COMPOSITION / INFORMATION ON INGREDIENTS

Principal Components: Water CAS number: 7732-18-5

Human Serum CAS number: N/A

Composition: The subject formulation is a nutrient blend of amino acids, vitamins, organic and inorganic supplements and salts and Human Serum in purified water. With the exception of 1-5% Human Serum and purified water, all other ingredients are in concentrations of less than 1%.

Synonym: N/A

SECTION 4 – FIRST AID MEASURES

Potential Health Effects:

Eye: May cause irritation of the eye. **Skin**: May cause skin irritation.

Ingestion: May be harmful if swallowed.

Inhalation: May be harmful if inhaled. Material may be irritating to mucous membranes and upper

respiratory tract.

First aid measures:

Oral Exposure: If swallowed, rinse out mouth with water provided person is conscious. Call a physician.

Dermal Exposure: In case of contact with skin, flush with copious amounts of water for at least 15 minutes. Should irritation occur, call a physician.

Eye Exposure: In case of contact with eyes, flush with copious amounts of water for at least 15 minutes. Assure adequate flushing by separating the eyelids with fingers. Call a physician.

SECTION 5 – FIRE FIGHTING MEASURES

General Fire hazard: Product does not present any special fire hazard. Carbon oxides may be released

in a fire.

Flash point: N/A

Extinguishing media: Use media appropriate for the material that is burning.

Advice for Firefighters: Wear self-contained breathing apparatus if necessary.

SECTION 6 – ACCIDENTAL RELEASE MEASURES

Personal Precautions and Protective Equipment: Refer to section 8 for appropriate personal protection.

Environmental Precautions: No special environmental precautions are required.

Methods for Clean Up: Absorb liquid with disposable laboratory towel or other absorbent material and then place in a closed container for biohazardous disposal. Wash spill site after liquid cleanup is complete with disinfectant cleansers appropriate for the spill site surface material.

SECTION 7 – HANDLING AND STORAGE

Precautions for Handling: Refer to section 8 for appropriate personal protection. Avoid contact with eyes, skin or clothing. Product may cause allergic reaction in sensitized individuals. Do not pipet by mouth.

Storage: Keep container tightly closed. Store at -20°C or below. Protect from light.

SECTION 8 – EXPOSURE CONTROLS AND PERSONAL PROTECTION

Exposure limits: Not listed on the OSHA Occupational Chemical database.

Engineering Controls: Eye wash stations are required.

Ventilation: Area ventilation is generally adequate.

Personal Protective Equipment:

Respiratory: Respirator is not required.

Hand:Chemical resistant gloves required.Eye:Safety glasses or goggles required.Clothing:Laboratory coat recommended.

General Hygiene Measures: Wash hands thoroughly after handling.

SECTION 9 – PHYSICAL / CHEMICAL PROPERTIES

Appearance: Frozen, pale yellow to tan liquid

Upper/lower flammability or Explosive limits: No data available

Odor: Faint earthy or musky odor

Vapor pressure: No data available **Odor threshold:** No data available Vapor density: No data available pH: No data available **Relative density:** No data available **Freezing point:** No data available **Solubility:** Soluble in water **Boiling point:** No data available Flash point: No data available Evaporation rate: No data available Flammability: Not flammable

Upper/lower flammability or explosive limits:Partition coefficient: n-octanol/water:
No data available

Auto-ignition temperature: No data available

Viscosity: No data available

SECTION 10 – STABILITY AND REACTIVITY

Reactivity: No data available

Chemical stability: Stable under recommended storage and usage conditions.

Possible hazardous reactions: No data available **Conditions to be avoided:** Heat, sparks and flames.

Incompatible materials: Acid chlorides, Phosphorus halides, Strong acids, Strong oxidizing agents,

Strong reducing agents

Hazardous decomposition products: Carbon oxides and Sulfur oxides may be released in a fire.

SECTION 11 – TOXICOLOGICAL INFORMATION

Likely routes of exposure: Ingestion, skin, eye contact.

Acute toxicity

Oral LD50: No data available
Inhalation LC50: No data available
Dermal LD50: No data available
Other: No data available

Chronic toxicity: No data available

Skin corrosion: No data available **Eye damage:** No data available

Sensitization (Respiration or Skin): No data available

Germ cell mutagenicity: No data available

Carcinogenicity: No data available

Reproductive toxicity: No data available

Teratogeniticity: No data available

Carcinogenicity

NTP: not listed IARC: not listed OSHA: not listed

SECTION 12 – ECOLOGICAL INFORMATION

Ecotoxicity: No data available **Persistence/Degradability:** No data available **Bioaccumulation Potential:** No data available

Mobility in Soil: No data available. Expected to be mobile in soil due to high solubility in water.

SECTION 13 – DISPOSAL CONSIDERATIONS

RCRA hazardous waste code: Not listed as a hazardous waste.

Appropriate disposal containers: No specific restrictions on waste container type.

Appropriate Method of Disposal: Clean up and dispose of waste in accordance with all federal, state and

local environmental regulations.

SECTION 14 – TRANSPORT INFORMATION

UN number: N/A **Proper Shipping Name**: None.

DOT:Non-hazardous for transport.**IMDG**:Non-hazardous for transport.**IATA**:Non-hazardous for transport.

SECTION 15 – REGULATORY INFORMATION

SARA 302 Components: No chemicals in this product are subject to SARA Title III, Section 302.

SARA 313 Components: This product does not contain chemical components with known CAS numbers

that exceed the threshold (De Minimus) reporting levels established by SARA Title III, Section 313.

SARA 311/312: Not a hazardous substance or mixture

Massachusetts Right to Know Components: No components are subject to Massachusetts Right to Know

Act.

Pennsylvania Right to Know Components: Water CAS number: 7732-18-5

Human Serum CAS number: N/A

New Jersey Right to Know Components: Human Serum CAS number: N/A

California Prop. 65 Components: This product does not contain any chemicals known to the state of California to cause cancer, birth defects or other reproductive harm.

SECTION 16 – OTHER INFORMATION

Preparation information:

Prepared by: Quality Department
Date Prepared: April 15, 2015
Replaced Version date: July 30, 2012

Disclaimer: This information is furnished without warranty, expressed or implied, except that it is accurate to the best knowledge of Lifeline Cell Technology. The data on this sheet relate only to the specific materials designated herein and shall only be used as a guide. Lifeline Cell Technology assumes no legal responsibility for the use or reliance upon these data.