

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 04/15/2014

Version 1.1

SECTION 1.Identification

Product identifier

Product number SX1075

Product name SUCROSE CRYSTALS

CAS-No. 57-50-1

Relevant identified uses of the substance or mixture and uses advised against

Identified uses Reagent for analysis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS-Labeling

Not a hazardous substance or mixture according to Regulation (EC) No 1272/2008.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200). This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS and may deviate from the GHS information.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula $C_{12}H_{22}O_{11}$ (Hill) Molar mass 342.29 g/mol

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number SX1075 Version 1.1

Product name SUCROSE CRYSTALS

Saccharose (>= 90 % - <= 100 %)

57-50-1

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

We have no description of any toxic symptoms.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

In the event of fire, wear self-contained breathing apparatus.

Further information

none

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid inhalation of dusts. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number SX1075 Version 1.1

Product name SUCROSE CRYSTALS

No special precautionary measures necessary.

Methods and materials for containment and cleaning up

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at room temperature.

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis Value Threshold Remarks

limits

Saccharose 57-50-1

ACGIH Time Weighted Average 10 mg/m³

(TWA):

NIOSH/GUIDE Recommended 10 mg/m³ Form of exposure: Total

exposure limit (REL):

Recommended 5 mg/m³ Form of exposure: Respirable.

exposure limit (REL):

OSHA_TRANS PEL: 15 mg/m³ Form of exposure: Total dust.

PEL: 5 mg/m^3 Form of exposure: Respirable fraction.

Z1A Time Weighted Average 15 mg/m³ Form of exposure: Total dust.

(TWA):

Time Weighted Average 5 mg/m³ Form of exposure: Respirable fraction.

(TWA):

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

Eye/face protection

Safety glasses

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number SX1075 Version 1.1

Product name SUCROSE CRYSTALS

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state solid

Color off-white

Odor odorless

Odor Threshold not applicable

pH ca. 7

at 100 g/l 68 °F (20 °C)

Melting point 169 - 170 °C

Boiling point No information available.

Flash point No information available.

Evaporation rate No information available.

Flammability (solid, gas) No information available.

Lower explosion limit No information available.

Upper explosion limit No information available.

Vapor pressure No information available.

Relative vapor density No information available.

Density No information available.

Relative density No information available.

Water solubility at 68 °F (20 °C)

soluble

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number SX1075 Version 1.1

Product name SUCROSE CRYSTALS

Partition coefficient: n- log Pow: -3.70 octanol/water (experimental)

(Lit.) Bioaccumulation is not expected.

Autoignition temperature No information available.

Decomposition temperature > 336 °F (> 169 °C)

Viscosity, dynamic No information available.

Explosive properties Not classified as explosive.

Oxidizing properties none

Bulk density ca.800 - 950 kg/m³

Conductivity <= 35 μS/cm

at 68 °F (20 °C)

SECTION 10. Stability and reactivity

Reactivity

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents

Conditions to avoid

Strong heating (decomposition).

Incompatible materials

no information available

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Target Organs

Eyes

Respiratory system

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number SX1075 Version 1.1

Product name SUCROSE CRYSTALS

Acute oral toxicity

LD50 rat: 29,700 mg/kg (RTECS)

Genotoxicity in vitro

Mutagenicity (mammal cell test):

Result: negative

(National Toxicology Program)

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

egual to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

Further information

Substances which occur in nature

Hazardous properties cannot be excluded but are unlikely when the product is handled appropriately.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: -3.70 (experimental)

(Lit.) Bioaccumulation is not expected.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number SX1075 Version 1.1

Product name SUCROSE CRYSTALS

Mobility in soil

No information available.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Target organ effects

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Chronic Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number SX1075 Version 1.1

Product name SUCROSE CRYSTALS

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients

Saccharose

Pennsylvania Right To Know

Ingredients

Saccharose

New Jersey Right To Know

Ingredients

Saccharose

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 04/15/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.