



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 01/27/2015

Version 1.4

SECTION 1. Identification

Product identifier

Product number	109411
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Corrosive to Metals, Category 1, H290

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word

Warning

Hazard Statements

H290 May be corrosive to metals.

Precautionary Statements

P234 Keep only in original container.

P390 Absorb spillage to prevent material damage.

P406 Store in corrosive resistant stainless steel container with a resistant inliner.

Other hazards

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	109411	Version 1.4
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®	

None known.

SECTION 3. Composition/information on ingredients

Chemical nature	Aqueous solution of inorganic compounds.
Remarks	No hazardous ingredients according to the OSHA Hazard Communication Standard 29 CFR 1910.1200.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Consult a physician.

Eye contact

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Allergic reactions

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Fire may cause evolution of:
nitrogen oxides

Advice for firefighters

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	109411	Version 1.4
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®	

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemisorb® H⁺, Art. No. 101595).

Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	109411	Version 1.4
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®	

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	light blue
Odor	odorless
Odor Threshold	Not applicable
pH	ca. 1 at 68 °F (20 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	ca. 1.005 g/cm ³ at 68 °F (20 °C)
Relative density	No information available.
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	109411	Version 1.4
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®	

Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.
Oxidizing properties	none
Corrosion	May be corrosive to metals.

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

Because of low concentration of the dissolved substance(s): none; exception: the generally known reaction partners of water.

Conditions to avoid

no information available

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Sensitization

Mixture may cause an allergic skin reaction.

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC

No ingredient of this product present at levels greater than or

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	109411	Version 1.4
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®	

	equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.

Other information

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

Further data:

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	109411	Version 1.4
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®	

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID)
Class	8
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID SOLUTION)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID SOLUTION)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-B

SECTION 15. Regulatory information

United States of America

SARA 313

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

The following components are subject to reporting levels established by SARA Title III, Section 302:

Ingredients

Selenious acid	7783-00-8
nitric acid	7697-37-2

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	109411	Version 1.4
Product name	ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®	

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients

nitric acid

Selenious acid

California Prop 65 Components

WARNING: This product contains a chemical known in the State of California to cause birth defects or other reproductive harm.

Ingredients

Lead(II) nitrate

Cadmium nitrate

California Prop 65 Components

WARNING: this product contains a chemical known in the State of California to cause cancer.

Ingredients

Lead(II) nitrate

Arsenic acid

Cadmium nitrate

nickel(II) nitrate

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

KOREA: Not in compliance with the inventory

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H290 May be corrosive to metals.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 01/27/2015

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 109411

Version 1.4

Product name ICP Multi element standard solution XXIV tuning solution 700 ES CertiPUR®

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.