

Recombinant Murine MCP-2

CATALOG #:	4226-10	10 µg
	4226-1000	1 mg
LOT #:		
SOURCE:	<i>E. coli</i>	
PURITY:	>98% by SDS-PAGE and HPLC analyses Endotoxin level is <0.1 ng per µg of MCP-2.	
MOL. WEIGHT:	8.5 kDa	
FORM:	Sterile filtered and then lyophilized with no additives	
RECONSTITUTION:	Centrifuge the vial prior to opening. Reconstitute in water to a concentration of 0.1-1.0 mg/ml. This solution can then be diluted into other aqueous buffers or stored at 4°C for 1 week or -20°C for future use.	
STORAGE CONDITIONS:	The lyophilized MCP-2 is best-stored desiccated below 0°C. Reconstituted MCP-2 should be stored in working aliquots at -20°C. For long term storage it is recommended to add a carrier protein (0.1% HSA or BSA). Please prevent freeze-thaw cycles.	
DESCRIPTION:	Macrophage/monocyte chemotactic protein-2 (MCP-2) plays an important role in the inflammatory response of blood monocytes, activated T cells, basophils, NK cells, and immature dendritic cells. Recombinant murine MCP-2 is an 8.5 kDa protein containing 74 amino acid residues.	
BIOLOGICAL ACTIVITY:	Determined by its ability to chemoattract human peripheral blood monocytes using a concentration range of 10-100 ng/ml.	

RELATED PRODUCTS:

- Apoptosis Detection Kits & Reagents
 - Annexin V Kits & Bulk Reagents
 - Caspase Assay Kits & Reagents
 - Mitochondrial Apoptosis Kits & Reagents
 - Nuclear Apoptosis Kits & Reagents
 - Apoptosis Inducers and Set
 - Apoptosis siRNA Vectors
- Cell Fractionation System
 - Mitochondria/Cytosol Fractionation Kit
 - Nuclear/Cytosol Fractionation Kit
 - Membrane Protein Extraction Kit
 - Cytosol/Particulate Rapid Separation Kit
 - Mammalian Cell Extraction Kit
 - FractionPREP Fractionation System
- Cell Proliferation & Senescence
 - Quick Cell Proliferation Assay Kit
 - Senescence Detection Kit
 - High Throughput Apoptosis/Cell Viability Assay Kits
 - LDH-Cytotoxicity Assay Kit
 - Bioluminescence Cytotoxicity Assay Kit
 - Live/Dead Cell Staining Kit
- Cell Damage & Repair
 - HDAC Fluorometric & Colorimetric Assays & Drug Discovery Kits
 - HAT Colorimetric Assay Kit & Reagents
 - DNA Damage Quantification Kit
 - Glutathione & Nitric Oxide Fluorometric & Colorimetric Assay Kits
- Signal Transduction
 - cAMP & cGMP Assay Kits
 - Akt & JNK Activity Assay Kits
 - Beta-Secretase Activity Assay Kit
- Adipocyte & Lipid Transfer
 - Recombinant Adiponectin, Survivin, & Leptin
 - CETP Activity Assay & Drug Discovery Kits
 - PLTP Activity Assay & Drug Discovery Kits
 - Total Cholesterol Quantification Kit
- Molecular Biology & Reporter Assays
 - siRNA Vectors
 - Cloning Insert Quick Screening Kit
 - Mitochondrial & Genomic DNA Isolation Kits
 - 5 Minutes DNA Ligation Kit
 - 20 Minutes Gel Staining/Destaining Kit
 - β -Galactosidase Staining Kit & Luciferase Reporter Assay Kit
- Growth Factors and Cytokines
- Monoclonal and Polyclonal Antibodies

FOR RESEARCH USE ONLY! Not to be used on humans.