

FGF-7 (KGF), Human CellExp™, human recombinant

CATALOG #:	6450-10	10 µg
	6450-50	50 µg
ALTERNATE NAMES:	HBGF-7, FGF7, FGF-7, KGF.	
SOURCE:	Human Cell Expressed	
PURITY:	> 95% by SDS - PAGE	
MOL. WEIGHT:	17 and 30 kDa, monomer, glycosylated	
ENDOTOXIN LEVEL:	< 1.0 EU per 1 µg of protein	
FORMULATION:	Lyophilized from a PBS solution.	
RECONSTITUTION:	Reconstitute in sterile PBS containing 0.1% endotoxin-free, recombinant human serum albumin.	

STORAGE CONDITIONS:

Aliquot and store at -20°C or -70°C. Avoid repeated freezing and thawing cycles.

ADVANTAGES:


- Animal-derived product free
- High Activity
- Authentic Glycosylation

DESCRIPTION:

FGF-7 is a member of the fibroblast growth factor (FGF) family. FGF family members possess broad mitogenic and cell survival activities, and are involved in a variety of biological processes, including embryonic development, cell growth, morphogenesis, tissue repair, tumor growth and invasion. FGF7 is a potent epithelial cell-specific growth factor, whose mitogenic activity is predominantly exhibited in keratinocytes but not in fibroblasts and endothelial cells. Studies of mouse and rat homologs of this gene implicated roles in morphogenesis of epithelium, reepithelialization of wounds, hair development and early lung organogenesis.

BIOLOGICAL ACTIVITY:

ED₅₀ is typically 1.5 to 7.5 ng/mL. The specific activity was determined by the Dose-dependent stimulation of the proliferation of 4MBr-5 cells (monkey epithelial cell line).



Human Cell^{exp} Human Recombinant FGF-7 (KGF)

RELATED PRODUCTS:

- Human Cell^{exp} Human Recombinant FGF Basic (Cat # 6448-10, -50)
- Human Cell^{exp} Human Recombinant FGF-4 (Cat # 6449-10, -50)
- Human Cell^{exp} Human Recombinant FGF-8b (Cat # 6451-10, -50)
- FGF- basic 147, human recombinant (Cat # 4036-10, -50, -1000)
- FGF-1, human recombinant (Cat # 4034-10, -50, -1000)
- FGF-1, murine recombinant (Cat # 4035-10, -50, -1000)
- FGF-10/KGF-2, human recombinant (Cat # 4060-25, -100, -1000)
- FGF-18, human recombinant (Cat # 4082-25, -100, -1000)
- FGF-19, human recombinant (Cat # 4542-25, -100, -1000)
- FGF-2, bovine recombinant (Cat # 4040-10, -50, -1000)
- FGF-2, human recombinant (Cat # 4037-10, -50, -1000)
- FGF-2, murine recombinant (Cat # 4038-10, -50, -1000)
- FGF-2, rat recombinant (Cat # 4039-10, -50, -1000)
- FGF-20, human recombinant (Cat # 4589-20, -100)
- FGF-21, human recombinant (Cat # 4066-100, -1000)
- FGF-21, murine recombinant (Cat # 4067-10, -1000)
- FGF-22, human recombinant (Cat # 4063-10, -100, -1000)
- FGF-4, human recombinant (Cat # 4043-25, -100, -1000)
- FGF-7/KGF, human recombinant (Cat # 4050-10, -50, -1000)
- FGF-8, human recombinant (Cat # 4053-25, -100, -1000)
- FGF-9, human recombinant (Cat # 4056-20, -1000)

FOR RESEARCH USE ONLY! Not to be used in humans.