SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 01/26/2015 Version 1.2

SECTION 1.Identification

Product identifier

Product number	170316
Product name	Erbium ICP standard traceable to SRM from NIST Er_2O_3 in HNO_3 2-3% 1000 mg/l Er CertiPUR®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Corrosive to Metals, Category 1, H290
Skin irritation, Category 2, H315
Eye irritation, Category 2A, H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Warning

Hazard Statements
H290 May be corrosive to metals.
H315 Causes skin irritation.
H319 Causes serious eye irritation.

Precautionary Statements
P234 Keep only in original container.
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ eye protection/ face protection.
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P321 Specific treatment (see supplemental first aid instructions on this label).
P332 + P313 If skin irritation occurs: Get medical advice/ attention.
P337 + P313 If eye irritation persists: Get medical advice/ attention.
P362 Take off contaminated clothing and wash before reuse.
P390 Absorb spillage to prevent material damage.
P406 Store in corrosive resistant stainless steel container with a resistant inliner.

Other hazards
None known.

SECTION 3. Composition/information on ingredients
Chemical nature Aqueous solution

Hazardous ingredients
Chemical Name (Concentration)
CAS-No.
nitric acid (>= 1 % - < 5 %)
7697-37-2

Exact percentages are being wihtheld as a trade secret.

SECTION 4. First aid measures
Description of first-aid measures
Inhalation
After inhalation: fresh air.

Skin contact
After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact
After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion
After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed
irritant effects
The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

none

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

No special precautionary measures necessary.

Methods and materials for containment and cleaning up

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® H^+, Art. No. 101595).

Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
nitric acid 7697-37-2			
ACGIH	Time Weighted Average (TWA):	2 ppm	
	Short Term Exposure Limit (STEL):	4 ppm	
NIOSH/GUIDE	Recommended exposure limit (REL):	2 ppm 5 mg/m³	
	Short Term Exposure Limit (STEL):	4 ppm 10 mg/m³	
OSHA_TRANS	PEL:	2 ppm 5 mg/m³	
Z1A	Time Weighted Average (TWA):	2 ppm 5 mg/m³	
	Short Term Exposure Limit (STEL):	4 ppm 10 mg/m³	

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	odorless
Odor Threshold	Not applicable
pH	ca. 0.5 at 68 °F (20 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	ca.1.013 g/cm³ at 68 °F (20 °C)
Relative density	No information available.
Water solubility	No information available.
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.
Oxidizing properties	No information available.

Corrosion	May be corrosive to metals.

SECTION 10. Stability and reactivity

Reactivity
See below

Chemical stability
The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions
increased reactivity with:

oxidizable substances, organic solvent, Metals, metal alloys, Alkali metals, Alkaline earth metals, Ammonia, alkalines, acids

Conditions to avoid
Heating.

Incompatible materials
Metals, metal alloys
(generation of hydrogen)

Hazardous decomposition products
no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact

Target Organs
Eyes
Skin
Respiratory system
teeth

Acute oral toxicity
Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract.

Acute inhalation toxicity

Symptoms: Possible damages:, mucosal irritations

Skin irritation
Mixture causes skin irritation.

Eye irritation
Mixture causes serious eye irritation.

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information
Quantitative data on the toxicity of this product are not available.
Other information
The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.
Further data:
Other dangerous properties can not be excluded.
Handle in accordance with good industrial hygiene and safety practice.

Ingredients

nitric acid

Skin irritation
Rabbit
Result: Causes severe burns.
(IUCLID)

Eye irritation
Rabbit
Result: Causes burns.
(IUCLID)

Germ cell mutagenicity
Genotoxicity in vitro
Ames test
Salmonella typhimurium
Result: negative
Method: OECD Test Guideline 471

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

No ecological problems are to be expected when the product is handled and used with due care and attention.

Ingredients

nitric acid

Toxicity to fish

LC50 Gambusia affinis (Mosquito fish): 72 mg/l; 96 h (IUCLID)

Biodegradability

The methods for determining the biological degradability are not applicable to inorganic substances.

Substance does not meets the criteria for PBT or vPvB according to Regulation (EC) No 1907/2006, Annex XIII.

Henry constant

2482 Pa*m³/mol
Method: (calculated)
(Lit.) Distribution preferentially in air.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID NOT MORE THAN 5%)
Class	8
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID SOLUTION)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID NOT MORE THAN 5%)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-B

SECTION 15. Regulatory information

United States of America

SARA 313

The following components are subject to reporting levels established by SARA Title III, Section 313:

Ingredients

nitric acid	7697-37-2	*2.438 %*

SARA 302

The following components are subject to reporting levels established by SARA Title III, Section 302:

Ingredients

nitric acid	7697-37-2

DEA List I
Not listed

DEA List II
Not listed

US State Regulations

Massachusetts Right To Know
Ingredients
nitric acid

Pennsylvania Right To Know
Ingredients
nitric acid

New Jersey Right To Know
Ingredients
nitric acid

California Prop 65 Components
This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	All components of the product are listed in the TSCA-inventory.
DSL:	All components of this product are on the Canadian DSL.
KOREA:	Not in compliance with the inventory

SECTION 16. Other information

Training advice
Provide adequate information, instruction and training for operators.

Labeling
Hazard pictograms



Signal Word
Warning

Hazard Statements
H290 May be corrosive to metals.
H315 Causes skin irritation.
H319 Causes serious eye irritation.

Precautionary Statements
Response
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P313 Get medical advice/ attention.

Full text of H-Statements referred to under sections 2 and 3.

H290	May be corrosive to metals.
H315	Causes skin irritation.
H319	Causes serious eye irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet
Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date01/26/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.
All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.