SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 01/27/2015 Version 1.2

SECTION 1.Identification

Product identifier

Product number	100518
Product name	Perchloric acid 60% for analysis EMSURE® ACS

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis, Chemical production

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Oxidizing liquid, Category 1, H271
Corrosive to Metals, Category 1, H290
Skin corrosion, Category 1A, H314
Serious eye damage, Category 1, H318

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements
H271 May cause fire or explosion; strong oxidizer.
H290 May be corrosive to metals.
H314 Causes severe skin burns and eye damage.

Precautionary Statements
P210 Keep away from heat.
P220 Keep/Store away from clothing/ combustible materials.
P221 Take any precaution to avoid mixing with combustibles.
P234 Keep only in original container.
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P283 Wear fire/ flame resistant/ retardant clothing.
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.
P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P306 + P360 IF ON CLOTHING: rinse immediately contaminated clothing and skin with plenty of water before removing clothes.
P310 Immediately call a POISON CENTER or doctor/ physician.
P321 Specific treatment (see supplemental first aid instructions on this label).
P363 Wash contaminated clothing before reuse.
P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.
P371 + P380 + P375 In case of major fire and large quantities: Evacuate area. Fight fire remotely due to the risk of explosion.
P390 Absorb spillage to prevent material damage.
P405 Store locked up.
P406 Store in corrosive resistant stainless steel container with a resistant inliner.
P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature Aqueous solution

Hazardous ingredients

Chemical Name (Concentration)
CAS-No.
Perchloric acid (>= 50 % - < 70 %)
7601-90-3

Exact percentages are being wihtheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation
After inhalation: fresh air. Call in physician.

Skin contact
After skin contact: wash off with plenty of water. Immediately remove contaminated clothing. If available swab with polyethylene glycol 400. Call a physician immediately.

Eye contact
After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion
After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Do not attempt to neutralize.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed
Irritation and corrosion

Indication of any immediate medical attention and special treatment needed
No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media
Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media
For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture
Not combustible.
Has a fire-promoting effect due to release of oxygen.
Explosive decomposition possible on heating.
Development of hazardous combustion gases or vapors possible in the event of fire.
Fire may cause evolution of:
Hydrogen chloride gas

Advice for firefighters

Special protective equipment for fire-fighters
Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information
Cool closed containers exposed to fire with water spray. Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures
Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions
Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up
Cover drains. Collect, bind, and pump off spills.
Observe possible material restrictions (see sections 7 and 10).
Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® H^+, Art. No. 101595).
Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling
Keep all containers, equipment and working place clean. Explosive perchlorates may develop. Carefully avoid drying of perchloric acid solution at inaccessible places (e.g. cracks in tiles and jointings).

Observe label precautions.

Conditions for safe storage, including any incompatibilities
Requirements for storage areas and containers No metal or light-weight-metal containers.

Tightly closed. Separately or together with other oxidizing substances only and away from sources of ignition and heat. Because of their oxidation potential these products can raise the burning rate of combustible substances substantially or ignite combustible substances on contact with them.

Store at +5°C to +30°C (+41°F to +86°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)
Contains no substances with occupational exposure limit values.

Engineering measures
Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures
Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures
Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection
Tightly fitting safety goggles

Hand protection
Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:
Acid-resistant protective clothing.

Respiratory protection
required when vapors/aerosols are generated.
Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	odorless
Odor Threshold	No information available.
pH	at 68 °F (20 °C) strongly acid
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	1.53 g/cm³ at 59 °F (15 °C)
Relative density	No information available.
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.

Viscosity, dynamic	No information available.
Explosive properties	No information available.
Oxidizing properties	The substance or mixture is classified as oxidizing with the category 1.
Corrosion	May be corrosive to metals.

SECTION 10. Stability and reactivity

Reactivity
Explosive

Chemical stability
The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions
Risk of explosion with:

semimetals, Antimony oxide, Metals, Hydrogen, Impurities, organic combustible substances, acetic acid, Halogenated hydrocarbon, Hydrogen halides, Fluorine, Ether, sulfoxides, metallic oxides, Alcohols, acetonitrile

sulfuric acid, Nitric acid, with, Organic Substances

Risk of explosion/exothermic reaction with:

metallic salts, Acetic anhydride, phenol, pyridine, Reducing agents, conc. sulfuric acid, nonmetallic oxides

Exothermic reaction with:

Ketones, phosphides, bases

Conditions to avoid
Warming (decomposition).

Incompatible materials
rubber, Light metals, Metals

Hazardous decomposition products
in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact

Acute oral toxicity
Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach.

Acute inhalation toxicity

Symptoms: burns of mucous membranes, Lungs, Possible damages:, Lung edema

Skin irritation
Mixture causes severe burns.

Eye irritation
Risk of blindness!
Mixture causes serious eye damage.

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information
Quantitative data on the toxicity of this product are not available.
Further toxicological data:
Strongly corrosive substance.
After uptake:
cardiac arrest
Further data:
Other dangerous properties can not be excluded.
Handle in accordance with good industrial hygiene and safety practice.

Ingredients

Perchloric acid
No information available.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish
LC100 Cyprinus carpio (Carp): 180 mg/l; 24 h

Persistence and degradability
No information available.

Bioaccumulative potential
No information available.

Mobility in soil
No information available.

Additional ecological information
Biological effects:

Harmful effect due to pH shift.

Forms corrosive mixtures with water even if diluted.
Further information on ecology
Discharge into the environment must be avoided.

Ingredients

Perchloric acid
No information available.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 1873
Proper shipping name	PERCHLORIC ACID
Class	5.1 (8)
Packing group	I
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 1873
Proper shipping name	PERCHLORIC ACID
Class	5.1 (8)
Packing group	I
Environmentally hazardous	--
Special precautions for user	yes
IATA (Passenger)	**Not permitted for transport**

Sea transport (IMDG)

UN number	UN 1873
Proper shipping name	PERCHLORIC ACID MORE THAN 50% BUT NOT MORE THAN 72%
Class	5.1 (8)
Packing group	I
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-Q

SECTION 15. Regulatory information

United States of America

SARA 313

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients
Perchloric acid

Pennsylvania Right To Know

Ingredients
Perchloric acid

New Jersey Right To Know

Ingredients
Perchloric acid

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	All components of the product are listed in the TSCA-inventory.
DSL:	All components of this product are on the Canadian DSL.
KOREA:	Not in compliance with the inventory

SECTION 16. Other information

Training advice
Provide adequate information, instruction and training for operators.

Labeling
Hazard pictograms



Signal Word
Danger

Hazard Statements
H271 May cause fire or explosion; strong oxidizer.
H290 May be corrosive to metals.
H314 Causes severe skin burns and eye damage.

Precautionary Statements
Prevention
P210 Keep away from heat.
P221 Take any precaution to avoid mixing with combustibles, heavy-metal compounds, acids and alkalis.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308 + P310 IF exposed or concerned: immediately call a POISON CENTER or doctor/ physician.

Full text of H-Statements referred to under sections 2 and 3.

H271	May cause fire or explosion; strong oxidizer.
H290	May be corrosive to metals.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.

Key or legend to abbreviations and acronyms used in the safety data sheet
Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date01/27/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.
All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.