



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/22/2013

Version 1.1

SECTION 1. Identification

Product identifier

Product number	102427
Product name	1-Chloro-2,4-dinitrobenzene GR for analysis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	---

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Acute toxicity, Category 3, Inhalation, H331
Acute toxicity, Category 3, Dermal, H311
Acute toxicity, Category 3, Oral, H301
Specific target organ systemic toxicity - repeated exposure, Category 2, H373
Acute aquatic toxicity, Category 1, H400
Chronic aquatic toxicity, Category 1, H410

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word

Danger

Hazard Statements

H301 + H311 + H331 Toxic if swallowed, in contact with skin or if inhaled.

H373 May cause damage to organs through prolonged or repeated exposure.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427
Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Version 1.1

H410 Very toxic to aquatic life with long lasting effects.

Precautionary Statements

P280 Wear protective gloves.

P273 Avoid release to the environment.

P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula $C_6H_3ClN_2O_4$ (Hill)

CAS-No. 97-00-7

Molar mass 202.55 g/mol

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

1-chloro-2,4-dinitrobenzene ($\geq 90\%$ - $\leq 100\%$)

97-00-7

SECTION 4. First aid measures

Description of first-aid measures

General advice

First aider needs to protect himself.

Inhalation

After inhalation: fresh air. If breathing stops: immediately apply artificial respiration, if necessary oxygen. Immediately call in physician.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Call a physician immediately.

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion

If swallowed: give water to drink (two glasses at most). Seek medical advice immediately. In exceptional cases only, if medical care is not available within one hour, induce vomiting (only in persons who are wide awake and fully conscious), administer activated charcoal (20 - 40 g in a 10% slurry) and consult a doctor as quickly as possible.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427
Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Version 1.1

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, irritant effects

The following applies to aromatic nitro compounds in general: systemic effect: methemoglobinemia with headache, cardiac dysrhythmias, drop in blood pressure, dyspnoea, and spasms; principal sign: cyanosis (blue discoloration of the blood).

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Carbon dioxide (CO₂), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible material

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

nitrogen oxides, Hydrogen chloride gas

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid inhalation of dusts in all circumstances. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427
Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Version 1.1

SECTION 7. Handling and storage

Precautions for safe handling

Work under hood. Do not inhale substance/mixture.

Conditions for safe storage, including any incompatibilities

Dry. Tightly closed. Keep in a well-ventilated place. Keep locked up or in an area accessible only to qualified or authorized persons.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance. Work under hood. Do not inhale substance/mixture.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	solid
Color	light yellow
Odor	characteristic
Odor Threshold	No information available.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	102427	Version 1.1
Product name	1-Chloro-2,4-dinitrobenzene GR for analysis	

pH	No information available.
Melting point	48 - 52 °C
Boiling point/boiling range	599 °F (315 °C) at 1,013 hPa
Flash point	381 °F (194 °C)
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	1.9 %(V)
Upper explosion limit	22 %(V)
Vapor pressure	1 hPa at 223 °F (106 °C)
Relative vapor density	No information available.
Relative density	1.7 g/cm ³ at 68 °F (20 °C)
Water solubility	0.36 g/l at 68 °F (20 °C)
Partition coefficient: n-octanol/water	log Pow: 2.17 (experimental) (Lit.)
	Bioaccumulation is not expected (log Pow <1).
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	No information available.
Ignition temperature	867 °F (464 °C)
Bulk density	ca. 760 kg/m ³

SECTION 10. Stability and reactivity

Reactivity

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427
Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Version 1.1

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

Alkali metals, Alcohols, nitrogen oxides, organic nitro compounds, chlorates, Nitric acid, Water, Organic Substances, aluminum halides, phenols

Risk of explosion with:

Ammonia, Hydrazine hydrate

Conditions to avoid

Strong heating (explosive decomposition).

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Acute oral toxicity

LD50 rat: 640 mg/kg (RTECS)

Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract.

absorption

Acute inhalation toxicity

Symptoms: Irritation symptoms in the respiratory tract.

absorption

Acute toxicity estimate: 0.6 mg/l

Expert judgment

Acute dermal toxicity

LD50 rabbit: 130 mg/kg
(RTECS)

absorption

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

102427

Version 1.1

Product name

1-Chloro-2,4-dinitrobenzene GR for analysis

Skin irritation

rabbit

Result: Severe irritations
(IUCLID)

Severe irritations

(Regulation (EC) No 1272/2008, Annex VI)

Eye irritation

rabbit

Result: Severe irritations
(IUCLID)

Severe eye irritation

(Regulation (EC) No 1272/2008, Annex VI)

Sensitization

In animal experiments:

Result: positive

Method: OECD Test Guideline 406

(Regulation (EC) No 1272/2008, Annex VI)

Genotoxicity in vitro

Ames test

Result: positive
(IUCLID)

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

May cause damage to organs through prolonged or repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

ACGIH

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427
Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Version 1.1

Methemoglobin formation after intensive contact with skin cannot be excluded.

Other information

The following applies to aromatic nitro compounds in general: systemic effect: methemoglobinemia with headache, cardiac dysrhythmias, drop in blood pressure, dyspnoea, and spasms; principal sign: cyanosis (blue discoloration of the blood).

Further data:

This substance should be handled with particular care.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 Danio rerio (zebra fish): 0.71 mg/l; 96 h

OECD Test Guideline 203

Toxicity to daphnia and other aquatic invertebrates

EC50 Daphnia magna (Water flea): 0.49 mg/l; 48 h (ECOTOX Database)

Persistence and degradability

Biodegradability

Not readily biodegradable.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 2.17

(experimental)

(Lit.)

Bioaccumulation is not expected (log Pow <1).

Mobility in soil

No information available.

Additional ecological information

Biological effects:

Hazard for drinking water supplies.

Further information on ecology

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427
Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Version 1.1

SECTION 14. Transport information

Land transport (DOT)

UN number UN 3441
Proper shipping name CHLORODINITROBENZENES, SOLID
Class 6.1
Packing group II
Environmentally hazardous --

Air transport (IATA)

UN number UN 3441
Proper shipping name CHLORODINITROBENZENES, SOLID
Class 6.1
Packing group II
Environmentally hazardous --
Special precautions for user no

Sea transport (IMDG)

UN number UN 3441
Proper shipping name CHLORODINITROBENZENES, SOLID
Class 6.1
Packing group II
Environmentally hazardous --
Special precautions for user yes
EmS F-A S-A

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Harmful if swallowed.

Highly toxic by skin absorption

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427

Version 1.1

Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients

1-chloro-2,4-dinitrobenzene

Pennsylvania Right To Know

Ingredients

1-chloro-2,4-dinitrobenzene

New Jersey Right To Know

Ingredients

1-chloro-2,4-dinitrobenzene

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 102427

Version 1.1

Product name 1-Chloro-2,4-dinitrobenzene GR for analysis

Full text of H-Statements referred to under sections 2 and 3.

H301	Toxic if swallowed.
H311	Toxic in contact with skin.
H331	Toxic if inhaled.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 08/22/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.