

Product Specifications

VWR Part Number:	IR1911
ImmunoReagents, Inc. Part Number:	GtxMu-003-J2
Product:	GOAT X MOUSE IGG AP 1VL
Concentration:	> 4.5 mg/ml (E 1% at 280 nm = 13.0)
Amount:	1.0 mg
Conjugate:	Unconjugated
Form:	Clear, colorless liquid, 0.2 µm filtered
Purification:	Affinity purified using solid phase Mouse IgG
Purity:	> 90% based on SDS-PAGE Small amounts of intact IgG may be present.
Host:	Goat
Immunogen:	Purified Mouse IgG, whole molecule
Buffer: Protease/IgG free	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA,
Storage:	2-8 °C
Shelf Life:	1 year from date of receipt. Prepare working dilution prior to use and then discard.
Specificity:	Based on IEP, this antibody reacts with: · heavy (?) chains on mouse IgG · light chains on all mouse immunoglobulins
Cross Reactivity:	Based on IEP, no reactivity is observed to: · non-immunoglobulin mouse serum immunoglobulins · serum proteins from bovine, horse, human rabbit or swine
Country of Origin:	Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.
Applications:	This antibody is suitable for all immunoassay applications. The optimal working dilution should be determined by the investigator.

Disclaimer: For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.