

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 09/21/2015

Version 1.1

#### **SECTION 1.Identification**

## Product identifier

Product number 107872

Product name Strontium nitrate for analysis EMSURE®

CAS-No. 10042-76-9

## Relevant identified uses of the substance or mixture and uses advised against

Identified uses Reagent for analysis

## Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

#### **SECTION 2. Hazards identification**

## **GHS Classification**

Oxidizing solid, Category 1, H271 Serious eye damage, Category 1, H318

For the full text of the H-Statements mentioned in this Section, see Section 16.

## **GHS-Labeling**

Hazard pictograms





Signal Word
Danger

Hazard Statements

H271 May cause fire or explosion; strong oxidizer.

H318 Causes serious eye damage.

Precautionary Statements

P210 Keep away from heat.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

P220 Keep/Store away from clothing/ combustible materials.

P221 Take any precaution to avoid mixing with combustibles.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

P283 Wear fire/ flame resistant/ retardant clothing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact

lenses, if present and easy to do. Continue rinsing.

P306 + P360 IF ON CLOTHING: rinse immediately contaminated clothing and skin with plenty of water before removing clothes.

P310 Immediately call a POISON CENTER or doctor/ physician.

P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

P371 + P380 + P375 In case of major fire and large quantities: Evacuate area. Fight fire remotely due to the risk of explosion.

P501 Dispose of contents/ container to an approved waste disposal plant.

#### Other hazards

None known.

## SECTION 3. Composition/information on ingredients

Formula  $Sr(NO_3)_2$   $N_2O_6Sr$  (Hill)

Molar mass 211.63 g/mol

#### Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Strontium nitrate (>= 90 % - <= 100 % )

10042-76-9

Exact percentages are being withheld as a trade secret.

## **SECTION 4. First aid measures**

#### Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eve contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

#### Most important symptoms and effects, both acute and delayed

Irritation and corrosion, Nausea, Vomiting

Risk of serious damage to eyes.

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

The following applies to strontium compounds in general: only slightly absorbable via the gastrointestinal tract.

#### Indication of any immediate medical attention and special treatment needed

No information available.

# **SECTION 5. Fire-fighting measures**

## Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

## Special hazards arising from the substance or mixture

Not combustible.

Has a fire-promoting effect due to release of oxygen.

Ambient fire may liberate hazardous vapors.

Fire may cause evolution of:

nitrous gases

## Advice for firefighters

Special protective equipment for fire-fighters

In the event of fire, wear self-contained breathing apparatus.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

## SECTION 6. Accidental release measures

## Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid generation of dusts; do not inhale dusts. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

## **Environmental precautions**

Do not empty into drains.

## Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

## SECTION 7. Handling and storage

## Precautions for safe handling

Observe label precautions.

## Conditions for safe storage, including any incompatibilities

Tightly closed. Dry. Away from combustible materials and sources of ignition and heat.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

Store at +5°C to +30°C (+41°F to +86°F).

## SECTION 8. Exposure controls/personal protection

## Exposure limit(s)

Contains no substances with occupational exposure limit values.

## **Engineering measures**

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

## Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

## Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

## Eye/face protection

Safety glasses

#### Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

#### Respiratory protection

required when dusts are generated.

## SECTION 9. Physical and chemical properties

Physical state solid

Color white

Odor odorless

Odor Threshold No information available.

pH ca. 5 - 7

at 50 g/l 20 °C (20 °C)

Melting point 570 °C

Boiling point/boiling range 645 °C (645 °C)

Flash point No information available.

Evaporation rate No information available.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

Flammability (solid, gas) No information available.

Lower explosion limit No information available.

Upper explosion limit No information available.

Vapor pressure No information available.

Relative vapor density No information available.

Density 2.986 g/cm3

at 20 °C (20 °C)

Relative density No information available.

Water solubility 660 g/l

at 20 °C (20 °C)

Partition coefficient: n-

octanol/water

log Pow: 0.19 (calculated)

(Lit.) Bioaccumulation is not expected.

Autoignition temperature No information available.

Decomposition temperature No information available.

Viscosity, dynamic No information available.

Explosive properties Not classified as explosive.

Oxidizing properties The substance or mixture is classified as oxidizing with the

category 1.

Bulk density ca.1,000 kg/m3

## SECTION 10. Stability and reactivity

## Reactivity

polymerizable

#### Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

#### Possibility of hazardous reactions

combustible substances, Powdered metals, sulfur, oxidizable substances, Polyvinyl chloride Violent reactions possible with:

#### Conditions to avoid

no information available

#### Incompatible materials

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

no information available

## Hazardous decomposition products

in the event of fire: See section 5.

## **SECTION 11. Toxicological information**

## Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact, Ingestion

Acute oral toxicity

LD50 Rat: > 2,000 mg/kg OECD Test Guideline 423

Symptoms: After uptake of large quantities:, Nausea, Vomiting

Acute inhalation toxicity

LC50 Rat: > 4.5 mg/l; 4 h; dust/mist

**OECD Test Guideline 403** 

Symptoms: Possible damages:, mucosal irritations

Skin irritation In vitro study

Result: No skin irritation Human Skin Model Test

Eye irritation Rabbit

Result: Irreversible effects on the eye

OECD Test Guideline 405

Causes serious eye damage.

Sensitization

Maximization Test (GPMT) Guinea pig Result: Does not cause skin sensitization.

Method: OECD Test Guideline 406

The value is given in analogy to the following substances: strontium chloride hexahydrate

Genotoxicity in vitro

In vitro mammalian cell gene mutation test

MOUSE LYMPHOMA TEST

Result: negative

Method: OECD Test Guideline 476

Mutagenicity (mammal cell test): chromosome aberration.

Human lymphocytes Result: negative

Method: OECD Test Guideline 405

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

## Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

#### Further information

Other information

The following applies to strontium compounds in general: only slightly absorbable via the gastrointestinal tract.

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

Further data:

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

#### **SECTION 12. Ecological information**

#### **Ecotoxicity**

Toxicity to fish

static test LC50 Cyprinus carpio (Carp): > 97.5 mg/l; 96 h

Analytical monitoring: yes OECD Test Guideline 203

Toxicity to daphnia and other aquatic invertebrates

static test LC50 Daphnia magna (Water flea): 125 mg/l; 48 h (ECHA)

Toxicity to algae

static test ErC50 Pseudokirchneriella subcapitata (green algae): > 104.7 mg/l; 72 h

Analytical monitoring: yes OECD Test Guideline 201

Toxicity to bacteria

static test EC50 activated sludge: > 100 mg/l; 3 h

**OECD Test Guideline 209** 

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

Toxicity to fish (Chronic toxicity)

flow-through test NOEC Danio rerio (zebra fish): >= 100 mg/l; 34 d

Analytical monitoring: yes OECD Test Guideline 210

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) semi-static test NOEC Daphnia magna (Water flea): 21 mg/l; 21 d

**OECD Test Guideline 211** 

## Persistence and degradability

Biodegradability

The methods for determining the biological degradability are not applicable to inorganic substances.

## Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 0.19 (calculated)

(Lit.) Bioaccumulation is not expected.

#### Mobility in soil

No information available.

Additional ecological information

We have no quantitative data concerning the ecological effects of this product.

Biological effects:

Depending on the concentration, phosphorus and/or nitrogen compounds may contribute to the eutrophication of drinking- water supplies.

Hazard for drinking water supplies.

Further information on ecology

Discharge into the environment must be avoided.

#### **SECTION 13. Disposal considerations**

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

# **SECTION 14. Transport information**

Land transport (DOT)

UN number UN 1507

Proper shipping name STRONTIUM NITRATE

Class 5.1
Packing group III
Environmentally hazardous --

Air transport (IATA)

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

UN number UN 1507

Proper shipping name STRONTIUM NITRATE

Class 5.1
Packing group III
Environmentally hazardous -Special precautions for user no

Sea transport (IMDG)

UN number UN 1507

Proper shipping name STRONTIUM NITRATE

Class 5.1

Packing group III

Environmentally hazardous -
Special precautions for user yes

EmS F-A S-Q

## **SECTION 15. Regulatory information**

#### **United States of America**

#### **SARA 313**

The following components are subject to reporting levels established by SARA Title III, Section 313:

Ingredients

Strontium nitrate 10042-76-9 100 %

## **SARA 302**

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

#### **Clean Water Act**

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

This product does not contain any toxic pollutants listed under the U.S. Clean Water Act Section 307

## **US State Regulations**

## Massachusetts Right To Know

Ingredients

Strontium nitrate

## Pennsylvania Right To Know

Ingredients

Strontium nitrate

#### **New Jersey Right To Know**

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

## Ingredients

Strontium nitrate

## California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

#### Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL

#### **SECTION 16. Other information**

#### Training advice

Provide adequate information, instruction and training for operators.

## Labeling

Hazard pictograms





# Signal Word Danger

## Hazard Statements

H271 May cause fire or explosion; strong oxidizer.

H318 Causes serious eye damage.

## Precautionary Statements

Prevention

P210 Keep away from heat.

P221 Take any precaution to avoid mixing with combustibles, heavy-metal compounds, acids and alkalis.

P280 Wear eye protection.

Response

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P313 Get medical advice/ attention.

## Full text of H-Statements referred to under sections 2 and 3.

H271 May cause fire or explosion; strong oxidizer.

H318 Causes serious eye damage.

## Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 107872 Version 1.1

Product name Strontium nitrate for analysis EMSURE®

## Revision Date09/21/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.