



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 01/27/2015

Version 2.1

SECTION 1. Identification

Product identifier

Product number	108450
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l Titripur®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 3, H226
Skin corrosion, Category 1A, H314
Serious eye damage, Category 1, H318

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements

H226 Flammable liquid and vapor.
H314 Causes severe skin burns and eye damage.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l	
	Titripur®	

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P233 Keep container tightly closed.
P240 Ground/bond container and receiving equipment.
P241 Use explosion-proof electrical/ ventilating/ lighting/ equipment.
P242 Use only non-sparking tools.
P243 Take precautionary measures against static discharge.
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing.
Rinse skin with water/ shower.
P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310 Immediately call a POISON CENTER or doctor/ physician.
P321 Specific treatment (see supplemental first aid instructions on this label).
P363 Wash contaminated clothing before reuse.
P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.
P403 + P235 Store in a well-ventilated place. Keep cool.
P405 Store locked up.
P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature Acetic acid solution.

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

acetic acid (>= 90 % - <= 100 %)

64-19-7

Exact percentages are being withheld as a trade secret.

trifluoromethanesulphonic acid (>= 1 % - < 5 %)

1493-13-6

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air. Call in physician.

Skin contact

After skin contact: wash off with plenty of water. Immediately remove contaminated clothing. If available swab with polyethylene glycol 400. Call a physician immediately.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c ($\text{CF}_3\text{SO}_3\text{H}$) = 0.1 mol/l	
	Titripur®	

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Do not attempt to neutralize.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, bronchitis, Shortness of breath, gastric spasms, Nausea, Vomiting,
Circulatory collapse, shock
Risk of corneal clouding.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Carbon dioxide (CO_2), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible material, Vapors are heavier than air and may spread along floors.
Forms explosive mixtures with air at elevated temperatures.
Development of hazardous combustion gases or vapors possible in the event of fire.
Fire may cause evolution of:
Hydrogen fluoride, Sulfur oxides, Acetic acid vapors

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols.
Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

No special precautionary measures necessary.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l Titripur®	

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® H⁺, Art. No. 101595).

Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep away from heat and sources of ignition. Keep container tightly closed in a dry and well-ventilated place.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
<i>acetic acid 64-19-7</i>			
ACGIH	Time Weighted Average (TWA):	10 ppm	
	Short Term Exposure Limit (STEL):	15 ppm	
NIOSH/GUIDE	Recommended exposure limit (REL):	10 ppm 25 mg/m ³	
	Short Term Exposure Limit (STEL):	15 ppm 37 mg/m ³	
OSHA_TRANS	PEL:	10 ppm 25 mg/m ³	
Z1A	Time Weighted Average (TWA):	10 ppm 25 mg/m ³	

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l Titripur®	

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Tightly fitting safety goggles

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Acid-resistant protective clothing.

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	of acetic acid
Odor Threshold	No information available.
pH	< 0.5 at 68 °F (20 °C)
Melting point	No information available.
Boiling point/boiling range	244 °F (118 °C) at 1,013 hPa
Flash point	104 °F (40 °C)
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l Titripur®	

Density	ca. 1.06 g/cm ³ at 68 °F (20 °C)
Relative density	No information available.
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	No information available.
Oxidizing properties	No information available.

SECTION 10. Stability and reactivity

Reactivity

Vapor/air-mixtures are explosive at intense warming.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Risk of explosion with:

Strong oxidizing agents, peroxi compounds, perchloric acid, chromosulfuric acid, nitrates, fuming sulfuric acid, phosphorus halides, hydrogen peroxide

Violent reactions possible with:

Metals, Iron, Zinc, magnesium, alkali hydroxides, nonmetallic halides, ethanolamine, Aldehydes, Alcohols, halogen-halogen compounds, chlorosulfonic acid, strong alkalis, Nitric acid

Conditions to avoid

Heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

various metals

Hazardous decomposition products

in the event of fire: See section 5.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l	
	Titripur®	

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Target Organs

Eyes

Skin

Respiratory system

teeth

Acute oral toxicity

Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach., Nausea, Vomiting, Pulmonary failure possible after aspiration of vomit.

Acute inhalation toxicity

Symptoms: Possible damages:, burns of mucous membranes, Pneumonia, bronchitis, Inhalation may lead to the formation of oedemas in the respiratory tract., Symptoms may be delayed.

Skin irritation

Mixture causes severe burns.

Eye irritation

Mixture causes serious eye damage. Risk of blindness! Risk of corneal clouding. Risk of perforation!

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l	
	Titripur®	

Further information

Quantitative data on the toxicity of this product are not available.

Further toxicological data:

Systemic effects:

Shortness of breath, gastric spasms, shock, Circulatory collapse, acidosis

Possible damages:

Damage to:

Kidney

Further data:

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

Ingredients

acetic acid

Acute oral toxicity

LD50 Rat: 3,310 mg/kg (RTECS)

Acute inhalation toxicity

LCLO Rat: 39.95 mg/l; 4 h (RTECS)

Skin irritation

Rabbit

Result: Causes burns.

(IUCLID)

Eye irritation

Rabbit

Result: Causes burns.

(IUCLID)

Germ cell mutagenicity

Genotoxicity in vitro

Ames test

Salmonella typhimurium

Result: negative

(National Toxicology Program)

Teratogenicity

Did not show teratogenic effects in animal experiments. (IUCLID)

trifluoromethanesulphonic acid

Acute oral toxicity

LD50 Rat: 1,605 mg/kg (External MSDS)

Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach.

Acute dermal toxicity

LD50 Rat: > 2,000 mg/kg (External MSDS)

Sensitization

Sensitization test (Magnusson and Kligman):

Result: negative

(External MSDS)

Germ cell mutagenicity

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l Titripur®	

Genotoxicity in vitro

Ames test

Result: negative

(External MSDS)

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Ingredients

acetic acid

Toxicity to fish

LC50 *Lepomis macrochirus* (Bluegill sunfish): 75 mg/l; 96 h (Lit.)

Toxicity to daphnia and other aquatic invertebrates

EC50 *E. sulcatum*: 78 mg/l; 72 h neutral (maximum permissible toxic concentration) (Lit.)

EC50 *Daphnia magna* (Water flea): 47 mg/l; 24 h (Lit.)

Toxicity to algae

IC50 *Scenedesmus quadricauda* (Green algae): 4,000 mg/l; 16 h (maximum permissible toxic concentration) (Lit.)

Toxicity to bacteria

EC50 *Pseudomonas putida*: 2,850 mg/l; 16 h neutral (maximum permissible toxic concentration) (Lit.)

microtox test EC50 *Photobacterium phosphoreum*: 11 mg/l; 15 min (IUCLID)

Biodegradability

99 %; 30 d

OECD Test Guideline 301D

(HSDB)

Readily biodegradable.

95 %; 5 d

OECD Test Guideline 302B

Readily eliminated from water

Biochemical Oxygen Demand (BOD)

880 mg/g (5 d)

(Lit.)

Ratio BOD/ThBOD

BOD5 76 %

(IUCLID)

Substance does not meet the criteria for PBT or vPvB according to Regulation (EC) No 1907/2006, Annex XIII.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l Titripur®	

trifluoromethanesulphonic acid

Toxicity to fish

LC50 Pimephales promelas (fathead minnow): > 2,000 mg/l; 96 h (External MSDS)

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 2920
Proper shipping name	CORROSIVE LIQUID, FLAMMABLE, N.O.S. (TRIFLUORO METHANE SULFONIC ACID, ACETIC ACID)
Class	8 (3)
Packing group	II
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 2920
Proper shipping name	CORROSIVE LIQUID, FLAMMABLE, N.O.S. (TRIFLUORO METHANE SULFONIC ACID, ACETIC ACID)
Class	8 (3)
Packing group	II
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 2920
Proper shipping name	CORROSIVE LIQUID, FLAMMABLE, N.O.S. (TRIFLUORO METHANE SULFONIC ACID, ACETIC ACID)
Class	8 (3)
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-E S-C
Segregation Group	0001 Acids

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l	
	Titripur®	

SECTION 15. Regulatory information

United States of America

SARA 313

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients

acetic acid

Pennsylvania Right To Know

Ingredients

acetic acid

New Jersey Right To Know

Ingredients

acetic acid

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

KOREA: Not in compliance with the inventory

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	108450	Version 2.1
Product name	Trifluoromethanesulfonic acid in anhydrous acetic acid c (CF ₃ SO ₃ H) = 0.1 mol/l	
	Titripur®	

Labeling

Hazard pictograms



Signal Word

Danger

Hazard Statements

H226 Flammable liquid and vapor.

H314 Causes severe skin burns and eye damage.

Precautionary Statements

Prevention

P210 Keep away from heat.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response

P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P308 + P310 IF exposed or concerned: immediately call a POISON CENTER or doctor/ physician.

Full text of H-Statements referred to under sections 2 and 3.

H226 Flammable liquid and vapor.

H314 Causes severe skin burns and eye damage.

H318 Causes serious eye damage.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 01/27/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.