



SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 01/26/2015

Version 1.3

SECTION 1. Identification

Product identifier

Product number	170301
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Corrosive to Metals, Category 1, H290
Skin irritation, Category 2, H315
Eye irritation, Category 2A, H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Warning

Hazard Statements

H290 May be corrosive to metals.
H315 Causes skin irritation.
H319 Causes serious eye irritation.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Precautionary Statements

P234 Keep only in original container.

P264 Wash skin thoroughly after handling.

P280 Wear protective gloves/ eye protection/ face protection.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P321 Specific treatment (see supplemental first aid instructions on this label).

P332 + P313 If skin irritation occurs: Get medical advice/ attention.

P337 + P313 If eye irritation persists: Get medical advice/ attention.

P362 Take off contaminated clothing and wash before reuse.

P390 Absorb spillage to prevent material damage.

P406 Store in corrosive resistant stainless steel container with a resistant inliner.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature

Aqueous solution

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

nitric acid ($\geq 1\%$ - $< 5\%$)

7697-37-2

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not let product enter drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemisorb® H⁺, Art. No. 101595).

Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed.

Requirements for storage areas and containers

No metal containers.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
<i>nitric acid 7697-37-2</i>			
ACGIH	Time Weighted Average (TWA):	2 ppm	
	Short Term Exposure Limit (STEL):	4 ppm	
NIOSH/GUIDE	Recommended exposure limit (REL):	2 ppm	
		5 mg/m ³	
	Short Term Exposure Limit (STEL):	4 ppm	
		10 mg/m ³	
OSHA_TRANS	PEL:	2 ppm	
		5 mg/m ³	
Z1A	Time Weighted Average (TWA):	2 ppm	
		5 mg/m ³	
	Short Term Exposure Limit (STEL):	4 ppm	
		10 mg/m ³	

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	odorless
Odor Threshold	Not applicable
pH	ca. 0.5 at 68 °F (20 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	Not applicable
Evaporation rate	No information available.
Flammability (solid, gas)	Not applicable
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Density	ca. 1.017 g/cm ³ at 68 °F (20 °C)
Relative density	No information available.
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Explosive properties	Not classified as explosive.
Oxidizing properties	none
Corrosion	May be corrosive to metals.

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

increased reactivity with:

oxidizable substances, organic solvent, Metals, metal alloys, Alkali metals, Alkaline earth metals, Ammonia, alkalines, acids

Conditions to avoid

Heating.

Incompatible materials

Metals, metal alloys
(generation of hydrogen)

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Target Organs

Eyes

Skin

Respiratory system

teeth

Acute oral toxicity

Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract.

Acute inhalation toxicity

Symptoms: Possible damages:., mucosal irritations

Skin irritation

Mixture causes skin irritation.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Eye irritation

Mixture causes serious eye irritation.

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.

Other information

The following applies to aluminum compounds in general: After swallowing: only slightly absorbable via the gastrointestinal tract. Serious disorders in man (from about 4000 mg aluminum up): phosphate metabolism, calcium metabolism.

The following applies to nitrites/nitrates in general: methemoglobinemia after the uptake of large quantities.

Further data:

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

Ingredients

nitric acid

Skin irritation

Rabbit

Result: Causes severe burns.

(IUCLID)

Eye irritation

Rabbit

Result: Causes burns.

(IUCLID)

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Germ cell mutagenicity
Genotoxicity in vitro
Ames test
Salmonella typhimurium
Result: negative
Method: OECD Test Guideline 471

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

Biological effects:

Harmful effect due to pH shift. Caustic even in diluted form. Hazard for drinking water supplies.

Further information on ecology

Depending on the concentration, phosphorus and/or nitrogen compounds may contribute to the eutrophication of drinking- water supplies.

Discharge into the environment must be avoided.

Ingredients

nitric acid

Toxicity to fish

LC50 *Gambusia affinis* (Mosquito fish): 72 mg/l; 96 h (IUCLID)

Biodegradability

The methods for determining the biological degradability are not applicable to inorganic substances.

Substance does not meet the criteria for PBT or vPvB according to Regulation (EC) No 1907/2006, Annex XIII.

Henry constant

2482 Pa·m³/mol

Method: (calculated)

(Lit.) Distribution preferentially in air.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID NOT MORE THAN 5%)
Class	8
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID SOLUTION)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID NOT MORE THAN 5%)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-B

SECTION 15. Regulatory information

United States of America

SARA 313

The following components are subject to reporting levels established by SARA Title III, Section 313:

Ingredients

nitric acid	7697-37-2	2.4067 %
-------------	-----------	----------

SARA 302

The following components are subject to reporting levels established by SARA Title III, Section 302:

Ingredients

nitric acid	7697-37-2
-------------	-----------

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Ingredients

nitric acid

Pennsylvania Right To Know

Ingredients

nitric acid

New Jersey Right To Know

Ingredients

nitric acid

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA: All components of the product are listed in the TSCA-inventory.

DSL: All components of this product are on the Canadian DSL.

KOREA: Not in compliance with the inventory

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Labeling

Hazard pictograms



Signal Word

Warning

Hazard Statements

H290 May be corrosive to metals.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	170301	Version 1.3
Product name	Aluminium ICP standard traceable to SRM from NIST $\text{Al}(\text{NO}_3)_3$ in HNO_3 2-3% 1000 mg/l Al Certipur®	

Precautionary Statements

Response

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P313 Get medical advice/ attention.

Full text of H-Statements referred to under sections 2 and 3.

H290	May be corrosive to metals.
H315	Causes skin irritation.
H319	Causes serious eye irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 01/26/2015

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.