

Reviewed on 12/13/2012

1 Identification of the substance/mixture and of the company/undertaking

· Product identifier

· Trade name: Iodoacetamide

· Article number: 100351

· CAS Number: 144-48-9 · EC number: 205-630-1

· Details of the supplier of the safety data sheet

· Manufacturer/Supplier: MP Biomedicals, LLC 29525 Fountain Parkway Solon, OH 44139 **United States** www.mpbio.com

· Information department: Product safety department

· Emergency telephone number: CHEMTREC: 1-800-424-9300 (1-703-527-3887)

2 Hazards identification

· Classification of the substance or mixture



GHS06 Skull and crossbones

Acute Tox. 3 H301 Toxic if swallowed.

Acute Tox. 3 H311 Toxic in contact with skin.

Acute Tox. 3 H331 Toxic if inhaled.

· Classification according to Directive 67/548/EEC or Directive 1999/45/EC



Toxic by inhalation, in contact with skin and if swallowed.

- · Information concerning particular hazards for human and environment: Not applicable.
- · Label elements
- · GHS label elements

The substance is classified and labelled according to the Globally Harmonized System (GHS).

· Hazard pictograms



GHS06

- · Signal word Danger
- · Hazard-determining components of labelling:

2-iodoacetamide

· Hazard statements

Toxic if swallowed, in contact with skin or if inhaled.

· Precautionary statements

If medical advice is needed, have product container or label at hand.

Keep out of reach of children.

Read label before use.

(Contd. on page 2)

Printing date 12/13/2012 Reviewed on 12/13/2012

Trade name: Iodoacetamide

(Contd. of page 1)

Avoid breathing dust/fume/gas/mist/vapours/spray.

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

Remove/Take off immediately all contaminated clothing.

Specific treatment (see on this label).

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

- · Classification system:
- · NFPA ratings (scale 0 4)



Health = 3Fire = 0Reactivity = 0

· HMIS-ratings (scale 0 - 4)



3 Health = 3Fire = 0

- · Other hazards
- · Results of PBT and vPvB assessment
- · **PBT**: Not applicable.
- · vPvB: Not applicable.

3 Composition/information on ingredients

- · Chemical characterization: Substances
- · CAS No. Description

144-48-9 2-iodoacetamide

- · Identification number(s)
- · EC number: 205-630-1

4 First aid measures

- · Description of first aid measures
- · General information:

Immediately remove any clothing soiled by the product.

Remove breathing apparatus only after contaminated clothing have been completely removed.

In case of irregular breathing or respiratory arrest provide artificial respiration.

· After inhalation:

Supply fresh air or oxygen; call for doctor.

In case of unconsciousness place patient stably in side position for transportation.

- · After skin contact: Immediately wash with water and soap and rinse thoroughly.
- · After eye contact: Rinse opened eye for several minutes under running water. Then consult a doctor.
- · After swallowing: Do not induce vomiting; immediately call for medical help.
- · Information for doctor:
- · Most important symptoms and effects, both acute and delayed No further relevant information available.
- · Indication of any immediate medical attention and special treatment needed

No further relevant information available.

Printing date 12/13/2012 Reviewed on 12/13/2012

Trade name: Iodoacetamide

(Contd. of page 2)

5 Firefighting measures

- · Extinguishing media
- · Suitable extinguishing agents:

CO2, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- · Special hazards arising from the substance or mixture No further relevant information available.
- · Advice for firefighters
- · Protective equipment: Mouth respiratory protective device.

6 Accidental release measures

- · Personal precautions, protective equipment and emergency procedures Not required.
- Environmental precautions: Do not allow to enter sewers/ surface or ground water.
- · Methods and material for containment and cleaning up:

Dispose contaminated material as waste according to item 13.

Ensure adequate ventilation.

· Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage

- · Handling:
- · Precautions for safe handling

Thorough dedusting.

Ensure good ventilation/exhaustion at the workplace.

Open and handle receptacle with care.

- · Information about protection against explosions and fires: Keep respiratory protective device available.
- · Conditions for safe storage, including any incompatibilities
- · Storage: <0°C
- Requirements to be met by storerooms and receptacles: No special requirements.
- · Information about storage in one common storage facility: Not required.
- · Further information about storage conditions:

Protect from exposure to the light.

Keep receptacle tightly sealed.

· Specific end use(s) No further relevant information available.

8 Exposure controls/personal protection

- · Additional information about design of technical systems: No further data; see item 7.
- · Control parameters
- · Components with limit values that require monitoring at the workplace: Not required.
- · Additional information: The lists that were valid during the creation were used as basis.
- · Exposure controls
- · Personal protective equipment:
- · General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

(Contd. on page 4)

Printing date 12/13/2012 Reviewed on 12/13/2012

Trade name: Iodoacetamide

(Contd. of page 3)

Store protective clothing separately.

Avoid contact with the eyes and skin.

· Breathing equipment:

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· Protection of hands:



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection: Not required.

9 Physical	and	chemical	properties
> I Ivybrowi	CUI VCV	Citciitteat	properties

Melting point/Melting range:

· Density at $20^{\circ}C$ (68 °F):

· Information on basic physic · General Information	al and chemical properties	
· Appearance:		
Form:	Solid	
Color:	Not determined.	
· Odor:	Characteristic	
· Odour threshold:	Not determined.	
· pH-value:	Not applicable.	
· Change in condition		

92-95°C (198-203 °F)

Boiling point/Boiling range:	Undetermined.
· Flash point:	Not applicable.

· Flammability (solid, gaseous):	Product is not flammable.	
· Ignition temperature:		
Decomposition temperature:	Not determined.	
· Auto igniting:	Not determined.	
· Danger of explosion:	Product does not present an explosion hazard.	
· Explosion limits:		
Lower:	Not determined.	
Upper:	Not determined.	
· Vapor pressure:	Not applicable.	

1 g/cm³ (8.345 lbs/gal)

(Contd. on page 5)

Printing date 12/13/2012 Reviewed on 12/13/2012

Trade name: Iodoacetamide

(Contd. of page 4) · Relative density Not determined. · Vapour density Not applicable. Not applicable. · Evaporation rate · Solubility in / Miscibility with Insoluble. Water: · Partition coefficient (n-octanol/water): Not determined. Dynamic: Not applicable. Kinematic: Not applicable. Organic solvents: 0.0%Solids content: · Other information No further relevant information available.

10 Stability and reactivity

- · Reactivity
- · Chemical stability
- · Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.
- · Possibility of hazardous reactions No dangerous reactions known.
- · Conditions to avoid No further relevant information available.
- · Incompatible materials: No further relevant information available.
- · Hazardous decomposition products: No dangerous decomposition products known.

11 Toxicological information

- · Information on toxicological effects
- · Acute toxicity:
- · LD/LC50 values that are relevant for classification:

144-48-9 2-iodoacetamide

Oral LD50 74 mg/kg (mouse)

- · Primary irritant effect:
- · on the skin: No irritant effect.
- · on the eve: No irritating effect.
- · Sensitization: No sensitizing effects known.
- · Additional toxicological information:
- · Carcinogenic categories
- · IARC (International Agency for Research on Cancer)

Substance is not listed.

· NTP (National Toxicology Program)

Substance is not listed.

12 Ecological information

- · Toxicity
- $\cdot \textbf{\textit{Aquatic toxicity:}} \ \textit{No further relevant information available}.$
- · Persistence and degradability No further relevant information available.

(Contd. on page 6)

Printing date 12/13/2012 Reviewed on 12/13/2012

Trade name: Iodoacetamide

(Contd. of page 5)

- · Behavior in environmental systems:
- · Bioaccumulative potential No further relevant information available.
- · Mobility in soil No further relevant information available.
- Additional ecological information:
- · General notes:

Water hazard class 2 (Self-assessment): hazardous for water

Do not allow product to reach ground water, water course or sewage system.

Danger to drinking water if even small quantities leak into the ground.

- · Results of PBT and vPvB assessment
- · **PBT**: Not applicable.
- · vPvB: Not applicable.
- · Other adverse effects No further relevant information available.

13 Disposal considerations

- · Waste treatment methods
- · Recommendation:

Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

- · Uncleaned packagings:
- · Recommendation: Disposal must be made according to official regulations.

14 Transport information	
· UN-Number · DOT, ADR, IMDG, IATA	UN2811
· UN proper shipping name · DOT, IMDG, IATA · ADR	TOXIC SOLID, ORGANIC, N.O.S. 2811 TOXIC SOLID, ORGANIC, N.O.S.
· Transport hazard class(es)	
· DOT	
TOXIC 6	
· Class	6.1 Toxic substances.
· Label	6.1
· ADR, IMDG, IATA	
\$	
· Class	6.1 Toxic substances
· Label	6.1
· Packing group · DOT, ADR, IMDG, IATA	III

(Contd. on page 7)
USA

Printing date 12/13/2012 Reviewed on 12/13/2012

Trade name: Iodoacetamide

(Contd. of page 6)

· Environmental hazards:

· Marine pollutant: No

· Special precautions for user Warning: Toxic substances

Danger code (Kemler):
 EMS Number:
 F-A,S-A

· Transport in bulk according to Annex II of

MARPOL73/78 and the IBC Code Not applicable.

· UN "Model Regulation": UN2811, TOXIC SOLID, ORGANIC, N.O.S., 6.1, III

15 Regulatory information

- · Safety, health and environmental regulations/legislation specific for the substance or mixture
- · Sara
- · Section 355 (extremely hazardous substances):

Substance is not listed.

· Section 313 (Specific toxic chemical listings):

Substance is not listed.

· TSCA (Toxic Substances Control Act):

Substance is listed.

- · Proposition 65
- · Chemicals known to cause cancer:

Substance is not listed.

· Chemicals known to cause reproductive toxicity for females:

Substance is not listed.

· Chemicals known to cause reproductive toxicity for males:

Substance is not listed.

· Chemicals known to cause developmental toxicity:

Substance is not listed.

- · Carcinogenic categories
- · EPA (Environmental Protection Agency)

Substance is not listed.

· TLV (Threshold Limit Value established by ACGIH)

Substance is not listed.

· NIOSH-Ca (National Institute for Occupational Safety and Health)

Substance is not listed.

· OSHA-Ca (Occupational Safety & Health Administration)

Substance is not listed.

· GHS label elements

The substance is classified and labelled according to the Globally Harmonized System (GHS).

(Contd. on page 8)

Printing date 12/13/2012 Reviewed on 12/13/2012

Trade name: Iodoacetamide

· Hazard pictograms

(Contd. of page 7)



- · Signal word Danger
- · Hazard-determining components of labelling:

2-iodoacetamide

· Hazard statements

Toxic if swallowed, in contact with skin or if inhaled.

· Precautionary statements

If medical advice is needed, have product container or label at hand.

Keep out of reach of children.

Read label before use.

Avoid breathing dust/fume/gas/mist/vapours/spray.

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

Remove/Take off immediately all contaminated clothing.

Specific treatment (see on this label).

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- · Department issuing MSDS: Product safety department
- · Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists EINECS: European Inventory of Existing Commercial Chemical Substances CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

- USA