
Product Specifications

VWR Part Number:	IR1826
ImmunoReagents, Inc. Part Number:	GtxHu-006-DRHOX
Product:	GOAT X HU IGM MU TRITC 1VL
Concentration:	1.0 mg/ml (E 1% at 280 nm = 13.0)
Amount:	1.0 mg
Conjugate:	Tetramethylrhodamine-5-isothiocyanate (TRITC) Amax = 550 nm; Emax = 570 nm
Form:	Lyophilized
Purification:	Affinity purified using solid phase Human IgM
Purity:	Affinity purified antibody is > 95% based on SDS-PAGE
Host:	Goat
Immunogen:	Purified Human IgM, μ chain
Buffer: Protease/IgG free	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA,
Storage:	2-8 °C
Shelf Life:	1 year from date of receipt. Prepare working dilution prior to use and then discard.
Specificity:	Based on IEP, this antibody reacts with: · heavy (?) chains on human IgM
Cross Reactivity:	Based on IEP, no reactivity is observed to: · non-immunoglobulin human serum proteins · light chains on all human immunoglobulins
Country of Origin:	Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.
Applications:	This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications
Disclaimer:	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.