

# Safety Data Sheet

## 94072 Flux Remover

# Stoner

Copying and/or downloading of this information for the purpose of properly utilizing Stoner Inc. product is allowed provided that: (1) the information is copied in full with no changes unless prior agreement is obtained from Stoner Inc., & (2) neither the copy nor the original is resold or otherwise distributed with intention of earning profit thereon.

### 1. IDENTIFICATION

Stoner Incorporated  
1070 Robert Fulton Hwy.  
Quarryville, PA 17566  
1-800-227-5538


Product Name: Flux Remover  
Product Code: 94072  
Product Use: Flux Remover  
24-hour emergency phone: 1-800-424-9300 [CHEMTREC]

### 2. HAZARD IDENTIFICATION

#### POTENTIAL HEALTH EFFECTS

Classification of the chemical in accordance with paragraph (d) of §1910.1200;

GHS Hazard  
Symbols



#### GHS Classification

Gases under pressure - Liquefied Gas  
Serious Eye Damage/Eye Irritation Category 2A  
Specific Target Organ Systemic Toxicity (STOT) - Single Exposure Category 3  
Simple Asphyxiant Category 1

#### Signal Word

Warning

#### Hazard Statements

Contains gas under pressure; may explode if heated.  
Causes serious eye irritation.  
May cause drowsiness or dizziness.  
May displace oxygen and cause rapid suffocation

#### Precautionary Statements

##### Prevention

Avoid breathing dust/fume/gas/mist/vapours/spray.  
Wash thoroughly after handling.  
Use only outdoors or in a well-ventilated area.  
Wear protective gloves/protective clothing/eye protection/face protection.

##### Response

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.  
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.  
Continue rinsing.  
Call a POISON CENTER or doctor/physician if you feel unwell.  
If eye irritation persists: Get medical advice/attention.

##### Storage

Store in a well-ventilated place. Keep container tightly closed.  
Store locked up.  
Protect from sunlight. Store in a well-ventilated place.

##### Disposal

Dispose of contents/container in accordance with local/regional/national/international regulation for hazardous wastes.

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

COMPONENT	CAS #	Percent
NJ Trade Secret Registry	#80100382-5152P	60 - 80
Halogenated hydrocarbon	811-97-2	1-20
Dimethyl carbinol	67-63-0	1-20

#### HMIS® III\* HAZARDOUS WARNINGS:

Health: 2

Flammability: 2

Physical: 0

Personal Protective  
Equipment: See Section 8

\* See [www.paint.org/hmis](http://www.paint.org/hmis) or call the NPCA at 1 (202) 462-6272 for more information on this current rating system.

#### 4. FIRST AID MEASURES

Eyes:	Immediately flush eyes gently with plenty of water for at least 15 minutes while holding eyelids apart. If symptoms persist or there is visual difficulty, seek medical attention.
Skin Contact:	In case of contact, immediately wash contaminated area with plenty of water for at least 15 minutes. Seek medical attention if symptoms persist. Wash clothing before reuse.
Ingestion:	Do not induce vomiting. Contact a physician, medical facility, or poison control center immediately.
Inhalation:	Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Seek immediate medical attention. Keep the victim warm and quiet.

#### NOTES TO PHYSICIAN:

Because of possible disturbances of cardiac rhythm, catecholamine drugs, such as epinephrine, should be used only in situations of emergency life support.

#### 5. FIRE FIGHTING MEASURES

Fire and/or Explosion Hazards:	This product contains a component(s) that is considered a flammable liquid, which has vapors that are heavier than air and may travel along the ground or be moved by ventilation and ignited by heat, pilot lights, or other flames and ignition sources at locations distant from the material's handling point. Hazardous decomposition products may be formed (see Sec.10). Containers may rupture or explode under fire conditions.
Fire Fighting Instructions:	Use CO <sub>2</sub> , foam or dry chemical. Fire fighters should wear normal protective equipment and positive-pressure self-contained breathing apparatus. Avoid breathing the products and substances that may result from the thermal decomposition of the product or other substances in the fire zone. Water is generally not effective and may spread fire; however, water spray may be used from a safe distance to cool closed containers and protect surrounding area.

#### 6. ACCIDENTAL RELEASE MEASURES

##### STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED:

Ventilate contaminated area. Wear appropriate personal protective equipment (PPE). Stop or reduce discharge if it can be done safely. Avoid run-off into storm sewers and ditches which may lead to natural waterways. Clean up with absorbent material. Place absorbent materials into container and close it tightly. Dispose of container properly. Remove all sources of ignition. If runoff occurs, notify authorities as required.

#### 7. HANDLING AND STORAGE

Handling:	Use with adequate ventilation. Avoid prolonged or repeated contact with skin. Avoid prolonged or repeated breathing of vapor. Do not use near ignition sources. Do not breathe vapor. May cause frostbite. If ventilation is not sufficient, wear proper respiratory equipment. Do not store containers in excessive heat or direct sunlight. Protect container against physical damage. Normal precautions common to safe manufacturing practice should be followed in handling and storage.
Storage:	Store in a cool, dry, well ventilated area away from all sources of ignition. Store away from heat and direct sunlight. Do not store at temperatures above 120 degrees F. Empty container may contain residues which are hazardous.

#### 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering Controls:	Ventilation should be adequate to prevent exposures above the limits indicated below in this section of the MSDS (from known, suspected or apparent adverse effects). Local exhaust should be used in areas where exposure limits may be exceeded.
Eye Protection:	Wear chemically resistant safety glasses with side shields when handling this product. Wear additional eye protection such as chemical splash goggles and/or face shield when the possibility exists for eye contact with splashing or spraying liquid or airborne material. Have an eye wash station available.
Skin Protection:	The use of chemically resistant gloves is recommended if there is any possibility of prolonged or repeated liquid contact with skin.
Respiratory Protection:	Use NIOSH approved respirator where there is likelihood of inhalation of the product mist, spray or aerosol. A supplied air respirator should be used if ventilation is not sufficient to maintain exposure limits.

<u>COMPONENT</u>	<u>CAS #</u>	<u>ACGIH TLV</u>	<u>OSHA PEL</u>	<u>OTHER</u>
NJ Trade Secret Registry	#80100382-5152P	Not established	Not established	800 ppm (mfr. recommend)
Halogenated hydrocarbon	811-97-2	Not established	Not established	1000ppm (mfr. recommend)
Dimethyl carbinol	67-63-0	400 ppm	Not established	500 ppm STEL

## 9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State:	Aerosol can	Lower Flammability Limit (%):	Not applicable
Appearance:	Clear Colorless	Upper Flammability Limit (%):	Not applicable
Odor:	Characteristic	Vapor Pressure (PSIG @ 70°F):	Not determined
Odor Threshold:	Mild	Vapor Density [air = 1]:	>1
pH:	Not applicable	Relative Density (H2O=1):	Not applicable
Melting/Freezing Point (°F):	No data available	Solubility in Water:	Negligible; 0-1%
Boiling Point (°F):	No data available	Partial Coefficient: n-octanol/water:	No data available
Flash Point (°F PMCC):	Not applicable	Autoignition Temperature (°F):	Not applicable
Evaporation Rate:	Not determined	Decomposition Temperature (°F):	No data available
Flammability (solid, gas):	No data available	Viscosity, dynamic (cSt):	No data available
Percent VOCs (%):	1-20		

## 10. STABILITY AND REACTION

Chemical Stability:	Stable. Do not mix with oxygen or air above atmospheric pressure. Any source of high temperature [>250 C], may form hydrofluoric acid and possibly carbonyl fluoride decomposition products.
Conditions to Avoid:	Avoid contact with: Sparks, open flame, other ignition sources, and elevated temperatures. Can form a combustible mixture with air at pressures above atmospheric pressure. Do not mix with oxygen or air above atmospheric pressure. Ignition sources such as open flames, sparks, static discharges or glowing metal surfaces. Alkali. Alkaline earth metals. Freshly abraded aluminum surfaces. Powdered metals. Magnesium. Zinc. Chemically active metals: calcium, powdered aluminum, zinc, sodium, potassium, magnesium, etc. Acetaldehyde. Acids. Chlorine. Ethylene oxide. Isocyanates. Strong oxidizing agents.
Decomposition Products:	Burning can produce the following combustion products: Carbon dioxide and carbon monoxide. Hydrogen chloride. Hydrogen Chloride. Carbonyl halides. This material can be decomposed by extremely high temperatures (open flames, glowing metal surfaces, etc.) forming hydrofluoric acid and carbonyl fluoride.

## 11. TOXICOLOGICAL INFORMATION

Dermal Toxicity:	Not irritating to skin.
Inhalation Toxicity:	High concentrations may cause central nervous system depression resulting in headaches, dizziness and nausea; continued inhalation may result in unconsciousness and/or death.
Reproductive & Developmental Toxicity:	No data available.

Ingredient	CAS #	Toxicological Data
NJ Trade Secret Registry	#80100382-5152P	No data available Inhalation LC50 (4h) Rat 120000 ppm
Halogenated hydrocarbon	811-97-2	No data available Inhalation LC50 (4h) Rat > 500000 ppm
Dimethyl carbinol	67-63-0	Dermal LD50 Rabbit > 12800 mg/kg Oral LD50 Rat = 5000 mg/kg Inhalation LC50 (4h) Rat > 40 mg/L

## 12. ECOLOGICAL INFORMATION

Ecological Toxicity:	No data available
Mobility:	No data available This material (or one of its components), dissolves in water. If it enters the soil, it will be highly mobile and may contaminate ground water.

Ingredient	CAS #	Toxicological Data
NJ Trade Secret Registry	#80100382-5152P	Aquatic LC50 (96h) Rainbow Trout 38 mg/L 48HR EC50 Daphnia 82 mg/L 72HR EC50 Algae 106.7 mg/L Aquatic LC50 (96h) MINNOW = 9640 mg/L 24HR EC50 Daphnia > 10000 mg/L
Dimethyl carbinol	67-63-0	

## 13. DISPOSAL CONSIDERATIONS

Disposal : Dispose according to Federal, State and local regulations.

## 14. TRANSPORTATION INFORMATION

Agency	UN Number	Proper Shipping name	Hazard Class	Packing Group
DOT	UN1950	Aerosols, Non- Flammable†	2.2	Not applicable
IATA	ID8000	Consumer Commodity†	9	Not applicable
IMDG	UN1950	Aerosols, Non- Flammable†	2.2	Not applicable

† "Limited Quantities" may be applicable for this transportation mode.

## 15. REGULATORY INFORMATION

Warning: This product contains the following chemicals that are subject to reporting requirements for the following regulatory bodies listed below:

COMPONENT	CAS #	% BY WEIGHT	Regulatory Body
No components listed in this section.			
SARA Section 313			

Warning: This product may contain chemicals known to the State of California to cause cancer. See list below.

No components listed in this section.

Prop65 Cancer

Warning: This product may contain chemicals known to the State of California to cause birth defects. See list below.

No components listed in this section.

Prop65 Birth Defects

All components of this product are listed on the TSCA inventory.

## 16. OTHER INFORMATION

Other Information : MSDS Prepared by L. Dean Swartz, MSDS Coordinator

Version Date: 09/16/15

**This information contained in this MSDS is believed to be accurate as of the version date, but is not warranted to be. Since the use of this information and the conditions of use of this product are not within the control of Stoner Inc, it is the user's obligation to determine the conditions of safe use.**