
Product Specifications

VWR Part Number:	IR1437
ImmunoReagents, Inc. Part Number:	GtxDk-003-D633NHSX
Product:	GOAT X DONKEY IGG DYLGHT 633 1VL
Concentration:	1.0 mg/ml (E 1% at 280 nm = 13.0)
Amount:	1.0 mg
Conjugate:	DyLight® 633 (Ex = 638 nm; Em = 658 nm)
Form:	Lyophilized
Purification:	Affinity purified using solid phase Donkey IgG
Purity:	Affinity purified antibody is > 95% based on SDS-PAGE
Host:	Goat
Immunogen:	Purified Donkey IgG, whole molecule
Buffer: Protease/IgG free	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA,
Storage:	Store freeze-dried powder at 2-8 °C.
Shelf Life:	Product is stable for up to 4 weeks at 2-8°C after rehydration. For extended storage after rehydration, add an equal volume of glycerol and store at -20°C.
Specificity:	Based on IEP, this antibody reacts with: · heavy (?) chains on donkey IgG · light chains on all donkey immunoglobulins
Cross Reactivity: immunoglobulins	Based on IEP, no reactivity is observed to: · non-immunoglobulin donkey serum
Country of Origin:	Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.
Applications:	This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications
Disclaimer:	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.