



## Resistin Antibody

CATALOG NUMBER: 54-210

### Specifications

|                             |   |
|-----------------------------|---|
| <b>SPECIES REACTIVITY:</b>  | Human, Mouse  |
| <b>TESTED APPLICATIONS:</b> | ELISA, WB   |
| <b>APPLICATIONS:</b>        | Resistin antibody can be used at 1:2,000 to 1:5,000 for immunoblot or ELISA tests. User needs to optimize the concentrations in assays.                       |
| <b>USER NOTE:</b>           | Optimal dilutions for each application to be determined by the researcher.  |
| <b>SPECIFICITY:</b>         | Resistin antibody specifically binds to human resistin. The product may cross-react with bovine resistin but does not cross react with mouse or rat resistin. |
| <b>IMMUNOGEN:</b>           | Human Resistin peptide aa94-108   |
| <b>HOST SPECIES:</b>        | Chicken   |

### Properties

|                            |  |
|----------------------------|--|
| <b>PURIFICATION:</b>       | Affinity Purified  |
| <b>PHYSICAL STATE:</b>     | Liquid   |
| <b>BUFFER:</b>             | PBS Buffer containing 0.02% sodium azide.                                |
| <b>STORAGE CONDITIONS:</b> | 2-8°C for one week and -20°C as an undiluted liquid for up to two years. |
| <b>CLONALITY:</b>          | Polyclonal   |
| <b>CONJUGATE:</b>          | Unconjugated   |

### Additional Info

|                         |   |
|-------------------------|---|
| <b>ALTERNATE NAMES:</b> | FIZZ3, HXCP1, RSTN, UNQ407/PRO1199, Resistin, Adipose tissue-specific secretory factor, ADSF, XCP1, RETN1 |
| <b>ACCESSION NO.:</b>   | NP_065148.1   |
| <b>PROTEIN GI NO.:</b>  | 9966777   |
| <b>OFFICIAL SYMBOL:</b> | RETN  |
| <b>GENE ID:</b>         | 56729   |

### Background

FOR RESEARCH USE ONLY

December 13, 2016