



Influenza A virus (H3N2) Antibody (HRP)

CATALOG NUMBER: 35-287

Specifications

SPECIES REACTIVITY:	Virus
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Specific to purified virions
IMMUNOGEN:	Influenza A, strain Texas 1/77 (H3N2)
HOST SPECIES:	Goat

Properties

PURIFICATION:	Purified IgG fraction of antiserum covalently coupled with highly purified preparation of horseradish peroxidase (RZ>3). Care is taken to insure adequate conjugation while preserving the maximum enzyme activity. Free enzyme is absent.
PHYSICAL STATE:	Liquid
BUFFER:	Influenza A virus (H3N2) antibody is in a phosphate saline buffer with bovine serum albumin (10mg/ml) and preserved with 0.002% thimerosal.
STORAGE CONDITIONS:	Influenza A virus (H3N2) antibody can be stored at -20°C, stable for one year.
CLONALITY:	Polyclonal
CONJUGATE:	HRP

Additional Info

ALTERNATE NAMES:	Anti-Influenza A virus (H3N2) Peroxidase conjugate
-------------------------	--

Background

FOR RESEARCH USE ONLY

December 12, 2016