



prosci-inc.com



**ProSci Incorporated**  
12170 Flint Place  
Poway, CA 92064



**Toll Free:** +1 (888) 513 9525  
**Local:** +1 (858) 513 2638  
**Fax:** +1 (858) 513 2692

techsupport@prosci-inc.com

## Adenovirus Antibody (FITC)

CATALOG NUMBER: 35-102

### Specifications

<b>SPECIES REACTIVITY:</b>	Virus
<b>TESTED APPLICATIONS:</b>	WB
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>SPECIFICITY:</b>	Specific to numerous Adeno proteins including hexon
<b>IMMUNOGEN:</b>	Gradient purified, disrupted Adenovirus type 5 virions
<b>HOST SPECIES:</b>	Goat

### Properties

<b>PURIFICATION:</b>	Purified IgG fraction of antiserum covalently coupled with high purity Isomer I of fluorescein isothiocyanate. Care is taken to insure complete removal of any free fluorescein from the final product.
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	Adenovirus antibody is in a phosphate saline buffer (0.01M, pH 7.2) containing bovine serum albumin (10 mg/ml) as a stabilizer and 0.1% sodium azide preservative.
<b>STORAGE CONDITIONS:</b>	Adenovirus antibody can be stored at -20°C, stable for one year.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	FITC

### Additional Info

<b>ALTERNATE NAMES:</b>	Anti-Adenovirus Fluorescein conjugate
-------------------------	---------------------------------------

### Background

FOR RESEARCH USE ONLY

December 12, 2016