

## 1 Identification

- **Product identifier**
- **Trade name:** WAVECALMIX VIS ZODIAC
- **Article number** N9302946
- **Application of the substance / the mixture** Laboratory chemicals
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**

PerkinElmer, Inc.  
710 Bridgeport Avenue  
Shelton, Connecticut 06484 USA  
CustomerCareUS@perkinelmer.com

- **Emergency telephone number:**  
CHEMTREC (within US) 800-424-9300  
CHEMTREC (from outside US) +1 703-527-3887 (call collect)

## 2 Hazard(s) identification

- **Classification of the substance or mixture**



Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2 H319 Causes serious eye irritation.

- **Label elements**
- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms** GHS07
- **Signal word** Warning
- **Hazard statements**  
H315 Causes skin irritation.  
H319 Causes serious eye irritation.

- **Precautionary statements**

P280 Wear protective gloves/protective clothing/eye protection/face protection.  
P264 Wash thoroughly after handling.  
P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P321 Specific treatment (see on this label).  
P332+P313 If skin irritation occurs: Get medical advice/attention.  
P337+P313 If eye irritation persists: Get medical advice/attention.  
P302+P352 IF ON SKIN: Wash with plenty of water.  
P362+P364 Take off contaminated clothing and wash it before reuse.

- **Classification system:**

- **NFPA ratings (scale 0 - 4)**



Health = 1  
Fire = 0  
Reactivity = 0

- **HMIS-ratings (scale 0 - 4)**



Health = 1  
Fire = 0  
Reactivity = 0

**Trade name: WAVECALMIX VIS ZODIAC**

(Contd. of page 1)

· **Other hazards**

The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds or formaldehydes.

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

### 3 Composition/information on ingredients

· **Chemical characterization: Substances**

· **CAS No. Description**

7732-18-5 Water


· **Identification number(s)**

· **EC number:** 231-791-2










· **Chemical characterization: Mixtures**

· **Description:** Mixture of the substances listed below with nonhazardous additions.

· **Hazardous components:**

7697-37-2	Nitric Acid	 Ox. Liq. 3, H272  Skin Corr. 1A, H314	2.0%
-----------	-------------	---	------

· **Additional Components**

7440-09-7	potassium	 Water-react. 1, H260  Skin Corr. 1B, H314	0.005%
1312-81-8	lanthanum oxide		0.001%
7439-93-2	lithium	 Water-react. 1, H260  Skin Corr. 1B, H314	0.001%
1317-35-7	trimanganese tetraoxide		0.001%
7440-23-5	sodium	 Water-react. 1, H260  Skin Corr. 1B, H314	0.001%
10042-76-9	strontium nitrate	 Ox. Sol. 2, H272	0.001%
7440-39-3	barium	 Water-react. 2, H261	0.0001%
7440-70-2	calcium	 Water-react. 2, H261	0.0001%
7732-18-5	Water		97.9898%

### 4 First-aid measures

· **Description of first aid measures**

· **General information:** Immediately remove any clothing soiled by the product.

· **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** If symptoms persist consult doctor.

· **Most important symptoms and effects, both acute and delayed** No further relevant information available.

· **Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

**Trade name: WAVECALMIX VIS ZODIAC**

(Contd. of page 2)

## 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

## 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:**  
Inform respective authorities in case of seepage into water course or sewage system.  
Dilute with plenty of water.  
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

## 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

### 7697-37-2 Nitric Acid

PEL	Long-term value: 5 mg/m <sup>3</sup> , 2 ppm
REL	Short-term value: 10 mg/m <sup>3</sup> , 4 ppm Long-term value: 5 mg/m <sup>3</sup> , 2 ppm
TLV	Short-term value: 10 mg/m <sup>3</sup> , 4 ppm Long-term value: 5.2 mg/m <sup>3</sup> , 2 ppm

- **Additional information:** The lists that were valid during the creation were used as basis.

(Contd. on page 4)

**Trade name: WAVECALMIX VIS ZODIAC**

(Contd. of page 3)

- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
Keep away from foodstuffs, beverages and feed.  
Immediately remove all soiled and contaminated clothing.  
Wash hands before breaks and at the end of work.  
Avoid contact with the eyes and skin.
- **Breathing equipment:** Not required.
- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**  
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**  
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:**



Tightly sealed goggles or safety glasses

## 9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Liquid
Color:	Transparent
- **Odor:** Odorless
- **Odour threshold:** Not determined.
- **pH-value:** Not determined.
- **Change in condition**

Melting point/Melting range:	0 °C (32 °F)
Boiling point/Boiling range:	100 °C (212 °F)
- **Flash point:** Not applicable.
- **Flammability (solid, gaseous):** Not applicable.
- **Ignition temperature:**
- **Decomposition temperature:** Not determined.

(Contd. on page 5)

**Trade name: WAVECALMIX VIS ZODIAC**

(Contd. of page 4)

· <b>Auto igniting:</b>	Product is not selfigniting.
· <b>Danger of explosion:</b>	Product does not present an explosion hazard.
· <b>Explosion limits:</b>	
<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.
· <b>Vapor pressure at 20 °C (68 °F):</b>	23 hPa (17 mm Hg)
· <b>Density at 20 °C (68 °F):</b>	1 g/cm <sup>3</sup> (8.345 lbs/gal)
· <b>Relative density</b>	Not determined.
· <b>Vapour density</b>	Not determined.
· <b>Evaporation rate</b>	Not determined.
· <b>Solubility in / Miscibility with Water:</b>	Fully miscible.
· <b>Partition coefficient (n-octanol/water):</b>	Not determined.
· <b>Viscosity:</b>	
<b>Dynamic:</b>	Not determined.
<b>Kinematic:</b>	Not determined.
· <b>Solvent content:</b>	
<b>Organic solvents:</b>	0.0 %
<b>Water:</b>	98.0 %
· <b>Other information</b>	No further relevant information available.

## 10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**  
The product shows the following dangers according to internally approved calculation methods for preparations:  
Irritant
- **Carcinogenic categories**
- **IARC (International Agency for Research on Cancer)**
- None of the ingredients is listed.

(Contd. on page 6)

Printing date 09/18/2015

Review date 09/18/2015

**Trade name: WAVECALMIX VIS ZODIAC**

(Contd. of page 5)

· **NTP (National Toxicology Program)**

None of the ingredients is listed.

· **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

**12 Ecological information**

· **Toxicity**

· **Aquatic toxicity:** No further relevant information available.

· **Persistence and degradability** No further relevant information available.

· **Behavior in environmental systems:**

· **Bioaccumulative potential** No further relevant information available.

· **Mobility in soil** No further relevant information available.

· **Additional ecological information:**

· **General notes:** Generally not hazardous for water

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **Other adverse effects** No further relevant information available.

**13 Disposal considerations**

· **Waste treatment methods**

· **Recommendation:**

Dispose of container and materials in accordance with local, regional and national regulations.

· **Uncleaned packagings:**

· **Recommendation:** Disposal must be made according to official regulations.

· **Recommended cleansing agent:** Water, if necessary with cleansing agents.

**14 Transport information**

· **UN-Number**

· **DOT, ADR, IMDG, IATA** UN3264

· **UN proper shipping name**

· **DOT, ADR** Corrosive liquid, acidic, inorganic, n.o.s.

· **IMDG, IATA** CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S.

· **Transport hazard class(es)**

· **DOT, ADR, IMDG, IATA**

· **Class** 8 Corrosive substances

· **Packing group**

· **DOT, ADR, IMDG, IATA** III

· **Environmental hazards:**

· **Marine pollutant:** No

· **Special precautions for user**

Warning: Corrosive substances

· **EMS Number:** F-A,S-B

(Contd. on page 7)

Printing date 09/18/2015

Review date 09/18/2015

**Trade name: WAVECALMIX VIS ZODIAC**





(Contd. of page 6)

· <b>Segregation groups</b>	Acids
· <b>Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	
· <b>DOT</b>	
· <b>Quantity limitations</b>	On passenger aircraft/rail: 5 L On cargo aircraft only: 60 L
· <b>ADR</b>	
· <b>Excepted quantities (EQ)</b>	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· <b>IMDG</b>	
· <b>Limited quantities (LQ)</b>	5L
· <b>Excepted quantities (EQ)</b>	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· <b>UN "Model Regulation":</b>	UN 3264 CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S., 8, III

\*

## 15 Regulatory information

### · Safety, health and environmental regulations/legislation specific for the substance or mixture

7732-18-5	Water		97.9898%
7697-37-2	Nitric Acid	 Ox. Liq. 3, H272  Skin Corr. 1A, H314	2.0%
7440-09-7	potassium	 Water-react. 1, H260  Skin Corr. 1B, H314	0.005%

### · Sara

#### · Section 355 (extremely hazardous substances):

7697-37-2	Nitric Acid
-----------	-------------

#### · Section 313 (Specific toxic chemical listings):

7697-37-2	Nitric Acid
1317-35-7	trimanganese tetraoxide
10042-76-9	strontium nitrate
7440-39-3	barium

#### · TSCA (Toxic Substances Control Act):

All ingredients are listed.

7697-37-2	Nitric Acid
7440-09-7	potassium
1312-81-8	lanthanum oxide
7439-93-2	lithium
1317-35-7	trimanganese tetraoxide
7440-23-5	sodium
10042-76-9	strontium nitrate

(Contd. on page 8)



Printing date 09/18/2015

Review date 09/18/2015

**Trade name: WAVECALMIX VIS ZODIAC**

(Contd. of page 7)

7440-39-3	barium
7440-70-2	calcium
7732-18-5	Water

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

· **Cancerogenity categories**

· **EPA (Environmental Protection Agency)**

1317-35-7	trimanganese tetraoxide	D
7440-39-3	barium	D, CBD(inh), NL(oral)

· **TLV (Threshold Limit Value established by ACGIH)**

7440-39-3	barium	A4
-----------	--------	----

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

· **Hazard pictograms** GHS07

· **Signal word** Warning

· **Hazard statements**

H315 Causes skin irritation.

H319 Causes serious eye irritation.

· **Precautionary statements**

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P264 Wash thoroughly after handling.

P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P321 Specific treatment (see on this label).

P332+P313 If skin irritation occurs: Get medical advice/attention.

P337+P313 If eye irritation persists: Get medical advice/attention.

P302+P352 IF ON SKIN: Wash with plenty of water.

P362+P364 Take off contaminated clothing and wash it before reuse.

· **National regulations:**

· **Information about limitation of use:**

Workers are not allowed to be exposed to this hazardous material. Exceptions can be made by the authorities in certain cases.

· **Water hazard class:** Generally not hazardous for water.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

**16 Other information**

**Disclaimer**

The information provided in this Material Safety Data Sheet is based on our present knowledge, and believed to be correct at the date of publication. However, no representation is made

(Contd. on page 9)



**Trade name: WAVECALMIX VIS ZODIAC**

(Contd. of page 8)

*concerning its accuracy and completeness. It is intended as guidance only, and is not to be considered a warranty or quality specification. All materials may present unknown hazards, and should be used with caution. Although certain hazards are described, we cannot guarantee that these are the only hazards which exist. PerkinElmer shall not be held liable for any damage resulting from handling or from contact with the product.*

• **Contact:**

*With in the USA: 1-(800)-762-4000*

*Out side the USA: 1-(203)-712-8488*

• **Abbreviations and acronyms:**

*RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)*

*ICAO: International Civil Aviation Organisation*

*ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*

*IMDG: International Maritime Code for Dangerous Goods*

*DOT: US Department of Transportation*

*IATA: International Air Transport Association*

*ACGIH: American Conference of Governmental Industrial Hygienists*

*EINECS: European Inventory of Existing Commercial Chemical Substances*

*ELINCS: European List of Notified Chemical Substances*

*CAS: Chemical Abstracts Service (division of the American Chemical Society)*

*NFPA: National Fire Protection Association (USA)*

*HMIS: Hazardous Materials Identification System (USA)*

*PBT: Persistent, Bioaccumulative and Toxic*

*vPvB: very Persistent and very Bioaccumulative*

*Ox. Liq. 3: Oxidising Liquids, Hazard Category 3*

*Skin Corr. 1A: Skin corrosion/irritation, Hazard Category 1A*

*Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2*

*Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2*

• **\* Data compared to the previous version altered.**