




HuR Antibody [4G8]

CATALOG NUMBER: 51-453



Immunohistochemistry of human breast tissue stained using HuR Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	HuR antibody can be used in ELISA, Western Blot starting at 1:1000, immunohistochemistry starting at 1:400, immunofluorescence, and immunoprecipitation.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	ELAVL1 (AAH03376, 1 a.a. ~ 101 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Store HuR antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ELAVL1, ELAV1, Hua, HUR, Hu antigen R, ELAV-like protein 1, Hu-antigen R, MeIG
ACCESSION NO.:	Q15717
PROTEIN GI NO.:	20981691
OFFICIAL SYMBOL:	ELAVL1
GENE ID:	1994

Background

