




CDC123 Antibody [4B9]

CATALOG NUMBER: 51-537



Immunohistochemistry of human testis tissue stained using CDC123 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	CDC123 antibody can be used in ELISA starting at 1: 10000, Western Blot starting at 1: 200 - 1: 1000, and immunohistochemistry starting at 1:200.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	C10orf7 (AAH09598, 1 a.a. ~ 337 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Store CDC123 antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CDC123, C10orf7, D123, HT-1080, Protein D123, PZ32
ACCESSION NO.:	O75794
PROTEIN GI NO.:	74739631
OFFICIAL SYMBOL:	CDC123
GENE ID:	8872

Background

