



EAT2A Antibody

CATALOG NUMBER: 46-836

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:1,000.

IMMUNOGEN: EAT2A antibody was raised against a 14 amino acid synthetic peptide near the C-Terminus of EAT2A.

HOST SPECIES: Goat

Properties

PURIFICATION: EAT2A antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: EAT2A antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: Sh2d1b, SH2 domain protein 1B [Mus musculus], MGI:1349420, EAT-2, EAT-2A, Eat2, Eat2a, EWS/FLI1 activated transcript 2, Sh2d1b2, SH2 domain protein 1B2, EAT-2B, Eat2b, Sh2d1c, EAT-2-related transducer, Sh2d1b1

ACCESSION NO.: NP_036139.2

PROTEIN GI NO.: 31542592

OFFICIAL SYMBOL: Sh2d1b / Sh2d1b2 (mouse)

GENE ID: 26904 (mouse);

Background

REFERENCES: 1) Roncagalli R, Taylor JE, Zhang S, Shi X, Chen R, Cruz-Munoz ME, Yin L, Latour S, Veillette A. Negative regulation of natural killer cell function by EAT-2, a SAP-related adaptor. Nat Immunol. 2005 Oct;6(10):1002-10.

FOR RESEARCH USE ONLY

December 13, 2016