



Foxp3 Antibody [3G3] (PE)

CATALOG NUMBER: 77-149

Specifications

SPECIES REACTIVITY:	Mouse
TESTED APPLICATIONS:	FACS
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	The 3G3 monoclonal antibody specifically reacts with the mouse 50-55 kDa Foxp3 protein (JM2, IPEX), a member of the forkhead family of transcription factors.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	The monoclonal antibody was purified utilizing affinity chromatography and unreacted dye was removed from the product.
PHYSICAL STATE:	liquid
BUFFER:	Phosphate-buffered aqueous solution, ≤0.09% Sodium azide, may contain carrier protein/stabilizer, pH7.2.
CONCENTRATION:	0.2 mg/mL
STORAGE CONDITIONS:	The product should be stored undiluted at 4°C and should be protected from prolonged exposure to light. Do not freeze.
CLONALITY:	Monoclonal
ISOTYPE:	Mouse IgG1, kappa
CONJUGATE:	PE

Additional Info

ALTERNATE NAMES:	sf, JM2, scurf, Foxp3
OFFICIAL SYMBOL:	Foxp3
GENE ID:	20371

Background

BACKGROUND:	The 3G3 monoclonal antibody specifically reacts with the mouse 50-55 kDa Foxp3 protein (JM2, IPEX), a member of the forkhead family of transcription factors. Foxp3 is expressed by the Treg lymphocytes, whose development and function are influenced by the forkhead protein. Ectopic expression of Foxp3 in T lymphocytes inhibits their activity and cytokine expression. Mutations of Foxp3 result in the "scurfy" mice phenotype.
--------------------	--

FOR RESEARCH USE ONLY

December 13, 2016