



S100 calcium binding protein A15A Recombinant Protein

CATALOG NUMBER: 92-713

Specifications

| | |
|------------------------|--|
| SPECIES: | Mouse |
| SOURCE SPECIES: | E. coli |
| SEQUENCE: | Met1-Tyr108 |
| FUSION TAG: | Tag Free |
| APPLICATIONS: | This recombinant protein can be used for biological assays. For research use only. |

Properties

| | |
|------------------------------------|---|
| PURITY: | Greater than 95% as determined by reducing SDS-PAGE. Endotoxin level less than 0.1 ng/ug (1 IEU/ug) as determined by LAL test. |
| PREDICTED MOLECULAR WEIGHT: | 12.9 kD |
| PHYSICAL STATE: | Lyophilized |
| BUFFER: | Lyophilized from a 0.2 um filtered solution of PBS, pH7.4. It is not recommended to reconstitute to a concentration less than 100 ug/ml. Dissolve the lyophilized protein in ddH ₂ O. |
| STORAGE CONDITIONS: | Lyophilized protein should be stored at -20°C, though stable at room temperature for 3 weeks. Reconstituted protein solution can be stored at 4-7°C for 2-7 days. Aliquots of reconstituted samples are stable at -20°C for 3 months. |

Additional Info

| | |
|-------------------------|--|
| ALTERNATE NAMES: | S100 calcium-binding protein A15A, Protein S100-A15A, Protein S100-A7A, S100 calcium-binding protein A7A, S100a15a |
| ACCESSION NO.: | Q6S5I3 |

Background

Description not available.

FOR RESEARCH USE ONLY

December 21, 2016