

## 1 Identification

- **Product identifier**
- **Trade name:** Taq Pol 5 U/ul
- **Article number:** EPTQD025
- **Application of the substance / the mixture** Research use only.
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
MP Biomedicals, LLC  
29525 Fountain Parkway  
Solon, OH 44139  
United States  
www.mpbio.com
- **Information department:** Product safety department
- **Emergency telephone number:** CHEMTREC: 1-800-424-9300 (1-703-527-3887)

## 2 Hazard(s) identification

- **Classification of the substance or mixture**  
The product is not classified according to the Globally Harmonized System (GHS).
- **Label elements**
- **GHS label elements** Void
- **Hazard pictograms** Void
- **Signal word** Void
- **Hazard statements** Void
- **Classification system:**
- **NFPA ratings (scale 0 - 4)**



- **HMIS-ratings (scale 0 - 4)**



- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

## 3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** Mixture of the substances listed below with nonhazardous additions.

### Dangerous components:

CAS: 56-81-5 EINECS: 200-289-5 RTECS: MA8050000	Glycerol	25-50%
---	----------	--------

## 4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.

(Contd. on page 2)

# Safety Data Sheet

## acc. to OSHA HCS

Printing date 12/22/2015

Reviewed on 12/21/2015

**Trade name: Taq Pol 5 U/ul**

(Contd. of page 1)

- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:**  
Dilute with plenty of water.  
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### 7 Handling and storage

- **Handling:**
- **Precautions for safe handling** No special measures required.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:** -20 °C
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Specific end use(s)** No further relevant information available.

### 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

#### 56-81-5 Glycerol

PEL Long-term value: 15\* 5\*\* mg/m<sup>3</sup>  
mist; \*total dust \*\*respirable fraction

TLV TLV withdrawn-insufficient data human occup. exp.

- **Additional information:** The lists that were valid during the creation were used as basis.

(Contd. on page 3)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2015

Reviewed on 12/21/2015

Trade name: Taq Pol 5 U/ul

(Contd. of page 2)

- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
The usual precautionary measures for handling chemicals should be followed.
- **Breathing equipment:** Not required.
- **Protection of hands:**  
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.  
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**  
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**  
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Goggles recommended during refilling.

## 9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**
  - Form: Liquid
  - Color: According to product specification
- **Odor:** Characteristic
- **Odor threshold:** Not determined.
- **pH-value:** Not determined.
- **Change in condition**
  - Melting point/Melting range: Undetermined.
  - Boiling point/Boiling range: 100 °C (212 °F)
- **Flash point:** 160 °C (320 °F)
- **Flammability (solid, gaseous):** Not applicable.
- **Ignition temperature:** 400 °C (752 °F)
- **Decomposition temperature:** Not determined.
- **Auto igniting:** Product is not selfigniting.
- **Danger of explosion:** Product does not present an explosion hazard.
- **Explosion limits:**
  - Lower: 0.9 Vol %
  - Upper: 0.0 Vol %
- **Vapor pressure at 20 °C (68 °F):** 23 hPa (17 mm Hg)
- **Density:** Not determined.
- **Relative density** Not determined.
- **Vapor density** Not determined.
- **Evaporation rate** Not determined.
- **Solubility in / Miscibility with** -
- **Water:** Fully miscible.

(Contd. on page 4)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2015

Reviewed on 12/21/2015

Trade name: **Taq Pol 5 U/ul**

(Contd. of page 3)

· **Partition coefficient (n-octanol/water):** Not determined.

· **Viscosity:**

**Dynamic:** Not determined.

**Kinematic:** Not determined.

· **Solvent content:**

**Organic solvents:** 50.0 %

**Water:** 43.6 %

**VOC content:** 0.0 g/l / 0.00 lb/gl

**Solids content:** 6.4 %

· **Other information** No further relevant information available.

## 10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

· **Information on toxicological effects**

· **Acute toxicity:**

· **Primary irritant effect:**

· **on the skin:** No irritant effect.

· **on the eye:** No irritating effect.

· **Sensitization:** No sensitizing effects known.

· **Additional toxicological information:**

The product is not subject to classification according to internally approved calculation methods for preparations:

When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

· **Carcinogenic categories**

· **IARC (International Agency for Research on Cancer)**

None of the ingredients is listed.

· **NTP (National Toxicology Program)**

None of the ingredients is listed.

· **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

## 12 Ecological information

· **Toxicity**

· **Aquatic toxicity:** No further relevant information available.

· **Persistence and degradability** No further relevant information available.

· **Behavior in environmental systems:**

· **Bioaccumulative potential** No further relevant information available.

· **Mobility in soil** No further relevant information available.

(Contd. on page 5)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2015

Reviewed on 12/21/2015

Trade name: Taq Pol 5 U/ul

(Contd. of page 4)

- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (Self-assessment): slightly hazardous for water  
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

## 13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

## 14 Transport information

- |  |                 |
|--|-----------------|
| · <b>UN-Number</b>   |                 |
| · <b>DOT, ADR, ADN, IMDG, IATA</b>   | Not regulated   |
| · <b>UN proper shipping name</b>   |                 |
| · <b>DOT, ADR, ADN, IMDG, IATA</b>   | Not regulated   |
| · <b>Transport hazard class(es)</b>  |                 |
| · <b>DOT, ADR, ADN, IMDG, IATA</b>   |                 |
| · <b>Class</b>   | Not regulated   |
| · <b>Packing group</b>   |                 |
| · <b>DOT, ADR, IMDG, IATA</b>  | Not regulated   |
| · <b>Environmental hazards:</b>  |                 |
| · <b>Marine pollutant:</b>   | No              |
| · <b>Special precautions for user</b>  | Not applicable. |
| · <b>Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b> | Not applicable. |
| · <b>UN "Model Regulation":</b>  | Not regulated   |

## 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**

- **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

- **TSCA (Toxic Substances Control Act):**

56-81-5 Glycerol

7447-40-7 Potassium Chloride

1185-53-1 Tris Hydrochloride

(Contd. on page 6)

# Safety Data Sheet

acc. to OSHA HCS

Printing date 12/22/2015

Reviewed on 12/21/2015

Trade name: **Taq Pol 5 U/ul**

(Contd. of page 5)

9004-95-9	LUBROL
60-00-4	edetic acid
7732-18-5	Water

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

· **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** Void

· **Hazard pictograms** Void

· **Signal word** Void

· **Hazard statements** Void

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Product safety department

· **Date of preparation / last revision** 12/22/2015 / -

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety & Health

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit