SAFETY DATA SHEET

Issuing Date 19-Oct-2010 **Revision Date** 08-Jan-2016 **Revision Number** 2

1. PRODUCT AND COMPANY IDENTIFICATION

Product Identifier
Product Name Agarose RA

Other means of identification
Product Code(s) N605
Synonyms No information available

Recommended use of the chemical and restrictions on use
Recommended Use For Further Manufacturing Use Only.
Uses advised against Not for Human or Animal Drug Use

Details of the supplier of the safety data sheet

Company Address	**Manufacturer Address**
VWR International, LLC	VWR International, LLC
Radnor Corporate Center	28600 Fountain Parkway
100 Matsonford Road	Solon, Ohio 44139
Radnor, PA 19087-8660	
Company Phone Number	1-800-448-4442
E-mail Address	info@amresco-inc.com

Emergency Telephone Number
Emergency Telephone Number Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status
This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.122)

Label elements

Emergency Overview

Appearance Fine white **Physical State** Powder **Odor** No information available

Hazards not otherwise classified (HNOC)
Not regulated
Other Information
Unknown Acute Toxicity 100 % of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS-No	EC No.	Weight %	Trade Secret
Agarose	9012-36-6	232-731-8	95-100	Not applicable

4. FIRST AID MEASURES

First Aid Measures

Eye Contact Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Skin Contact Wash off immediately with soap and plenty of water removing all contaminated clothes and shoes.

Inhalation Move to fresh air. If not breathing, give artificial respiration.

Ingestion Never give anything by mouth to an unconscious person. Rinse mouth.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms/Effects No information available.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media
Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media No information available.

Specific Hazards Arising from the Chemical
No information available.

Explosion Data
Sensitivity to Mechanical Impact None.
Sensitivity to Static Discharge None.

Protective Equipment and Precautions for Firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal protection Ensure adequate ventilation, especially in confined areas.

Environmental Precautions

Environmental Precautions See Section 12 for additional Ecological information.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for Cleaning Up Avoid dust formation. Pick up and transfer to properly labeled containers. Ventilate area and wash spill site after material pickup is complete.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible Products Strong oxidizing agents.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Agarose 9012-36-6	-	-	-

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/Face Protection Avoid contact with eyes. Safety glasses with side-shields.

Skin and Body Protection Wear protective gloves/clothing.

Respiratory Protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical State Powder
Appearance Fine white
Color No information available
Odor No information available
Odor Threshold No information available

Property	Values	Remarks • Method
pH	No information available	
Melting point/freezing point		
Boiling Point/Range	No information available	
Flash Point (High in °C)	No information available	
Evaporation Rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	No information available	
Vapor Density	No information available	
Specific Gravity	No information available	
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition coefficient	No information available	
Autoignition Temperature	No information available	
Decomposition Temperature	No information available	
Kinematic viscosity	No information available	

Dynamic viscosity	No information available
Explosive Properties	No information available
Oxidizing Properties	No information available

Other Information

Softening Point	No information available
Molecular Weight	No information available
VOC Content	No information available
Density	No information available
Bulk Density	No information available

10. STABILITY AND REACTIVITY

Reactivity
No data available

Chemical Stability
Stable under recommended storage conditions.
Possibility of Hazardous Reactions
None under normal processing.
Conditions to Avoid
Extremes of temperature and direct sunlight.
Incompatible Materials
Strong oxidizing agents.
Hazardous Decomposition Products
Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	There is no data available for this product.
Eye Contact	There is no data available for this product.
Skin Contact	There is no data available for this product.
Ingestion	There is no data available for this product.

Chemical Name	LD50 Oral	LD50 Dermal	LC50 Inhalation
Agarose 9012-36-6	-	-	-

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No information available.
Mutagenic Effects	No information available.
Carcinogenicity	No information available.

Chemical Name	ACGIH	IARC	NTP	OSHA
Agarose 9012-36-6	-	-	-	-

Reproductive Toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Aspiration hazard	No information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 100 % of the mixture consists of ingredient(s) of unknown toxicity

12. ECOLOGICAL INFORMATION

Ecotoxicity

100% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Toxicity to Fish	Crustacea
Agarose 9012-36-6	-	-	-

Persistence and Degradability
No information available.

Bioaccumulation/Accumulation
No information available.

Chemical Name	Partition coefficient
Agarose 9012-36-6	-

Other Adverse Effects No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Waste Disposal Method Dispose of material in accordance with all federal, state, and local regulations.

Contaminated Packaging Do not re-use empty containers.

Chemical Name	RCRA - Halogenated Organic Compounds	RCRA - P Series Wastes	RCRA - F Series Wastes	RCRA - K Series Wastes
Agarose 9012-36-6	-	-	-	-

Chemical Name	California Hazardous Waste Status
Agarose 9012-36-6	-

14. TRANSPORT INFORMATION

DOT Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies
EINECS/ELINCS	Complies
ENCS	Does not Comply
IECSC	Complies
KECL	Complies
PICCS	Complies

AICS Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AICS - Australian Inventory of Chemical Substances

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

Component	SARA 313 - Threshold Values %
Agarose 9012-36-6 (95-100)	-

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Agarose 9012-36-6	-	-	-	-

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

Chemical Name	Hazardous Substances RQs	Extremely Hazardous Substances RQs	RQ
Agarose 9012-36-6	-	-	-

U.S. State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

Chemical Name	California Prop. 65
Agarose - 9012-36-6	-

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Agarose 9012-36-6	-	-	-

U.S. EPA Label Information

EPA Pesticide Registration Number Not regulated

16. OTHER INFORMATION

Issuing Date 19-Oct-2010
Revision Date 08-Jan-2016
Revision Note
No information available

Disclaimer

The above information is believed to be correct but does not purport to be all-inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product. VWR International and its Affiliates shall not be held liable for any damage resulting from handling.

End of Safety Data Sheet