

VWR® UNDERCOUNTER  
LABORATORY  
REFRIGERATORS & FREEZERS

Temperature Uniformity

Easy Maintenance & Security

Compact Design



# VWR® UNDERCOUNTER LABORATORY REFRIGERATORS & FREEZERS



| MODEL NUMBER                    | 14236-525/ 82028-525                                  | 97014-903/ 97014-901                         |
|---------------------------------|-------------------------------------------------------|----------------------------------------------|
| ACCESS PORT                     | Right Side Top                                        |                                              |
| CABINET INSULATION              | Rigid Polyurethane Foamed-in Place                    |                                              |
| DATA MANAGEMENT                 | Skin Condenser Type                                   |                                              |
| DEFROST METHOD                  | Auto Cycle                                            | Manual                                       |
| DOOR SWING                      | Right-Side Hinge                                      |                                              |
| EXTERIOR DIMENSIONS (W X D X H) | 21.4" x 22.8" x 33.6" [543 x 579 x 854 mm]            | 21.4" x 25.9" x 33.6" [543 x 657 x 854 mm]   |
| EVAPORATOR                      | Roll Bond                                             | Wire and Tube                                |
| INTERIOR STORAGE                | 3 Adjustable Cantilever Wire Shelves                  | 2 Fixed Shelves with Cooling Coil in Shelves |
| NET WEIGHT                      | 76 lbs. (34.5 kg)                                     | 74 lbs. (33.6 kg)                            |
| POWER REQUIREMENTS              | AC 115V, 60 Hz                                        | AC 115V, 60 Hz                               |
| REFRIGERANT                     | R-134a                                                |                                              |
| SHIPPING DIMENSIONS (W X D X H) | 31.5" x 27.3" x 41.5" [800 x 692 x 1054 mm]           | 31.5" x 27.3" x 41.5" [800 x 692 x 1054 mm]  |
| NET SHIPPING WEIGHT             | 100 lbs. (45.4 kg)                                    | 98 lbs. (44.5 kg)                            |
| TEMPERATURE CONTROL             | Temperature control thermostad located inside chamber |                                              |
| TEMPERATURE RANGE               | -23°C to -12°C (maximum ambient temperature at 32°C)  |                                              |
| VOLUME                          | 4.9 cu. ft. (139 liters)                              | 5.0 cu. ft. (142 liters)                     |